

## Cabinet workbench, series V 2800

Universal coating 2800 mm, 4 drawers with full extension, 2 doors



### Application:

For 2 workstations

### Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 2 drawers with 100% full extension on the left, 1 x front height 180 mm, 1 x front height 360 mm, 1 door, height 540 mm on the right per workstation



<b>Art. no.</b>	<b>50201 457</b>
<b>Brand</b>	ANKE
<b>Manufacturer Part Number</b>	999.003.0140
<b>Number of drawers</b>	4 PCS
<b>Working height</b>	900 mm
<b>Number of doors</b>	2 PCS
<b>Worktop width</b>	2800 mm
<b>Worktop height</b>	50 mm
<b>Pullout type</b>	Full extension
<b>Worktop depth</b>	700 mm
<b>Colour of front</b>	Optional
<b>Cabinet colour</b>	Optional
<b>Drawer surface</b>	0.27 m <sup>2</sup>
<b>With single pull-out safety brake</b>	Yes
<b>Levelling</b>	Yes
<b>Lock type</b>	DOM® locking system
<b>Drawer front height</b>	2 x 180 mm, 2 x 360 mm
<b>Surface</b>	Powder-coated
<b>Drawer width (inner dimension)</b>	500 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	500 x 540 mm
<b>Load-carrying capacity</b>	1500 kg
<b>Drawer depth (inner dimension)</b>	540 mm
<b>Load-carrying capacity per drawer</b>	100 kg
<b>Material of worktop</b>	Universal covering
<b>Central locking</b>	Yes
<b>Gross Weight</b>	221.153 kg
<b>Product Group</b>	502

### EAN

4014641012625