

Disc brushes - with silicon carbide grain

For universal use – especially suitable for aluminium machining

ATORN®

Application

On CNC machining centres and with the use of robots, preferably in wet sanding with coolant. Machining flat components: precise deburring, edge rounding, fine machining after milling, surface finishing of e.g. sealing and contact surfaces.

Version

- With longitudinal slot for clamping on face mill arbors (DIN 6357) and combi mill arbors (DIN 6358) – no additional accessories required
- Disc brushes with dense sanding bristle trim (full trim) fully encapsulated in the plastic disc
- Ideally suited for the machining of aluminium

Advantage

- Post-machining directly after the cutting process – without changing the geometry of the workpiece
- Continuously released abrasive grain ensures reproducible results
- Very high dimensional stability and accuracy
- Controllable wear properties to end of tool life – no bristle breakage
- 4 x higher trim density produced than in conventional process (stamped)



| | |
|---------------------------------|------------------|
| Art. No. | 76098 615 |
| Brush diameter | 50 mm |
| Bore diameter | 16 mm |
| Edging material | Silicon carbide |
| Filling length | 35 mm |
| Grid size | 180 |
| Min./max. rotation speed | 2200-2500 rpm |
| Min./max. feed speed | 2000-4500 mm/min |

EAN-Code

4050293621389