



Figure similar

SIMATIC DP, IM151-8F PN/DP CPU FOR ET200S, 256 KB WORKING MEMORY, INT. PROFINET INTERFACE (WITH THREE RJ45 PORTS) AS IO-CONTROLLER, W/O BATTERY MMC REQUIRED

Product type designation

General information

Hardware product version	01
Firmware version	V3.2
Engineering with	
<ul style="list-style-type: none"> Programming package 	STEP 7 V 5.5 or higher, Distributed Safety V 5.4 SP4

Supply voltage

Rated value (DC)	
<ul style="list-style-type: none"> 24 V DC 	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes; against destruction
External protection for supply cables (recommendation)	2 A min.
Mains buffering	
<ul style="list-style-type: none"> Mains/voltage failure stored energy time 	5 ms

Input current

Inrush current, max.	1.8 A; Typical
I^2t	0.13 A ² -s
from supply voltage 1L+, max.	352 mA; 426 mA with DP master module

Output current

Current output to backplane bus (DC 5 V), max.	700 mA
--	--------

Power losses

Power loss, typ.	5.5 W
Memory	
Work memory	
<ul style="list-style-type: none"> • Integrated 	256 kbyte; For program and data
<ul style="list-style-type: none"> • expandable 	No
<ul style="list-style-type: none"> • Size of retentive memory for retentive data blocks 	64 kbyte
Load memory	
<ul style="list-style-type: none"> • pluggable (MMC) 	Yes
<ul style="list-style-type: none"> • pluggable (MMC), max. 	8 Mbyte
<ul style="list-style-type: none"> • Data management on MMC (after last programming), min. 	10 y
Backup	
<ul style="list-style-type: none"> • present 	Yes; Ensured by SIMATIC Micro Memory Card (maintenance-free)
CPU processing times	
for bit operations, typ.	0.06 μ s
for word operations, typ.	0.12 μ s
for fixed point arithmetic, typ.	0.16 μ s
for floating point arithmetic, typ.	0.59 μ s
CPU-blocks	
Number of blocks (total)	1 024; (DBs, FCs, FBs); the maximum number of loadable blocks can be reduced by the MMC used.
DB	
<ul style="list-style-type: none"> • Number, max. 	1 024; Number range: 1 to 16000
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
FB	
<ul style="list-style-type: none"> • Number, max. 	1 024; Number range: 0 to 7999
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
FC	
<ul style="list-style-type: none"> • Number, max. 	1 024; Number range: 0 to 7999
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
OB	
<ul style="list-style-type: none"> • Description 	See S7-300 operation list
<ul style="list-style-type: none"> • Size, max. 	64 kbyte
<ul style="list-style-type: none"> • Number of free cycle OBs 	1; OB 1
<ul style="list-style-type: none"> • Number of time alarm OBs 	1; OB 10
<ul style="list-style-type: none"> • Number of delay alarm OBs 	2; OB 20, 21
<ul style="list-style-type: none"> • Number of time interrupt OBs 	4; OB 32, 33, 34, 35
<ul style="list-style-type: none"> • Number of process alarm OBs 	1; OB 40
<ul style="list-style-type: none"> • Number of DPV1 alarm OBs 	3; OB 55, 56, 57

• Number isochronous mode OBs	1; OB 61; only for PROFINET
• Number of startup OBs	1; OB 100
• Number of asynchronous error OBs	6; OB 80, 82, 83, 85, 86, 87 (OB83 only for centralized I/O and PROFINET IO)
• Number of synchronous error OBs	2; OB 121, 122
Nesting depth	
• per priority class	16
• additional within an error OB	4
Counters, timers and their retentivity	
S7 counter	
• Number	256
Retentivity	
— can be set	Yes
— lower limit	0
— upper limit	255
— preset	Z 0 to Z 7
Counting range	
— can be set	Yes
— lower limit	0
— upper limit	999
IEC counter	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
S7 times	
• Number	256
Retentivity	
— can be set	Yes
— lower limit	0
— upper limit	255
— preset	No retentivity
Time range	
— lower limit	10 ms
— upper limit	9 990 s
IEC timer	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
Data areas and their retentivity	
Flag	
• Number, max.	256 byte

• Retentivity available	Yes
• Retentivity preset	MB 0 to MB 15
• Number of clock memories	8; 1 memory byte
Data blocks	
• Number, max.	1 024; Number range: 1 to 16000
• Size, max.	64 kbyte
• Retentivity adjustable	Yes; via non-retain property on DB
• Retentivity preset	Yes
Local data	
• per priority class, max.	32 768 byte; Max. 2048 bytes per block
Address area	
I/O address area	
• Inputs	2 048 byte
• Outputs	2 048 byte
of which, distributed	
— Inputs	2 048 byte
— Outputs	2 048 byte
Process image	
• Inputs, adjustable	2 048 byte
• Outputs, adjustable	2 048 byte
• Inputs, default	128 byte
• Outputs, default	128 byte
Subprocess images	
• Number of subprocess images, max.	1; With PROFINET IO, the length of the user data is limited to 1600 bytes
Digital channels	
• Inputs	16 336
— Inputs, of which central	496
• Outputs	16 336
— Outputs, of which central	496
Analog channels	
• Inputs	1 021
— Inputs, of which central	124
• Outputs	1 021
— Outputs, of which central	124
Hardware configuration	
Number of modules per system, max.	63; Centralized
Mounting rail	
• Number of mounting rails that can be used	1
• Max. length of mounting rail	Station width: ≤ 1 m or < 2 m
Time of day	

Clock	
• Hardware clock (real-time clock)	Yes
• battery-backed and synchronizable	Yes
• Deviation per day, max.	10 s; Typ.: 2 s
• Backup time	6 wk; At 40 °C ambient temperature, typically
• Behavior of the clock following POWER-ON	Clock continues running after POWER OFF
• Behavior of the clock following expiry of backup period	Clock continues to run with the time at which the power failure occurred
Operating hours counter	
• Number	1
• Number/Number range	0
• Range of values	0 to 2 ³¹ hours (when using SFC 101)
• Granularity	1 hour
• retentive	Yes; Must be restarted at each restart
Clock synchronization	
• supported	Yes
• to MPI, master	No
• to MPI, slave	No
• to DP, master	Yes; With DP master module
• to DP, slave	Yes; With DP master module
• in AS, master	No
• in AS, slave	No
• on Ethernet via NTP	Yes; As client
Interfaces	
PROFINET IO	
• Number of PROFINET interfaces	3
WLAN	
• Number of wireless interfaces	0
1st interface	
Interface type	PROFINET
Physics	Ethernet
Isolated	Yes
Integrated switch	Yes
Number of ports	3; RJ45
Automatic detection of transmission speed	Yes
Autonegotiation	Yes
Autocrossing	Yes
Change of IP address at runtime, supported	Yes
Media redundancy	
• supported	Yes
• Switchover time on line break, typically	200 ms; PROFINET MRP

• Number of stations in the ring, max.	50
Functionality	
• MPI	No
• DP master	No
• DP slave	No
• PROFINET IO Device	Yes; Also simultaneously with IO Controller functionality
• PROFINET IO Controller	Yes; Also simultaneously with IO-Device functionality
• PROFINET CBA	Yes
• Open IE communication	Yes
• Web server	Yes
— Number of HTTP clients	5
• Point-to-point connection	No
PROFINET IO Controller	
• Transmission rate, max.	100 Mbit/s; full duplex
• Number of connectable IO devices, max.	128
• Max. number of connectable IO devices for RT	128
— of which in line, max.	128
• Number of IO devices with IRT and the option "high flexibility"	128
— of which in line, max.	61
• Number of IO Devices with IRT and the option "high performance", max.	64
— of which in line, max.	64
• IRT	Yes
• Shared device	Yes
• Prioritized startup	Yes
— Number of IO Devices, max.	32
• Activation/deactivation of IO Devices	Yes
— Maximum number of IO devices that can be activated/deactivated at the same time.	8
• IO Devices changing during operation (partner ports), supported	Yes
— Max. number of IO devices per tool	8
• Device replacement without swap medium	Yes
• Send cycles	250 µs, 500 µs, 1 ms; 2 ms, 4 ms (not in the case of IRT with "high flexibility" option)
• Updating time	Minimum value depends on communication share set for PROFINET I/O, on the number of I/O devices, and on the number of configured user data items.
• Updating times	250 µs to 512 ms (depends on operating mode; for more details, refer to Operating Instructions, "Interface Module IM151-8 PN/DP CPU")
Services	

— PG/OP communication	Yes
— Routing	Yes; With DP master module
— S7 communication	Yes; with loadable FBs
— Isochronous mode	Yes; OB 61; only for PROFINET IO
— Open IE communication	Yes; Via TCP/IP, ISO on TCP, and UDP
Address area	
— Inputs, max.	2 kbyte
— Outputs, max.	2 kbyte
— User data consistency, max.	1 024 byte; with PROFINET I/O
PROFINET IO Device	
Services	
— PG/OP communication	Yes
— Routing	Yes
— S7 communication	Yes; with loadable FBs
— Isochronous mode	No
— Open IE communication	Yes; Via TCP/IP, ISO on TCP, and UDP
— IRT	Yes
— PROFlenergy	Yes; With SFB 73 / 74 prepared for loadable PROFlenergy standard FB for I-Device
— Shared device	Yes
— Number of IO controllers with shared device, max.	2
Transfer memory	
— Inputs, max.	1 440 byte; Per IO Controller with shared device
— Outputs, max.	1 440 byte; Per IO Controller with shared device
Submodules	
— Number, max.	64
— User data per submodule, max.	1 024 byte
PROFINET CBA	
• acyclic transmission	Yes
• Cyclic transmission	Yes
Open IE communication	
• Open IE communication	Yes; Via TCP/IP, ISO on TCP, and UDP
• Number of connections, max.	8
• Local port numbers used at the system end	0, 20, 21, 23, 25, 80, 102, 135, 161, 443, 8080, 34962, 34963, 34964, 65532, 65533, 65534, 65535
2nd interface	
Interface type	External interface via master module 6ES7138-4HA00-0AB0
Physics	RS 485
Isolated	Yes
Power supply to interface (15 to 30 V DC), max.	No
Functionality	

• MPI	No
• DP master	Yes
• DP slave	No
• PROFINET IO Controller	No
• PROFINET IO Device	No
• PROFINET CBA	No
• Open IE communication	No
• Web server	No
DP master	
• Transmission rate, max.	12 Mbit/s
• Number of DP slaves, max.	32; Per station
Services	
— PG/OP communication	Yes
— Routing	Yes
— Global data communication	No
— S7 basic communication	Yes; I blocks only
— S7 communication	Yes
— S7 communication, as client	No
— S7 communication, as server	Yes
— Equidistance mode support	Yes
— Isochronous mode	No
— SYNC/FREEZE	Yes
— Activation/deactivation of DP slaves	Yes
— Number of DP slaves that can be simultaneously activated/deactivated, max.	8
— Direct data exchange (slave-to-slave communication)	Yes
— DPV1	Yes
Address area	
— Inputs, max.	2 048 byte
— Outputs, max.	2 048 byte
User data per DP slave	
— Inputs, max.	244 byte
— Outputs, max.	244 byte
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Communication functions	
PG/OP communication	Yes
Data record routing	Yes; With DP master module
Global data communication	

• supported	No
S7 basic communication	
• supported	Yes; I blocks
• User data per job, max.	76 byte
• User data per job (of which consistent), max.	76 byte
S7 communication	
• supported	Yes
• as server	Yes
• As client	Yes; via integrated PROFINET interface and loadable FBs
• User data per job, max.	See online help of STEP 7 (shared parameters of the SFBs/FBs and of the SFCs/FCs of S7 Communication)
Open IE communication	
• TCP/IP	Yes; via integrated PROFINET interface and loadable FBs
— Number of connections, max.	8
— Data length for connection type 01H, max.	1 460 byte
— Data length for connection type 11H, max.	32 768 byte
— Several passive connections per port, supported	Yes
• ISO-on-TCP (RFC1006)	Yes; via integrated PROFINET interface and loadable FBs
— Number of connections, max.	8
— Data length, max.	32 768 byte
• UDP	Yes; via integrated PROFINET interface and loadable FBs
— Number of connections, max.	8
— Data length, max.	1 472 byte
Web server	
• supported	Yes
• Number of HTTP clients	5
• User-defined websites	Yes
PROFINET CBA (at set setpoint communication load)	
• Setpoint for the CPU communication load	50 %
• Number of remote interconnection partners	32
• Number of functions, master/slave	30
• Total of all Master/Slave connections	1 000
• Data length of all incoming connections master/slave, max.	4 000 byte
• Data length of all outgoing connections master/slave, max.	4 000 byte
• Number of device-internal and PROFIBUS interconnections	500
• Data length of device-internal und PROFIBUS interconnections, max.	4 000 byte
• Data length per connection, max.	1 400 byte

Remote interconnections with acyclic transmission	
— Sampling frequency: Sampling time, min.	500 ms
— Number of incoming interconnections	100
— Number of outgoing interconnections	100
— Data length of all incoming interconnections, max.	2 000 byte
— Data length of all outgoing interconnections, max.	2 000 byte
— Data length per connection, max.	1 400 byte
Remote interconnections with cyclic transmission	
— Transmission frequency: Transmission interval, min.	1 ms
— Number of incoming interconnections	200
— Number of outgoing interconnections	200
— Data length of all incoming interconnections, max.	2 000 byte
— Data length of all outgoing interconnections, max.	2 000 byte
— Data length per connection, max.	450 byte
HMI variables via PROFINET (acyclic)	
— Number of stations that can log on for HMI variables (PN OPC/iMap)	3; 2x PN OPC/1x iMap
— HMI variable updating	500 ms
— Number of HMI variables	200
— Data length of all HMI variables, max.	2 000 byte
PROFIBUS proxy functionality	
— supported	Yes
— Number of linked PROFIBUS devices	16
— Data length per connection, max.	240 byte; Slave-dependent
iPAR server	
• supported	Yes
Number of connections	
• overall	12
• usable for PG communication	11
— reserved for PG communication	1
— Adjustable for PG communication, min.	1
— Adjustable for PG communication, max.	11
• usable for OP communication	11
— reserved for OP communication	1
— adjustable for OP communication, min.	1
— adjustable for OP communication, max.	11
• usable for S7 basic communication	10

— Reserved for S7 basic communication	0
— adjustable for S7 basic communication, min.	0
— adjustable for S7 basic communication, max.	10
• usable for S7 communication	10; with loadable FBs
— Adjustable for S7 communication, max.	10
• Max. total number of instances	32
• usable for routing	4; max.

S7 message functions

Number of login stations for message functions, max.	12; Depending on the configured connections for PG/OP and S7 basic communication
Process diagnostic messages	Yes; ALARM_S, ALARM_SC, ALARM_SQ, ALARM_D, ALARM_DQ
simultaneously active Alarm-S blocks, max.	300

Test commissioning functions

Status block	Yes; Up to 2 simultaneously
Single step	Yes
Number of breakpoints	4

Status/control

• Status/control variable	Yes
• Variables	Inputs, outputs, memory bits, DB, times, counters
• Number of variables, max.	30
— of which status variables, max.	30
— of which control variables, max.	14

Forcing

• Forcing	Yes
• Force, variables	I/O
• Number of variables, max.	10

Diagnostic buffer

• present	Yes
• Number of entries, max.	500
— can be set	No
— Of which powerfail-proof	100; Only the last 100 entries are retained

Interrupts/diagnostics/status information

Alarms

• Alarms	Yes
----------	-----

Diagnostic messages

• Diagnostic functions	Yes
------------------------	-----

Diagnostics indication LED

• Bus activity PROFINET P1-LINK (green)	Yes
---	-----

- Bus activity PROFINET P2-LINK (green) Yes
- Bus activity PROFINET P3-LINK (green) Yes
- Bus error (red) Yes
- Maintenance information MT (yellow) Yes
- Group error SF (red) Yes
- Monitoring 24 V voltage supply ON (green) Yes

Galvanic isolation

between PROFIBUS DP and all other circuit components Yes

Permissible potential difference

between different circuits 75V DC/60V AC

Isolation

Isolation checked with 500 V DC

Degree and class of protection

IP degree of protection IP20

Configuration

Configuration software

- STEP 7 Yes; V5.5 or higher

programming

- Command set see instruction list
- Nesting levels 8
- System functions (SFC) see instruction list
- System function blocks (SFB) see instruction list

Programming language

- LAD Yes
- FBD Yes
- STL Yes
- SCL Yes; Optional
- CFC Yes; Optional
- GRAPH Yes; Optional
- HiGraph® Yes; Optional

Know-how protection

- User program protection/password protection Yes
- Block encryption Yes; With S7 block Privacy

Cycle time monitoring

- lower limit 1 ms
- upper limit 6 000 ms
- can be set Yes
- preset 150 ms

Dimensions

Width	120 mm; DP master module: 35 mm
Height	119.5 mm
Depth	75 mm

Weights

Weight, approx.	320 g; DP master module: Approx. 100 g
-----------------	--

last modified: 12.03.2015