


PA3026



Pressure transmitter with ceramic measuring cell

PA-2,5-RBR14-A-ZVG/USI / IV



Product characteristics

Output signal	analogue signal			
Measuring range	0...2.5 bar	0...2500 mbar	0...36 psi	0...250 kPa
Process connection	threaded connection G 1/4 internal thread			

Application

Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	20 bar	290 psi	2 MPa
Pressure rating	50 bar	725 psi	5 MPa
Min. bursting pressure			
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	9.6...32 DC		
Min. insulation resistance [$M\Omega$]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Pressure transmitter with ceramic measuring cell

PA-2,5-RBR14-A-ZVG/US/ IV

Outputs				
Total number of outputs		1		
Output signal		analogue signal		
Number of analogue outputs		1		
Analogue current output [mA]		4...20		
Max. load [Ω]		720; ($U_b = 24 \text{ V}$; $(U_b - 9,6 \text{ V}) / 20 \text{ mA}$)		
Overload protection		yes		
Measuring/setting range				
Measuring range	0...2.5 bar	0...2500 mbar	0...36 psi	0...250 kPa
Accuracy / deviations				
Repeatability [% of the span]		< 0,1; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]		< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Long-term stability [% of the span]		< ± 0,05; (per 6 months)		
Temperature coefficient zero point [% of the span / 10 K]		0,1; (0...80 °C)		
Temperature coefficient span [% of the span / 10 K]		0,2; (0...80 °C)		
Response times				
Step response time analogue output [ms]		3		
Operating conditions				
Ambient temperature [°C]		-25...80		
Storage temperature [°C]		-40...100		
Protection		IP 65		
Tests / approvals				
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD		
	EN 61000-4-3 HF radiated	30 V/m		
	EN 61000-4-4 Burst	2 kV		
	EN 61000-4-6 HF conducted	10 V		
	radiation of interference	according to the automotive directive 2004/104/EC		
	CISPR 25			
	immunity	according to the automotive directive 2004/104/EC		
Shock resistance	ISO 11452-2 HF radiated	100 V/m		
	ISO 7637-2 pulse	severity level 4		
	DIN EN 60068-2-27	50 g (11 ms)		
	DIN EN 61373	category 3		
	DIN EN 60068-2-6	20 g (10...2000 Hz)		
Vibration resistance	DIN EN 61373	category 2		
	MTTF [years]	506		
	Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
	Railway applications	DIN EN 50155 / IEC 60571 Klasse T3, C1, S1		

PA3026



Pressure transmitter with ceramic measuring cell

PA-2,5-RBR14-A-ZVG/US/ IV

Mechanical data

Weight	[g]	221
Materials		stainless steel (1.4404 / 316L); FKM; PA; EPDM/X
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; FKM
Min. pressure cycles		100 million
Process connection		threaded connection G 1/4 internal thread
Restrictor element integrated		no (can be retrofitted)

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; Contacts: gold-plated



Connection

