

### Advantages

Minimum size at high output

Low height

Dual input voltage for series or parallel connection

Dual output voltage for series or parallel connection

Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDenseFill resin encapsulation

Self-extinguishing potting material


## **Applications**

As a mains transformer for adjustment of the voltage and simple electrical isolation

As an isolating transformer for the safe electrical isolation of the input and output sides. The transformer may be used to set up protective separation as a protective measure in accordance with VDE 0100.

As a safety isolating transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

## Sample application



#### Standards

Isolating transformer to: VDE 0570 Part2-4, DIN EN 61558-2-4, EN 61558-2-4, IEC 61558-2-4, UL 5085-1/-2, CSA 22.2 No.66

**Approvals** 



UL 5085-1/-2, CSA 22.2 No.66





# Isolating transformer **FL 52/24**

	Туре	FL 52/24		Type	F
Electrical data +	Input		0	Terminal and mounting	
		2 x 115 Vac	30	Terminals	Pi
	Rated frequency	50 - 60 Hz		Measures and weights	
	Output		data	Core type	UI
	Rated output voltage	2 x 24 Vac	9	Weight	0.9
	Rated Power	52 VA	ō		
	No-load voltage (app. x factor)	1.12	Mechanical	15.0 PRI SEC 16	
	No-load loss (typ.)	4.00 W	اق		
	Efficiency	81.0 %	20		<b></b>
	Standards		ž		37.0
	Classification	Isolating transformer			10.0
	Approvals				70.0
	Approvals	cURus, VDE			•
	Environment				
	Ambient temperature max.	40 °C		75.0	
	Safety and protection			<b>4</b> 86.5 ►	
	Туре	Encapsulated			
	Insulation class	VDE=E, UL=class 105			
	Protection index	IP 00			
	Safety class (prepared)	II			
	Short circuit strength	non-short-circuit proof			
	Order numbers				
	Order Number	FL 52/24			

