




**Model Number**

NCN4-12GM40-Z1

**Features**

- 4 mm not embeddable
- 2-wire DC


**Connection**



**Accessories**

**BF 12**  
Mounting flange, 12 mm

**Dimensions**



**Technical Data**

**General specifications**

Switching element function	DC	NC
Rated operating distance	$s_n$	4 mm
Installation	not embeddable	
Output polarity	DC	
Assured operating distance	$s_a$	0 ... 3.24 mm
Reduction factor $r_{Al}$	0.42	
Reduction factor $r_{Cu}$	0.4	
Reduction factor $r_{303}$	0.75	

**Nominal ratings**

Operating voltage	$U_B$	5 ... 60 V
Switching frequency	$f$	0 ... 800 Hz
Hysteresis	$H$	1 ... 10 typ. 5 %
Reverse polarity protected	tolerant	
Short-circuit protection	pulsing	
Voltage drop	$U_d$	$\leq 5$ V
Operating current	$I_L$	2 ... 100 mA
Lowest operating current	$I_m$	2 mA
Off-state current	$I_r$	0 ... 0.5 mA typ.
Indication of the switching state	all direction LED, yellow	

**Ambient conditions**

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

**Mechanical specifications**

Connection type	cabl PUR , 2 m
Core cross-section	0.14 mm <sup>2</sup>
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PBT
Protection degree	IP67

**Compliance with standards and directives**

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

**Approvals and certificates**

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Certified by China Compulsory Certification (CCC)

Release date: 2011-07-08 13:37 Date of issue: 2011-07-08 069256\_eng.xml