

Twist drill set type U4 HSSE TiNAlOX

for universal use up to 1300 N/mm²

ATORN®

Application

Universal use in all material groups up to a strength of 1300 N/mm².

Version

- twist drill with four-edge section

Advantage

- innovative cutting geometry: four-edge section for drilling without centring
- universal use up to 1300 N/mm²
- state-of-the-art coating technology: TiNAlOX coating ensures prolonged service life and process stability
- Robust and user-friendly plastic box ensures reliable protection and good accessibility



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	40	20	10	10	8	60	80	70	45	40	30	30	10	30	10	10	10		

Art. No.	11037 930
Composition of set	1,0-13,0
Pitch of drill diameter	0.5 mm
Number of pieces in assortment/set	25 PCS
Surface	TiNAlOX
Cutting material	HSSE
Type	U4 (no. 11037)
DIN	338

EAN-Code

4050293055962