

## Internal micrometer set

**ATORN®**

### Application

For measuring large bore diameters, distances on workpieces, etc.

### Version

- Scale with anti-glare, brushed chromium-plated finish
- Carbide-tipped measuring faces
- Can be individually configured for the diameter being measured
- Graduated drum, Ø 17 mm
- Measuring body, 25 mm, adjustable
- Threaded connection, M7 x 1

### Advantage

- Ready for measuring with no special settings required
- High level of measuring accuracy due to extension rods hardened at the ends, lapped along the length of the gauge block and with insulated grips to prevent transfer of heat from the hands
- Measuring range extendible via screw-on extensions

### Delivery

In wooden case



<b>Art. no.</b>	<b>31678 185</b>
<b>Min./max. length measuring range</b>	50-850 mm
<b>Digit increment</b>	0.01 mm
<b>Extensions provided</b>	400 mm, 200 mm, 100 mm, 50 mm, 25 mm
<b>DIN</b>	863

### EAN-Code

4050293402254