



MASTER TL-D Secura

MASTER TL-D Secura 36W/840 SLV/25

This TL-D lamp has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. The lamp has a Teflon coating. It is compliant with HACCP regulations.

Warnings and Safety

- Not suitable for closed luminaires (as indicated by two blue rings)
- Recommended use in combination with self-stopping lamp control system
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- In order to ensure the integrity of the coating, it is strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Product data

General Information		LSF 20000 h Rated	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		2 %
Life To 10% Failures (Nom)	12000 h	Light Technical	
Life to 50% Failures (Nom)	15000 h	Color Code	840 [CCT of 4000K]
Life to 50% Failures Preheat (Nom)	20000 h	Luminous Flux (Nom)	3200 lm
LSF 2000 h Rated	99 %	Luminous Flux (Rated) (Nom)	3200 lm
LSF 4000 h Rated	99 %	Color Designation	Cool White (CW)
LSF 6000 h Rated	99 %	Correlated Color Temperature (Nom)	4000 K
LSF 8000 h Rated	99 %	Luminous Efficacy (rated) (Nom)	89 lm/W
LSF 12000 h Rated	89 %	Color Rendering Index (Nom)	85
LSF 16000 h Rated	33 %	LLMF 2000 h Rated	96 %
		LLMF 4000 h Rated	95 %

MASTER TL-D Secura

LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Nom)	36.0 W
Lamp Current (Nom)	0.440 A

Temperature

Design Temperature (Nom)	25 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Energy Efficiency Label (EEL)	A
-------------------------------	---

Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	42 kWh


UV

Damage Factor D/fc (Nom)	0.13
--------------------------	------

Product Data

Full product code	871150064014740
Order product name	MASTER TL-D Secura 36W/840 SLV/25
EAN/UPC - Product	8711500640147
Order code	927921484076
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927921484076
Net Weight (Piece)	195.500 g
ILCOS Code	FD-36/40/1B-E-G13


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Secura 36W/840 SLV/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D 36W/840 Secura

Photometric data




LDPB_TL-D8SE_Secura_840-Spectral power distribution B/W



LDPO_TL-D8SE_Secura_840-Spectral power distribution Colour


MASTER TL-D Secura

Lifetime



LDLE_TL-D8SE_0001-Life expectancy diagram

LDLE_TL-D8SE_0002-Life expectancy diagram



LDLM_TL-D8SE_0001-Lumen maintenance diagram

