

## Data sheet

IM 306 DP slave 135U/155U (306-1UE00)


### Technical data

<b>Order no.</b>	<b>306-1UE00</b>
Type	IM 306 DP slave 135U/155U

### General information

Note	-
Features	Converting Siemens S5 PLCs to S7 Exclusively suited for AG-135U/155U central controller and expansion units Integrated DC 24V power supply

### Technical data power supply

Power supply (rated value)	DC 24 V
Power supply (permitted range)	DC 20.4...28.8 V
Reverse polarity protection	
Current consumption (no-load operation)	0.1 A
Current consumption (rated value)	1 A
Inrush current	4 A
$I^2t$	0.5 A <sup>2</sup> s
Max. current drain at backplane bus	3.5 A
Max. current drain load supply	-
Power loss	4 W

### Status information, alarms, diagnostics


Status display	yes
Interrupts	yes, parameterizable
Process alarm	no
Diagnostic interrupt	yes, parameterizable
Diagnostic functions	yes, parameterizable
Diagnostics information read-out	possible
Supply voltage display	green LED
Service Indicator	-
Group error display	red LED
Channel error display	none

### Hardware configuration

Racks, max.	1
Modules per rack, max.	18
Number of digital modules, max.	18
Number of analog modules, max.	18

### Communication

Fieldbus	PROFIBUS-DP to EN 50170
Type of interface	RS485 isolated
Connector	Sub-D, 9-pin, female
Topology	Linear bus with bus termination at both ends

Electrically isolated	
Number of participants, max.	125
Node addresses	1 - 125
Transmission speed, min.	9.6 kbit/s
Transmission speed, max.	12 Mbit/s
Address range inputs, max.	244 Byte
Address range outputs, max.	244 Byte
Number of TxPDOs, max.	-
Number of RxPDOs, max.	-

### Housing

Material	PC GF20
Mounting	-

### Mechanical data

Dimensions (WxHxD)	20 mm x 233.4 mm x 160 mm
Weight	220 g

### Environmental conditions

Operating temperature	0 °C to 60 °C
Storage temperature	-25 °C to 70 °C

### Certifications

UL508 certification	-
---------------------	---