### **FEATURES AND SPECIFICATIONS**



# molex Keystone Jack, Category 6

#### **Features and Benefits**

Utilising patented IDC V-shaped contacts that flex not fatigue when terminated, the RJ-45 Keystone Jack is compatible with any product that accepts the standard keystone profile. This would include manufacturers such as: Wiremold®, Tyco®, Krone®, Leviton® and Hubbell®.

- Patented IDC V-shaped contacts that flex not fatigue when terminated
- Features pointed IDC towers to speed termination and enhance cable retention
- Dual colour-coding allows for 568 A/B wiring configuration
- Can be terminated using industry standard punch down tools
- RJ-11 & RJ-12 compatible
- Molded category identification on iack face
- RoHS compliant

#### **Commercial Standards**

TIA/EIA-568-C.2 Category 6 ANSI/EIA-1069-A ISO 11801 Category 6 IEC 60603-7-4

Aprrovals UL-1863 CSA C22.2 ETL Verified for Category 6 Component Compliance

#### **Reference Information**

Parts List Keystone jack with stuffer cap

#### **Technical Information**

#### **Mechanical Characteristics**

**Jack Connector** 

Plastic Housing: Thermoplastic

UL94V-0

Operating Life: Minimum 750

insertion cycles

Contact Material: Copper Alloy  $50\mu^{\prime\prime}~Gold/50\mu^{\prime\prime}$ Contact Plating:

Nickel

Contact Force: 100g minimum Plug Retention Force: 11 lb minimum

**IDC** Connector

Plastic Housing: Thermoplastic

UL94V-0

Operating Life: Minimum 200

reterminations

Contact Material: Copper Alloy IDC Contact Plating: Matte Tin

Wire Accommodation: 22-24 AWG solid


#### **Electrical/Optical Characteristics**

Interface Resistance: 20 milliohms Initial Contact Resistance: 2.5 milliohms

Insulation Resistance: >100 Megaohms

Dimensions (mm): 23(H) x 18(W) x 30.6(D)

Shipping Weight: 28g





## **ORDERING INFORMATION**

Order No.	SAP No.	Description
KSJ-00033-**	Consult Molex	Keystone Jack, Category 6, 8W, 568A/B

DataGate Colours - Replace the (\*\*) in the part number with one of the following: 01 = Almond, 02 = White, 04 = Black, 05 = Ivory, 08 = Light Grey, RD = Red, BL = Blue, GR = Green, YL = Yellow, RG = Orange, PP = Purple

#### **MOLEX PREMISE NETWORKS**

**Americas** Tel: 630 969 4550 www.molexpn.com

**EMEA** Tel: 44 (0)2392 205800 www.molexpn.co.uk

**APAC** Tel: 61 3 9971 7111 www.molexpn.com.au