

## High-performance drill bit, solid carbide TiAlSiN HPC 5xD, no IC, HA

For hard machining up to 65 HRC

**ATORN®**



### Application

For HPC drilling up to 65 HRC

### Version

- 2 drill heels
- 30° spiral angle
- Convex main cutting edge

### Advantage

- High centring accuracy
- Special coating for drilling hardened steels up to 65 HRC
- Extremely hard, low-friction and temperature-resistant TiAlSiN coating for longer service life
- Reinforced core with special tip and cutting chisel edge
- No internal coolant feed for higher stability

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	80	65	40											70				28	14

<b>Art. no.</b>	<b>11126 033</b>
<b>Cutting edge diameter</b>	3.3 mm
<b>Tolerance of cutting edge diameter</b>	h7
<b>Cutting material</b>	VHM
<b>Surface</b>	TiAlSiN
<b>Max. drilling depth (D)</b>	5xD
<b>Type</b>	HPC HARD
<b>Coolant supply</b>	External
<b>Tool holding device</b>	HA parallel shank
<b>Angle of the tip</b>	140 Degree
<b>Shaft diameter</b>	6 mm
<b>Chip flute length</b>	28 mm
<b>Length</b>	66 mm
<b>f hard 65 HRC</b>	0.06 mm/r
<b>DIN</b>	6537

### EAN-Code

4050293671148