

Electronic micrometer

MICROMASTER IP54 with data output

 **TESA**

Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Execution:

- Carbide measuring faces
- Advanced friction coupling for consistent, repeatable measuring force
- Zero setting at any position
- mm/inch switch-over
- Auto off
- Preset function
- ABS function
- Display blocking function

Delivery:

In a case, with battery (1 x 3 V lithium, type CR 2032)



| | |
|---|--------------------|
| Art. no. | 31409 250 |
| Brand | TESA |
| Manufacturer Part Number | 06030077 |
| Display | Digital |
| Min./max. length measuring range | 250-275 mm |
| Min./max. length measuring range in inches | 10-11 in |
| Digit increment | 0.001 mm |
| Measuring surface diameter | 8 mm |
| Material of measuring bolt | Carbide |
| IP protection class | IP 54 |
| Data transmission type | RS232 opto coupled |
| Spindle clamping | Yes |
| Digit height | 7 mm |
| Error limit | 9 µm |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 3V CR2032 Lithium |
| DIN | 863 |
| Bracket depth | 152 mm |
| Measuring spindle increments | 0.5 mm |
| Calibration Group | D |
| Gross Weight | 2.381 kg |
| Product Group | 362 |

EAN

7630041116656