

wing door cabinets fitted with plastic inserts

for CNC tool carriers, SK 40, SK 50 or HSK 63

Application:

For secure and clearly-laid-out storage and retrieval of CNC tools

Execution:

- Sturdy sheet steel structure, lockable with grip handle and cylinder lock, including 2 keys
- With 5 pairs of guide rails, including 7 supporting profiles
- Supporting profiles are equipped with SK or HSK adapter holders (number of holders, refer to table)
- Rails are inclined (15°), can be staggered against each other and height can be adjusted in increments of 30 mm to accommodate tools of different length
- Up to 3 supporting profiles can be used per pair of rails
- fork lift-compatible base with removable base panel for in-house transport
- cabinet can be fitted with an ELECTRONIC CODE combination lock at extra charge as an option, see no. 50392 020



Art. no.	50658 040
Brand	HK
Manufacturer Part Number	50658040
Door design	Inspection glass
Equipped	SK 40
Number of attachments	140 pieces
Height	1950 mm
Width	1018 mm
Depth	620 mm
Load-carrying capacity per rail pair	150 kg
Number of carrier sections	7 PCS
Load-carrying capacity per carrier section	50 kg
Load-carrying capacity	1000 kg
Central locking	Yes
Lock type	DOM® locking system
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Gross Weight	131.000 kg
Product Group	507

EAN

4053625101788