

P/N: TA60

Revision

29569

Last modified

2015-10-13 15:55 UTC+1

Copyright

© 2018, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.

Website

<http://www.flir.com>

Customer support

<http://support.flir.com>



Part number	TA60
Part description	Thermocouple Probe with Adapter
<ul style="list-style-type: none"> Type K thermocouple temperature sensor. Can be used to measure temperature with many meters. Fast responding with a wide general-purpose measurement range. Safety-shrouded banana to banana connection. 2 year warranty 	
Specifications	
Temperature range	-40 to 1200°C (-40 to 2192°F)
Meter data	
Suitable main unit	DM93, CM78 (DM92)
Warranty	2 years
Certifications	
Certifications	ITS-90 (JIS C-1602-1995 Class 2)
Meter physical data	
Weight	0.06 kg
Dimensions (H x W x L)	15.24 cm x 3.81 cm x 1.27 cm
Material	ABS plus PC, bronze (nickel plated), PVC
Color	Black and yellow
Shipping information	
Packaging type	Color box
Packaging contents	Manual, TA60
Packaging weight:	0.08 kg
Packaging dimensions (H x W x L)	7 .62 cm x 2.54 cm x 16.83 cm
Carton weight	4 kg
Carton dimensions	14.5" x 13" x 8"
Carton quantity	48
EAN-13	0793950377604