

Product information

95 32 340 SR

ACSR Cable Cutter

(ratchet action)

For cables with a steel core



- The cable cutter cuts through ACSR cable with a steel core (= Aluminium Conductor Steel Reinforced) up to Ø 32 mm
- With one- or two-handed operation, the high leverage guarantees a simple, accurate cut
- Handy and compact with highest performance
- Extremely stable, dual guided of the revolving blade
- No fanning out of the cable: precision-ground and induction-hardened cutting edge for a clean cut and long service life
- Low handforce required due to two-stage gear drive with ratchet mechanism
- Fixed handle with support area for putting down the pliers when cutting
- Locking mechanism for transporting with safely closed handles
- All wearing parts are available as spare parts and exchangeable
- Special high grade tool steel, multi stage oil-hardened

MM



| General | |
|-----------------|----------------------------|
| Article No. | 95 32 340 SR |
| EAN | 4003773081241 |
| Shears | burnished |
| Handles | with multi-component grips |
| Weight | 1,310 g |
| Dimensions | 340 x 135 x 30 mm |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

| Technical details | |
|-------------------|--------------|
| Diameter | 32 mm |
| Inch diameter | Ø 1 1/4 Inch |
| MCM | 477 |

technical change and errors excepted



Enormous power with a weight of just 1300 g



The strong "flange" on the handle can be used as a practical support surface when cutting larger diameters