

JBC DDSE

2-Tool Rework

JBC



Product Application Map

News



The complete solution to rework circuits with medium power requirement.

Equipped with T245 General Purpose Handle and DR560 Desoldering Iron.

Its DDE 2-Tool Control Unit is capable of manage up to 2 tools simultaneously and fully compatible with 10 different JBC tools.

It provides the best rework quality thanks to JBC Most Efficient Soldering System and, additionally, the intelligent Sleep & Hibernation Modes help to extend life of tips.

**Don't believe us...
TRY IT!**



REFERENCES

Equipped with Electric Pump:

- DDSE-9QD 100 V
- DDSE-1QD 120 V
- DDSE-2QD 230 V

PRODUCT COMPOSITION

- 1 DDE 2-Tool
- 1 MSE Electric Desoldering Module for DDE & DME
- 1 T245 General Purpose Handle (cartridge not included)
- 1 DR560 Desoldering Iron (C560003 already inserted)
- 1 ADS Stand for T210 & T245 Handles
- 1 DRS Stand for DR560 Desoldering Iron
- 1 SCH Cartridge Holder

SPECIFICATIONS

Peak power	150 W per tool – 23.5 V
Selectable temperature	90 to 450 °C / 190 to 840 °F
Vacuum	75% / 570 mmHg / 22.4 inHg
Flow rate	9 SLPM
Temperature accuracy	±3%
ESD safe	Meet ANSI/ESD S20.20-2021
Equipotential bonding	Connection to EPA
Tip-to-ground resistance	<2 ohms
Tip-to-ground voltage	<2 mV RMS
USB-A	Firmware update Graphics and profiles
USB-B	PC communications
FAE / Robot connector	Remote control or FAE Fume Extractor connection

WEIGHT AND DIMENSIONS

Control Unit	232 x 148 x 120 mm / 9.25 kg. 9.13 x 5.83 x 4.72 in / 20.40 lb.
Package	525 x 318 x 347 mm / 10.39 kg. 20.67 x 12.52 x 13.66 in / 22.91 lb.