



HEATER BLOWER, WITHOUT FAN 230 V, 300 W
HV031 03111.0-00

Figure similar

| Model | | |
|---|-----|---------|
| product brand name | | SIVACON |
| General technical data | | |
| Active power consumption / Rated value | W | 300 |
| Voltage | | |
| Continuous heat output / at 20 °C | W | 300 |
| Protection class | | |
| Protection class IP | | IP20 |
| Main circuit | | |
| Operating voltage | | |
| • Rated value / minimum | V | 230 |
| • Rated value / maximum | V | 230 |
| • with AC / at 50 Hz / Rated value / minimum | V | 220 |
| • with AC / at 50 Hz / Rated value / maximum | V | 230 |
| • with AC / at 60 Hz / Rated value / maximum | V | 240 |
| Operating current / of the slow-blow fuse link | A | 2 |
| Product details | | |
| Product component | | |
| • blower | | Yes |
| • Thermostat | | No |
| Connections | | |
| Tightening torque / with screw-type terminals / maximum | N·m | 0.8 |

Mechanical Design

| | | |
|-----------------------------|----|---------|
| Height | mm | 151 |
| Width | mm | 119 |
| Depth | mm | 22 |
| Material / of the enclosure | | plastic |

Environmental conditions

| | | |
|-------------------------------------|---|----|
| Relative humidity / Reference value | % | 90 |
|-------------------------------------|---|----|

Certificates

| | | |
|--|--|--------|
| Equipment marking <ul style="list-style-type: none">• acc. to DIN EN 61346-2• acc. to DIN EN 81346-2 | | R E |
|--|--|--------|

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21403A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21403A/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR21403A

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015