

**RoHS
Compliant**



Description

MLCC consists of a conducting material and electrodes. To manufacture a chip-type SMT and achieve miniaturization, high density and high efficiency, ceramic condensers are used. The MLCC is made by NP0, X7R, X6S, X5R and Y5V dielectric material and which provides product with high electrical precision, stability and reliability.

Features

- A wide selection of sizes is available (0201 to 1812).
- High capacitance in given case size.
- Capacitor with lead-free termination (pure Tin).


Application

- For general digital circuit.
- For power supply bypass capacitors.
- For consumer electronics.
- For telecommunication.

How To Order

1206 Size	B Dielectric	104 Capacitance	K Tolerance	500 Rated Voltage	C Termination	I Packaging style
Inch (mm) 0201 (0603) 0402 (1005) 0603 (1608) 0805 (2012) 1206 (3216) 1210 (3225) 1812 (4532)	N=NP0 (C0G) B=X7R F=Y5V X=X5R S=X6S A=X7S	Two significant digits followed by no. of zeros. And R is in place of decimal point. Eg.: 0R5=0.5pF 1R0=1.0pF 104 = 10×10^4 = 100nF	A=±0.05pF B=±0.1pF C=±0.25pF D=±0.5pF F=±1% G=±2% J=±5% K=±10% M=±20%	Two significant digits followed by no. of zeros. And R is in place of decimal point. 4R0=4V DC 6R3=6.3V DC 100=10V DC 160=16V DC 250=25V DC 350=35V DC 500=50V DC 101=100V DC	C=Cu/Ni/Sn	T=7" reeled G=13" reeled

External Dimensions



The outline of MLCC

Size Inch (mm)	L (mm)	W (mm)	T (mm)/Symbol		Soldering Method *	M _B (mm)
01R5 (0402)	0.4 ±0.02	0.2 ±0.02	0.2 ±0.02	V	R	0.1 ±0.03
0201 (0603)	0.6±0.03	0.3 ±0.03	0.3 ±0.03	L	R	0.15 ±0.05
	0.6±0.05 ^{#2}	0.3 ±0.05 ^{#2}	0.3 ±0.05 ^{#2}			0.15 +0.1/-0.05
	0.6±0.09 ^{#3}	0.3 ±0.09 ^{#3}	0.3 ±0.09 ^{#3}			
0402 (1005)	1 ±0.05	0.5 ±0.05	0.5 ±0.05	N	R	0.25 +0.05/-0.1
			0.5 +0.02/-0.05	Q		
	1 ±0.2	0.5 ±0.2	0.5 ±0.2	E		
	1 ±0.15 ^{#6}	0.5 ±0.15 ^{#6}	0.5 ±0.15 ^{#6}			

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Size Inch (mm)	L (mm)	W (mm)	T (mm)/Symbol		Soldering Method *	M _B (mm)
0603 (1608)	1.6 ±0.1	0.8 ±0.1	0.8 ±0.07	S	R / W	0.4 ±0.15
	1.6 +0.15/-0.1	0.8 +0.15/-0.1	0.5 ±0.1	H	R / W	
			0.8 +0.15/-0.1	X	R / W	
	1.6 ±0.2 ^{#1}	0.8 ±0.2 ^{#1}	0.8 ±0.2 ^{#1}			
0805 (2012)	2 ±0.15	1.25 ±0.1	0.5 ±0.1	H	R / W	0.5 ±0.2
			0.6 ±0.1	A	R / W	
			0.8 ±0.1	B	R / W	
			1.25 ±0.1	D	R	
	2 ±0.2	1.25 ±0.2	0.85 ±0.1	T	R / W	
			1.25 ±0.2	I	R	
1206 (3216)	3.2 ±0.15	1.6 ±0.15	0.8 ±0.1	B	R / W	0.6 ±0.2 (0.5±0.25) ^{***}
			0.95 ±0.1	C	R	
			1.25 ±0.1	D	R	
	3.2 ±0.2	1.6 ±0.2	1.15 ±0.15	J	R	
			1.6 ±0.2	G	R	
			0.85 ±0.1	T	R / W	
	3.2 +0.3/-0.1 3.3 +0.3/-0.1 ^{#5}	1.6 +0.3/-0.1	1.6 +0.3/-0.1	P	R	
1210 (3225)	3.2 ±0.3	2.5±0.2	0.95 ±0.1	C	R	0.75 ±0.25
			0.85 ±0.1	T	R	
			1.25 ±0.1	D	R	
	3.2±0.4	2.5±0.3	1.6 ±0.2	G	R	
			2 ±0.2	K	R	
			2.5 ±0.3	M	R	
	3.20 ±0.6 ^{#4}	2.5 ±0.5 ^{#4}	2.5 ±0.5 ^{#4}			
1808 (4520)	4.5 ±0.4 (4.5+0.5/-0.3) ^{**}	2.03 ±0.25	1.25 ±0.1	D	R	0.75 ±0.25 (0.5±0.25) ^{***}
			1.4 ±0.15	F	R	
			1.6 ±0.2	G	R	
			2 ±0.2	K	R	
1812 (4532)	4.5 ±0.4 4.5+0.5/-0.3) ^{**}	3.2 ±0.3	1.25 ±0.1	D	R	0.75 ±0.25 0.5±0.25) ^{***}
			1.6 ±0.2	G	R	
			2 ±0.2	K	R	
		3.2 ±0.4	2.5 ±0.3	M	R	
			2.8 ±0.3	U	R	

* R = Reflow soldering process ; W = Wave soldering process.

** For 1808/1812/1825_200V~4000V and safety certificated products.

*** For 1206_≥1000V, 1808/1812_200V~4000V and safety certificated products.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

**General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)**

multicompPRO

#1 : For 0603/Cap $\geq$ 10 μ F or 0603/Cap $\geq$ 4.7 μ F ($\leq$ 6.3V) or 0603/Cap $>$ 1 μ F ($>$ 10V) products.

#2 : For 0201/Cap $\geq$ 0.68 μ F products.

#3 : For 0201/Cap $\geq$ 1 μ F products.

#4 : For 1210_100V: Cap $>$ 1 μ F, 250V: Cap $>$ 0.47 μ F, 400V~630V: Cap $>$ 0.22 μ F.

General Electrical Data

Dielectric	NP0	X7R	Y5V	X5R	X6S	X7S
Size	0201, 0402, 0603, 0805, 1206, 1210, 1812					
Capacitance range*	0.1pF to 0.1 μ F	100pF to 47 μ F	0.01 μ F to 100 μ F	100pF to 220 μ F	0.1 μ F to 100 μ F	1 μ F to 100 μ F
Capacitance tolerance**	Cap $\leq$ 5pF#1: A ($\pm$ 0.05pF), B ($\pm$ 0.1pF), C ($\pm$ 0.25pF) 5pF<Cap<10pF: C ($\pm$ 0.25pF), D ($\pm$ 0.5pF) Cap $\geq$ 10pF: F ($\pm$ 1%), G ($\pm$ 2%), J ($\pm$ 5%), K ($\pm$ 10%)	J ($\pm$ 5%), K ($\pm$ 10%), M ($\pm$ 20%)	M ($\pm$ 20%), Z (-20/+80%)	K ($\pm$ 10%), M ($\pm$ 20%)	K ($\pm$ 10%), M ($\pm$ 20%)	K ($\pm$ 10%), M ($\pm$ 20%)
Rated voltage (WVDC)	10V, 16V, 25V, 50V, 100V	6.3V, 10V, 16V, 25V, 50V, 100V				
DF(Tan δ)*	Cap<30pF: Q $\geq$ 400+20C Cap $\geq$ 30pF: Q $\geq$ 1000	Note 1				
Operating temperature	-55 to +125 $^{\circ}$ C		-25 to +85 $^{\circ}$ C	-55 $^{\circ}$ C to +85 $^{\circ}$ C	-55 $^{\circ}$ C to +105 $^{\circ}$ C	-55 $^{\circ}$ C to +125 $^{\circ}$ C
Capacitance Characteristic	$\pm$ 30ppm	$\pm$ 15%	+30/-80%	$\pm$ 15%	$\pm$ 22%	$\pm$ 22%
Termination	Ni/Sn (lead-free termination)					

#1: NP0, 0.1pF product only provide B tolerance; 0603N0R3/0R4 provide B&C tolerance.

*Measured at the condition of 30~70% related humidity.

NP0: Apply 1.0 $\pm$ 0.2Vrms, 1.0MHz $\pm$ 10% for Cap $\leq$ 1000pF and 1.0 $\pm$ 0.2Vrms, 1.0kHz $\pm$ 10% for Cap $>$ 1000pF, 25 $^{\circ}$ C at ambient temperature

X7R/X6S/X5R/X7S: Refer "Reliability test conditions and requirements" details.

Y5V: Apply 1.0 $\pm$ 0.2Vrms, 1kHz $\pm$ 10%, at 20 $^{\circ}$ C ambient temperature.

** Preconditioning for Class II MLCC: Perform a heat treatment at 150 $\pm$ 10 $^{\circ}$ C for 1 hour, then leave in ambient condition for 24 $\pm$ 2 hours before measurement.

Note 1:

X7R/X5R/X6S/X7S

Rated vol.	D.F. $\leq$	Exception of D.F. $\leq$	
$\geq 100V$	$\leq 2.5\%$	$\leq 3\%$	1206 $\geq 0.47\mu F$
		$\leq 5\%$	0805 $> 0.1\mu F$; 0603 $\geq 0.068\mu F$; 1206 $> 1\mu F$; 1210 $\geq 2.2\mu F$; TT series
		$\leq 10\%$	0805 $> 0.22\mu F$; 1210 $\geq 3.3\mu F$
50V	$\leq 2.5\%$	$\leq 3\%$	0201(50V); 0603 $\geq 0.047\mu F$; 0805 $\geq 0.18\mu F$; 1206 $\geq 0.47\mu F$
		$\leq 5\%$	0201 $\geq 0.01\mu F$; 1210 $\geq 4.7\mu F$
		$\leq 10\%$	0402 $\geq 0.012\mu F$; 0603 $> 0.1\mu F$; 0805 $\geq 1\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 10\mu F$; TT series
35V	$\leq 3.5\%$	$\leq 10\%$	0603 $\geq 1\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 10\mu F$
25V	$\leq 3.5\%$	$\leq 5\%$	0201 $\geq 0.01\mu F$; 0805 $\geq 1\mu F$; 1210 $\geq 10\mu F$
		$\leq 7\%$	0603 $\geq 0.33\mu F$; 1206 $\geq 4.7\mu F$
		$\leq 10\%$	0201 $\geq 0.1\mu F$; 0402 $\geq 0.10\mu F$; 0603 $\geq 0.47\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 6.8\mu F$; 1210 $\geq 22\mu F$; TT series
		$\leq 12.5\%$	0402 $\geq 0.47\mu F$
16V	$\leq 3.5\%$	$\leq 5\%$	0201 $\geq 0.01\mu F$; 0402 $\geq 0.033\mu F$; 0603 $\geq 0.15\mu F$; 0805 $\geq 0.68\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 4.7\mu F$
		$\leq 10\%$	0201 $\geq 0.1\mu F$ (0201/X7R $\geq 0.022\mu F$); 0402 $\geq 0.22\mu F$; 0603 $\geq 1206 \geq 4.7\mu F$; 1210 $\geq 22\mu F$; TT series
10V	$\leq 5\%$	$\leq 10\%$	0201 $\geq 0.012\mu F$; 0402 $\geq 0.33\mu F$ (0402/X7R $\geq 0.22\mu F$); TT series
		$\leq 15\%$	0603 $\geq 0.33\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 22\mu F$; 01R5
6.3V	$\leq 10\%$	$\leq 15\%$	0201 $\geq 0.1\mu F$; 0402 $\geq 1\mu F$; 0603 $\geq 10\mu F$; 0805 $\geq 4.7\mu F$; 1206 $\geq 47\mu F$; 1210 $\geq 100\mu F$; TT series
		$\leq 20\%$	0402 $\geq 2.2\mu F$
4V	$\leq 15\%$	-	-

Y5V

Rated vol.	D.F. $\leq$	Exception of D.F. $\leq$	
$\geq 50V$	$\leq 5\%$	$\leq 7\%$	0603 $\geq 0.1\mu F$; 0805 $\geq 0.47\mu F$; 1206 $\geq 4.7\mu F$; TT series
		$\leq 12.5\%$	1210 $\geq 6.8\mu F$
35V	$\leq 7\%$	-	-
25V	$\leq 5\%$	$\leq 7\%$	0402 $\geq 0.047\mu F$; 0603 $\geq 0.1\mu F$; 0805 $\geq 0.33\mu F$; 1206 $\geq 1\mu F$; 1210 $\geq 4.7\mu F$
		$\leq 9\%$	0402 $\geq 0.068\mu F$; 0603 $\geq 0.47\mu F$; 1206 $\geq 4.7\mu F$; 1210 $\geq 22\mu F$; TT series
16V (C $< 1.0\mu F$)	$\leq 7\%$	$\leq 9\%$	0402 $\geq 0.068\mu F$; 0603 $\geq 0.68\mu F$
		$\leq 12.5\%$	0402 $\geq 0.22\mu F$
16V (C $\geq 1.0\mu F$)	$\leq 9\%$	$\leq 12.5\%$	0603 $\geq 2.2\mu F$; 0805 $\geq 3.3\mu F$; 1206 $\geq 10\mu F$; 1210 $\geq 22\mu F$; 1812 $\geq 47\mu F$; TT series
10V	$\leq 12.5\%$	$\leq 20\%$	0402 $\geq 0.47\mu F$
6.3V	$\leq 20\%$	-	-

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Capacitance Range

NP0 Dielectric 0201, 0402, 0603, 0805 Sizes

Dielectric		NP0																			
Size		0201					0402					0603					0805				
Rated Voltage (V DC)		10	16	25	50	100	10	16	25	50	100	10	16	25	50	100	10	16	25	50	100
Capacitance	0.1pF (0R1)	L	L	L	L	L	N	N	N	N											
	0.2pF (0R2)	L	L	L	L	L	N	N	N	N											
	0.3pF (0R3)	L	L	L	L	L	N	N	N	N		S	S	S	S						
	0.4pF (0R4)	L	L	L	L	L	N	N	N	N		S	S	S	S						
	0.5pF (0R5)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	0.6pF (0R6)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	0.7pF (0R7)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	0.8pF (0R8)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	0.9pF (0R9)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	1.0pF (1R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	1.2pF (1R2)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	1.5pF (1R5)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	1.8pF (1R8)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	2.0pF (2R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	2.2pF (2R2)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	2.7pF (2R7)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	3.0pF (3R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	3.3pF (3R3)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	3.9pF (3R9)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	4.0pF (4R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	4.7pF (4R7)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	5.0pF (5R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	5.6pF (5R6)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	6.0pF (6R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	6.8pF (6R8)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	7.0pF (7R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	8.0pF (8R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	8.2pF (8R2)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	9.0pF (9R0)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	10pF (100)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	12pF (120)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	15pF (150)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	18pF (180)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	22pF (220)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	27pF (270)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	33pF (330)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	39pF (390)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	47pF (470)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	56pF (560)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	68pF (680)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicomp PRO

Dielectric		NP0																			
Size		0201					0402					0603					0805				
Rated Voltage (V DC)		10	16	25	50	100	10	16	25	50	100	10	16	25	50	100	10	16	25	50	100
Capacitance	82pF (820)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	100pF (101)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	120pF (121)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	150pF (151)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	180pF (181)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	220pF (221)	L	L	L	L	L	N	N	N	N	N	S	S	S	S	S	A	A	A	A	A
	270pF (271)	L	L	L			N	N	N	N		S	S	S	S	S	A	A	A	A	A
	330pF (331)	L	L	L			N	N	N	N		S	S	S	S	S	A	A	A	A	A
	390pF (391)	L	L	L			N	N	N	N		S	S	S	S	S	B	B	B	B	B
	470pF (471)	L	L	L			N	N	N	N		S	S	S	S	S	B	B	B	B	B
	560pF (561)	L	L	L			N	N	N	N		S	S	S	S	S	B	B	B	B	B
	680pF (681)	L	L	L			N	N	N	N		S	S	S	S	S	B	B	B	B	B
	820pF (821)						N	N	N	N		S	S	S	S	S	B	B	B	B	B
	1,000pF (102)						N	N	N	N		S	S	S	S	S	B	B	B	B	B
	1,200pF (122)											X	X	X	X	X	B	B	B	B	B
	1,500pF (152)											X	X	X	X	X	B	B	B	B	B
	1,800pF (182)											X	X	X	X	X	B	B	B	B	B
	2,200pF (222)											X	X	X	X	X	B	B	B	B	B
	2,700pF (272)											X	X	X	X	X	D	D	D	D	D
	3,300pF (332)											X	X	X	X	X	D	D	D	D	D
	3,900pF (392)											X	X	X	X	X	D	D	D	D	D
	4,700pF (472)											X	X	X	X	X	D	D	D	D	D
	5,600pF (562)											X	X	X	X	X	D	D	D	D	D
	6,800pF (682)											X	X	X	X	X	D	D	D	D	D
	8,200pF (822)											X	X	X	X	X	D	D	D	D	D
	0.010μF (103)											X	X	X	X	X	D	D	D	D	D
	0.012μF (123)																D	D	D	D	D
	0.015μF (153)																D	D	D	D	D
	0.018μF (183)																D	D	D	D	D
	0.022μF (223)																D	D	D	D	D

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with “ * ” mark is expressed capacitance tolerance “J” (±5%) only.

NP0 Dielectric 1206, 1210, 1812 Sizes

Dielectric		NP0													
Size		1206					1210					1812			
Rated Voltage (V DC)		10	16	25	50	100	10	16	25	50	100	16	25	50	100
Capacitance	1.0pF (1R0)														
	1.2pF (1R2)	B	B	B	B	B									
	1.5pF (1R5)	B	B	B	B	B									
	1.8pF (1R8)	B	B	B	B	B									

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicomp PRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Dielectric		NP0													
Size		1206					1210					1812			
Rated Voltage (V DC)		10	16	25	50	100	10	16	25	50	100	16	25	50	100
Capacitance	2.2pF (2R2)	B	B	B	B	B									
	2.7pF (2R7)	B	B	B	B	B									
	3.3pF (3R3)	B	B	B	B	B									
	3.9pF (3R9)	B	B	B	B	B									
	4.7pF (4R7)	B	B	B	B	B									
	5.6pF (5R6)	B	B	B	B	B									
	6.8pF (6R8)	B	B	B	B	B									
	8.2pF (8R2)	B	B	B	B	B									
	10pF (100)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	12pF (120)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	15pF (150)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	18pF (180)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	22pF (220)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	27pF (270)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	33pF (330)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	39pF (390)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	47pF (470)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	56pF (560)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	68pF (680)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	82pF (820)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	100pF (101)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	120pF (121)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	150pF (151)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	180pF (181)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	220pF (221)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	270pF (271)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	330pF (331)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	390pF (391)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	470pF (471)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	560pF (561)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	680pF (681)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	820pF (821)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	1,000pF (102)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	1,200pF (122)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	1,500pF (152)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	1,800pF (182)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	2,200pF (222)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	2,700pF (272)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	3,300pF (332)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	3,900pF (392)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	4,700pF (472)	B	B	B	B	B	C	C	C	C	C	D	D	D	D

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Dielectric		NP0													
Size		1206					1210					1812			
Rated Voltage (V DC)		10	16	25	50	100	10	16	25	50	100	16	25	50	100
Capacitance	5,600pF (562)	B	B	B	B	B	C	C	C	C	C	D	D	D	D
	6,800pF (682)	C	C	C	C	C	C	C	C	C	C	D	D	D	D
	8,200pF (822)	D	D	D	D	D	C	C	C	C	C	D	D	D	D
	0.010μF (103)	D	D	D	D	D	C	C	C	C	C	D	D	D	D
	0.012μF (123)	P	P	P	P	P	D	D	D	D	D	D	D	D	D
	0.015μF (153)	P	P	P	P	P	D	D	D	D	D	D	D	D	D
	0.018μF (183)	P	P	P	P	P	K	K	K	K	K	D	D	D	D
	0.022μF (223)	P	P	P	P	P	K	K	K	K	K	D	D	D	D
	0.027μF (273)	P	P	P	P		K	K	K	K	K	D	D	D	D
	0.033μF (333)	P	P	P	P		K	K	K	K	K	D	D	D	D
	0.039μF (393)	P	P	P	P		K	K	K	K	K	M	M	M	M
	0.047μF (473)	P	P	P	P		K	K	K	K	K	M	M	M	M
	0.056μF (563)	P	P	P	P							M	M	M	M
	0.068μF (683)	P	P	P	P							M	M	M	M
	0.082μF (823)	P	P	P	P							M	M	M	M
	0.1μF (104)	P	P	P	P							M	M	M	M

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with " * " mark is expressed capacitance tolerance "J" (±5%) only.

X7R Dielectric 0201, 0402, 0603, 0805 Sizes

Dielectric		X7R																							
Size		0201					0402						0603						0805						
Rated Voltage (V DC)		6.3	10	16	25	50	6.3	10	16	25	50	100	6.3	10	16	25	50	100	6.3	10	16	25	35	50	100
Capacitance	100pF (101)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	120pF (121)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	150pF (151)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	180pF (181)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	220pF (221)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	270pF (271)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	330pF (331)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	390pF (391)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	470pF (471)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	560pF (561)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	680pF (681)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	820pF (821)			L	L	L		N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	1,000pF (102)	L	L	L	L	L	N	N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	1,200pF (122)	L	L	L	L			N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	1,500pF (152)	L	L	L	L			N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	1,800pF (182)	L	L	L				N	N	N	N	N		S	S	S	S	S		B	B	B		B	B
	2,200pF (222)	L	L	L				N	N	N	N	N		S	S	S	S	S		B	B	B		B	B

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Dielectric		X7R																											
Size		0201					0402						0603						0805										
Rated Voltage (V DC)		6.3	10	16	25	50	6.3	10	16	25	50	100	6.3	10	16	25	50	100	6.3	10	16	25	35	50	100				
Capacitance	2,700pF (272)	L	L	L				N	N	N	N	N		S	S	S	S	S		B	B	B		B	B				
	3,300pF (332)	L	L	L				N	N	N	N	N		S	S	S	S	S		B	B	B		B	B				
	3,900pF (392)	L	L	L				N	N	N	N	N		S	S	S	S	S		B	B	B		B	B				
	4,700pF (472)	L	L	L			N	N	N	N	N	N		S	S	S	S	S		B	B	B		B	B				
	5,600pF (562)	L	L					N	N	N	N			S	S	S	S	S		B	B	B		B	B				
	6,800pF (682)	L	L					N	N	N	N			S	S	S	S	S		B	B	B		B	B				
	8,200pF (822)	L	L					N	N	N	N			S	S	S	S	S		B	B	B		B	B				
	0.010μF (103)	L	L	L			N	N	N	N	N			S	S	S	S	S		B	B	B		B	B				
	0.012μF (123)							N	N	N	N			S	S	S	S	X		B	B	B		B	B				
	0.015μF (153)							N	N	N	N			S	S	S	S	X		B	B	B		B	B				
	0.018μF (183)							N	N	N	N			S	S	S	S	X		B	B	B		B	B				
	0.022μF (223)						N	N	N	N	N			S	S	S	S	X		B	B	B		B	B				
	0.027μF (273)							N	N	N	N			S	S	S	S	X		B	B	B		B	D				
	0.033μF (333)							N	N	N	N			S	S	S	X	X		B	B	B		B	D				
	0.039μF (393)							N	N	N	N			S	S	S	X	X		B	B	B		B	D				
	0.047μF (473)							N	N	N	N			S	S	S	X	X		B	B	B		B	D				
	0.056μF (563)							N	N		E			S	S	S	X	X		B	B	B		B	D				
	0.068μF (683)							N	N		E			S	S	S	X	X		B	B	B		B	D				
	0.082μF (823)							N	N		E			S	S	S	X	X		B	B	B		B	D				
	0.10μF (104)						N	N	N	N	E			S	S	S	X	X		B	B	B		B	D				
	0.12μF (124)													S	S	X				B	B	B		B	I				
	0.15μF (154)								N					S	S	X	X			D	D	D		D	I				
	0.18μF (184)													S	S	X				D	D	D		D	I				
	0.22μF (224)						N	N	N	N				S	S	X	X			D	D	D		D	I				
	0.27μF (274)													X	X	X	X			D	D	D		I	I				
	0.33μF (334)						N	N						X	X	X	X	X		D	D	D		I	I				
	0.39μF (394)													X	X	X	X			D	D	D		I	I				
	0.47μF (474)						N	N						X	X	X	X	X		D	D	D		I	I				
	0.56μF (564)													X	X	X				D	D	D							
	0.68μF (684)													X	X	X				D	D	D		I					
	0.82μF (824)													X	X	X				D	D	D							
	1.0μF (105)						N							X	X	X	X	X		D	D	D	I	I					
	1.5μF (155)																			I	I	I							
	2.2μF (225)													X	X	X				I	I	I	I	I	I				
	3.3μF (335)																												
	4.7μF (475)													X	X					I	I	I	I						
	6.8μF (685)																												
	10μF (106)																			I	I	I*							
	22μF (226)																												

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with “*” mark is expressed product not in 10% (code “K”) tolerance.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

X7R Dielectric 1206, 1210, 1812 Sizes

Dielectric		X7R																		
Size		1206						1210						1812						
Rated Voltage (V DC)		6.3	10	16	25	35	50	100	6.3	10	16	25	35	50	100	10	16	25	50	100
Capacitance	100pF (101)																			
	120pF (121)																			
	150pF (151)		B	B	B		B	B												
	180pF (181)		B	B	B		B	B												
	220pF (221)		B	B	B		B	B												
	270pF (271)		B	B	B		B	B												
	330pF (331)		B	B	B		B	B												
	390pF (391)		B	B	B		B	B												
	470pF (471)		B	B	B		B	B												
	560pF (561)		B	B	B		B	B												
	680pF (681)		B	B	B		B	B												
	820pF (821)		B	B	B		B	B												
	1,000pF (102)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	1,200pF (122)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	1,500pF (152)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	1,800pF (182)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	2,200pF (222)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	2,700pF (272)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	3,300pF (332)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	3,900pF (392)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	4,700pF (472)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	5,600pF (562)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	6,800pF (682)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	8,200pF (822)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.010μF (103)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.012μF (123)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.015μF (153)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.018μF (183)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.022μF (223)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.027μF (273)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.033μF (333)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.039μF (393)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.047μF (473)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.056μF (563)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.068μF (683)		B	B	B		B	B		C	C	C			C	C	D	D	D	D
	0.082μF (823)		B	B	B		B	D		C	C	C			C	C	D	D	D	D
0.10μF (104)		B	B	B		B	C		C	C	C			C	C	D	D	D	D	
0.12μF (124)		B	B	B		B	D		C	C	C			C	C	D	D	D	D	
0.15μF (154)		C	C	C		C	G		C	C	C			C	D	D	D	D	D	
0.18μF (184)		C	C	C		C	G		C	C	C			C	D	D	D	D	D	

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Dielectric		X7R																		
Size		1206						1210						1812						
Rated Voltage (V DC)		6.3	10	16	25	35	50	100	6.3	10	16	25	35	50	100	10	16	25	50	100
Capacitance	0.22μF (224)		C	C	C		C	G		C	C	C		C	D	D	D	D	D	
	0.27μF (274)		C	C	C		D	G		C	C	C		C	G	D	D	D	D	
	0.33μF (334)		C	C	C		D	G		C	C	C		D	G	D	D	D	D	
	0.39μF (394)		C	C	J		P	G		C	C	C		D	M	D	D	D	D	
	0.47μF (474)		J	J	J		P	G		C	C	C		D	M	D	D	D	K	
	0.56μF (564)		J	J	J		P	P		D	D	D		D	M	D	D	D	K	
	0.68μF (684)		J	J	J		P	P		D	D	D		D	K	D	D	D	K	
	0.82μF (824)		J	J	J		P	P		D	D	D		D	K	D	D	D	K	
	1.0μF (105)		J	J	J		P	P		D	D	D		D	K	D	D	D	K	
	1.5μF (155)		J	J	P		P			G	G			M	M	D	D	D	K	
	2.2μF (225)		J	J	P		P	p		G	G			M	M	G	G	G	M	
	3.3μF (335)		P	P	P		P			G	G			M		K	K	K	K	
	4.7μF (475)		P	P	P		P			K	K	K		M	M	M	M	M	M	
	6.8μF (685)															M	M	M	M	
	10μF (106)	P	P	P	P	P				K	K	K	K	M	M		M	M	M	M
	22μF (226)	P	P	P*							M	M	M				M	M	M	
	47μF (476)									M	M									
100μF (107)																				

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with " * " mark is expressed product not in 10% (code "K") tolerance.

Y5V Dielectric 0402, 0603, 0805 Sizes

Dielectric		Y5V															
Size		0402					0603					0805					
Rated Voltage (VDC)		6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50	100
Capacitance	0.01μF (103)		N	N	N	N		S	S	S	S		A	A	A	A	B
	0.015μF (153)		N	N	N	N		S	S	S	S		A	A	A	A	B
	0.022μF (223)		N	N	N	N		S	S	S	S		A	A	A	A	B
	0.033μF (333)		N	N	N	N		S	S	S	S		A	A	A	A	B
	0.047μF (473)		N	N	N			S	S	S	S		A	A	A	A	B
	0.068μF (683)		N	N	N			S	S	S	S		A	A	A	A	B
	0.10μF (104)		N	N	N			S	S	S	S		A	A	A	A	B
	0.15μF (154)		N	N				S	S	S	S		A	A	A	A	
	0.22μF (224)	N	N	N				S	S	S	S		A	A	A	A	
	0.33μF (334)	N	N	N				S	S	S	X		B	B	B	B	
	0.47μF (474)	N	N	N				S	S	X	X		B	B	B	B	
	0.68μF (684)	N						S	X	X			B	B	D	D	
	1.0μF (105)	N	N					S	X	X			B	B	D	D	
	1.5μF (155)							S					D	D			
	2.2μF (225)						S	S	X				D	D	I		

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

multicompPRO

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicomp PRO

Dielectric		Y5V															
Size		0402					0603					0805					
Rated Voltage (VDC)		6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50	100
Capacitance	3.3μF (335)												D	D			
	4.7μF (475)						X	X					D	D	I		
	6.8μF (685)												I				
	10μF (106)											I	I	I			
	22μF (226)											I	I				

1. The letter in cell is expressed the symbol of product thickness.

Y5V Dielectric 1206, 1210, 1812 Sizes

Dielectric		Y5V																	
Size		1206						1210						1812					
Rated Voltage (VDC)		6.3	10	16	25	50	100	6.3	10	16	25	35	50	100	10	16	25	50	100
Capacitance	0.010μF (103)		B	B	B	B	B							C					D
	0.015μF (153)		B	B	B	B	B							C					D
	0.022μF (223)		B	B	B	B	B							C					D
	0.033μF (333)		B	B	B	B	B							C					D
	0.047μF (473)		B	B	B	B	B							C					D
	0.068μF (683)		B	B	B	B	B							C					D
	0.10μF (104)		B	B	B	B	B		C	C	C		C	C	D	D	D	D	D
	0.15μF (154)		B	B	B	B	C		C	C	C		C	C	D	D	D	D	D
	0.22μF (224)		B	B	B	B	C		C	C	C		C	C	D	D	D	D	D
	0.33μF (334)		B	B	B	B			C	C	C		C	C	D	D	D	D	D
	0.47μF (474)		B	B	B	B			C	C	C		C		D	D	D	D	D
	0.68μF (684)		B	B	B	B			C	C	C		C		D	D	D	D	D
	1.0μF (105)		C	C	C	C			C	C	C		C		D	D	D	D	D
	1.5μF (155)		C	C	C				C	C	C				D	D	D	D	
	2.2μF (225)		C	C	C	J			C	C	C		G		D	D	D	D	
	3.3μF (335)		J	J	J				C	C	C				D	D	D	D	
	4.7μF (475)		J	J	J	P			C	C	D		G		D	D	D	D	
	6.8μF (685)		J	J					C	C	D		K		D	D	D	D	
	10μF (106)		J	J	P				D	D	G	K	K		D	D	D	K	
22μF (226)		P	P					K	K										
47μF (476)	P						K	K							M				
100μF (107)							M												

1. The letter in cell is expressed the symbol of product thickness.

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicomp PRO

X5R Dielectric 0201, 0402, 0603, 0805, 1206, 1210 Sizes

Dielectric		X5R																		
Size		0201					0402							0603						
Rated Voltage (V DC)		6.3	10	16	25	50	4	6.3	10	16	25	50	63	4	6.3	10	16	25	35	50
Capacitance	100pF (101)			L	L	L														
	150pF (151)			L	L	L														
	220pF (221)			L	L	L														
	330pF (331)			L	L	L														
	470pF (471)			L	L	L														
	680pF (681)			L	L	L														
	820pF (821)			L	L	L														
	1,000pF (102)		L	L	L	L														
	1,500pF (152)		L	L	L															
	2,200pF (222)		L	L	L															
	2,700pF (272)		L	L	L															
	3,300pF (332)		L	L	L															
	4,700pF (472)		L	L	L															
	6,800pF (682)		L	L	L															
	0.010μF (103)	L	L	L	L	L														
	0.015μF (153)	L	L									N								
	0.022μF (223)	L	L	L	L						N	N								
	0.033μF (333)	L	L							N		N								
	0.047μF (473)	L	L	L	L			N	N	N		N								
	0.068μF (683)	L	L					N	N	N		E								
	0.082μF (823)	L	L					N	N	N		E								
	0.10μF (104)	L	L	L	L			N	N	N	N	E								
	0.15μF (154)							N	N	N	N									
	0.22μF (224)	L	L	L	L			N	N	N	N	N	N		X	X	X	X		
	0.33μF (334)	L	L	L	L			N	N	N	N				X	X	X	X		
	0.47μF (474)	L	L					N	N	N	N				X	X	X	X		X
	0.68μF (684)							N	N						X	X	X	X		
	0.82uF (824)														X	X	X	X		
	1.0μF (105)	L	L*	L*				N	N	N	N	E			X	X	X	X	X	X
	1.5μF (155)														X	X				
	2.2μF (225)	L*	L*					N	N	E	E				X	X	X	X		X
	3.3μF (335)														X	X				
	4.7μF (475)							E	E	E*					X	X	X	X		
	6.8uF (685)																			
	10μF (106)						E*	E*	E*						X	X	X	X	X	
	22μF (226)						E*	E*							X*	X*	X*			
	47μF (476)														X*	X*				

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicompPRO

Dielectric		X5R																				
Size		0805						1206							1210							
Rated Voltage (V DC)		4	6.3	10	16	25	50	4	6.3	10	16	25	50	63	4	6.3	10	16	25	35	50	
Capacitance	1.0μF (105)			D	D	D	I						P									
	1.5μF (155)		I	I	I	I				J	J	P	P				K	K				
	2.2μF (225)		I	I	I	I	I			J	J	P	P				K	K				
	3.3μF (335)		I	I	I	I				P	P	P	P									
	4.7μF (475)		I	I	I	I	I		P	P	P	P	P				K	K	K			
	6.8uF (685)								P	P												
	10μF (106)		I	I	I	I	I		P	P	P	P	P				K	K	K	K	M	M
	22μF (226)		I	I*	I*	I*			P	P	P	P					M	M	M	M	M	
	47μF (476)	I*	I*	I*					P*	P*	P*						M	M	M	M*		
	100μF (107)	I*	I*						P								M*	M*	M*			
	220μF (227)								P*	P*						M*	M*					

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with " * " mark is expressed product not in 10% (code "K") tolerance.

X6S Dielectric 0201, 0402, 0603, 0805, 1206, 1210 Sizes

Dielectric		X6S												
Size		0201				0402				0603				
Rated Voltage (VDC)		6.3	10	16	25	6.3	10	16	25	4	6.3	10	16	25
Capacitance	0.10μF (104)	L	L	L	L									
	0.15μF (154)													
	0.22μF (224)	L	L*											
	0.33μF (334)													
	0.47μF (474)					E								
	0.68μF (684)													
	1.0μF (105)	L*				E	E	E	E					
	1.5μF (155)													
	2.2μF (225)					E	E	E					X	X
	3.3μF (335)													
	4.7μF (475)										X	X	X	X
	6.8uF (685)													
	10μF (106)					E*					X*	X*	X*	
	22μF (226)									X*	X*			
	47μF (476)													
	100μF (107)													

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicomp PRO

Dielectric		X6S																
Size		0805					1206					1210						
Rated Voltage (VDC)		4	6.3	10	16	25	50	6.3	10	16	25	50	6.3	10	16	25	50	
Capacitance	0.10μF (104)																	
	0.15μF (154)																	
	0.22μF (224)																	
	0.33μF (334)																	
	0.47μF (474)																	
	0.68μF (684)																	
	1.0μF (105)																	
	1.5μF (155)																	
	2.2μF (225)																	
	3.3μF (335)																	
	4.7μF (475)					I	I											
	6.8uF (685)																	
	10μF (106)	I	I	I	I	I					P							
	22μF (226)		I*	I*	I*				P	P*	P						M	
	47μF (476)	I*	I*					P					M	M	M			
	100μF (107)												M*	M*				

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with " * " mark is expressed product not in 10% (code "K") tolerance.

X7S Dielectric 0402, 0603, 0805, 1206, 1210 Sizes

Dielectric		X7S																					
Size		0402			0603				0805					1206					1210				
Rated Voltage (VDC)		6.3	10	16	6.3	10	16	25	10	16	25	50	100	6.3	10	16	25	50	6.3	10	16	25	50
Capacitance	1.0μF (105)		E										I										
	1.5μF (155)																						
	2.2μF (225)	E	E				X	X															
	3.3μF (335)																						
	4.7μF (475)					X	X					I											
	6.8uF (685)																						
	10μF (106)									I	I												
	22μF (226)															P*							
	47μF (476)													P*									
	100μF (107)																		P*				

1. The letter in cell is expressed the symbol of product thickness.
2. The letter in cell with " * " mark is expressed product not in 10% (code "K") tolerance.

Packaging Dimension and Quantity

Size	Thickness (mm)/Symbol		Paper tape		Plastic tape	
			7" reel	13" reel	7" reel	13" reel
0201 (0603)	0.3 ±0.03	L	15,000	70,000	-	-
	0.3 ±0.05	L	15,000	50,000	-	-
	0.3 ±0.09	L	15,000	50,000	-	-
0603 (1608)	0.5 ±0.05	N	10,000	50,000	-	-
	0.5 +0.02/-0.05	Q	10,000	50,000	-	-
	0.5 ±0.20	E	10,000	-	-	-
0805 (2012)	0.5 ±0.10	H	4,000	-	-	-
	0.8 ±0.07	S	4,000	15,000	-	-
	0.8 +0.15/-0.10	X	4,000	15,000	-	-
0805 (2012)	0.5 ±0.10	H	4,000	15,000	-	-
	0.6 ±0.10	A	4,000	15,000	-	-
	0.8 ±0.10	B	4,000	15,000	-	-
	0.85±0.10	T	4,000	15,000	-	-
	1.25±0.10	D	-	-	3,000	10,000
	1.25±0.20	I	-	-	3,000	10,000
1206 (3216)	0.8 ±0.10	B	4,000	15,000	-	-
	0.85±0.10	T	4,000	15,000	-	-
	0.95±0.10	C	-	-	3,000	10,000
	1.15±0.15	J	-	-	3,000	10,000
	1.25±0.10	D	-	-	3,000	10,000
	1.6 ±0.20	G	-	-	2,000	10,000
	1.6 +0.30/-0.10	P	-	-	2,000	9,000
1210 (3225)	0.85 ±0.10	T	-	-	3,000	10,000
	0.95 ±0.10	C	-	-	3,000	10,000
	1.25 ±0.10	D	-	-	3,000	10,000
	1.6 ±0.20	G	-	-	2,000	-
	2 ±0.20	K	-	-	1,000	6,000
	2.5 ±0.30	M	-	-	1,000	6,000
1808 (4520)	1.25 ±0.10	D	-	-	2,000	10,000
	1.4 ±0.15	F	-	-	2,000	10,000
	1.6 ±0.20	G	-	-	2,000	8,000
	2 ±0.20	K	-	-	1,000	6,000
1812 (4532)	1.25±0.10	D	-	-	1,000	5,000
	1.6 ±0.20	G	-	-	1,000	-
	2 ±0.20	K	-	-	1,000	-
	2.5 ±0.30	M	-	-	500	3,000
	2.8 ±0.30	U	-	-	500	-

Unit : pieces

Reliability Test Conditions And Requirements:

No	Item	Test Condition	Requirements																																				
1	Visual and Mechanical	-	No remarkable defect. Dimensions to conForm to individual specification sheet.																																				
2	Capacitance		*Shall not exceed the limits given in the detailed spec. NP0: Cap≥30pF, Q≥1000; Cap<30pF,Q≥400+20C X7R:																																				
3	Q/ D.F. (Dissipation Factor)	*Test temp.: Room Temperature. *Class I: (NP0) ≤1000pF, 1.0±0.2Vrms,1MHz±10% >1000pF, 1.0±0.2Vrms,1kHz±10% Class II: (X7R, X7E, X6S, X5R,X7S) C≤10μF, 1.0±0.2Vrms; 1kHz±10% ** C>10μF, 0.5±0.2Vrms; 120Hz±20% ** Test condition: 0.5±0.2Vrms; 1kHz±10% X7R: 0603/475(6.3V) X5R #1 : 0201≥224 (6.3V,10V,16V), 0402≥475 (6.3V,16V), 0402≥225(10V), 0603=106 (6.3V) TT18X≥475(10V) , TT15X series	<table><tr><th>Rated vol.</th><th>D.F. ≡</th><th colspan="2">Exception of D.F. ≡</th></tr><tr><td rowspan="3">≧100V</td><td rowspan="3">≧2.5%</td><td>≧3%</td><td>1206≧0.47μF</td></tr><tr><td>≧3.5%</td><td>1812≧4.7μF;1825≧4.7μF;2220≧4.7μF;2225≧4.7μF</td></tr><tr><td>≧5%</td><td>0805>0.1μF, 0603≧0.068μF, 1206>1μF;</td></tr><tr><td rowspan="4">≧50V</td><td rowspan="4">≧2.5%</td><td>≧3%</td><td>0201(50V); 0603≧0.047μF; 0805≧0.18μF;1206≧0.47μF</td></tr><tr><td>≧3.5%</td><td>1812≧4.7μF;1825≧4.7μF;2220≧4.7μF;2225≧4.7μF</td></tr><tr><td>≧5%</td><td>0201≧0.01μF; 0402≧0.012μF; 1210≧3.3μF</td></tr><tr><td>≧10%</td><td>0402≧0.1μF; 0603≧1μF; 0805≧1μF; 1206≧4.7μF; 1210≧10μF</td></tr><tr><td>35V</td><td>≧3.5%</td><td>≧10%</td><td>0603≧1μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧10μF</td></tr><tr><td rowspan="4">25V</td><td rowspan="4">≧3.5%</td><td>≧5%</td><td>0201≧0.01μF;0805≧1μF; 1210≧10μF</td></tr><tr><td>≧7%</td><td>0603≧0.33μF; 1206≧4.7μF</td></tr><tr><td>≧10%</td><td>0402≧0.10μF;0603≧0.47μF;0805≧2.2μF; 1206≧6.8μF ; 1210≧22μF;</td></tr><tr><td>≧12.5%</td><td>0402≧0.33μF</td></tr></table>	Rated vol.	D.F. ≡	Exception of D.F. ≡		≧100V	≧2.5%	≧3%	1206≧0.47μF	≧3.5%	1812≧4.7μF;1825≧4.7μF;2220≧4.7μF;2225≧4.7μF	≧5%	0805>0.1μF, 0603≧0.068μF, 1206>1μF;	≧50V	≧2.5%	≧3%	0201(50V); 0603≧0.047μF; 0805≧0.18μF;1206≧0.47μF	≧3.5%	1812≧4.7μF;1825≧4.7μF;2220≧4.7μF;2225≧4.7μF	≧5%	0201≧0.01μF; 0402≧0.012μF; 1210≧3.3μF	≧10%	0402≧0.1μF; 0603≧1μF; 0805≧1μF; 1206≧4.7μF; 1210≧10μF	35V	≧3.5%	≧10%	0603≧1μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧10μF	25V	≧3.5%	≧5%	0201≧0.01μF;0805≧1μF; 1210≧10μF	≧7%	0603≧0.33μF; 1206≧4.7μF	≧10%	0402≧0.10μF;0603≧0.47μF;0805≧2.2μF; 1206≧6.8μF ; 1210≧22μF;	≧12.5%	0402≧0.33μF
			Rated vol.	D.F. ≡	Exception of D.F. ≡																																		
≧100V	≧2.5%	≧3%	1206≧0.47μF																																				
		≧3.5%	1812≧4.7μF;1825≧4.7μF;2220≧4.7μF;2225≧4.7μF																																				
		≧5%	0805>0.1μF, 0603≧0.068μF, 1206>1μF;																																				
≧50V	≧2.5%	≧3%	0201(50V); 0603≧0.047μF; 0805≧0.18μF;1206≧0.47μF																																				
		≧3.5%	1812≧4.7μF;1825≧4.7μF;2220≧4.7μF;2225≧4.7μF																																				
		≧5%	0201≧0.01μF; 0402≧0.012μF; 1210≧3.3μF																																				
		≧10%	0402≧0.1μF; 0603≧1μF; 0805≧1μF; 1206≧4.7μF; 1210≧10μF																																				
35V	≧3.5%	≧10%	0603≧1μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧10μF																																				
25V	≧3.5%	≧5%	0201≧0.01μF;0805≧1μF; 1210≧10μF																																				
		≧7%	0603≧0.33μF; 1206≧4.7μF																																				
		≧10%	0402≧0.10μF;0603≧0.47μF;0805≧2.2μF; 1206≧6.8μF ; 1210≧22μF;																																				
		≧12.5%	0402≧0.33μF																																				
<table><tr><th>Rated vol.</th><th>D.F. ≡</th><th colspan="2">Exception of D.F. ≡</th></tr><tr><td rowspan="2">16V</td><td rowspan="2">≧3.5%</td><td>≧5%</td><td>0201≧0.01μF; 0402≧0.033μF; 0603≧0.15μF; 0805≧0.68μF; 1206≧2.2μF; 1210≧4.7μF</td></tr><tr><td>≧10%</td><td>0201/X7R≧0.022μF; 0402≧0.15uF; 0603>0.47μF; 0805≧2.2μF; 1206≧4.7μF; 1210≧22μF</td></tr><tr><td rowspan="2">10V</td><td rowspan="2">≧5%</td><td>≧10%</td><td>0201≧0.012μF; 0402≧0.15μF; 0603≧0.33μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧22μF</td></tr><tr><td>≧15%</td><td>0201≧0.1μF; 0402≧1μF</td></tr><tr><td rowspan="2">6.3V</td><td rowspan="2">≧10%</td><td>≧15%</td><td>0201≧0.1μF;0402≧1μF;0603≧10μF; 0805≧4.7μF; 1206≧47μF ;1210≧100μF;</td></tr><tr><td>≧20%</td><td>0402≧2.2μF</td></tr><tr><td>4V</td><td>≧15%</td><td>-</td><td>-</td></tr></table>	Rated vol.	D.F. ≡	Exception of D.F. ≡		16V	≧3.5%	≧5%	0201≧0.01μF; 0402≧0.033μF; 0603≧0.15μF; 0805≧0.68μF; 1206≧2.2μF; 1210≧4.7μF	≧10%	0201/X7R≧0.022μF; 0402≧0.15uF; 0603>0.47μF; 0805≧2.2μF; 1206≧4.7μF; 1210≧22μF	10V	≧5%	≧10%	0201≧0.012μF; 0402≧0.15μF; 0603≧0.33μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧22μF	≧15%	0201≧0.1μF; 0402≧1μF	6.3V	≧10%	≧15%	0201≧0.1μF;0402≧1μF;0603≧10μF; 0805≧4.7μF; 1206≧47μF ;1210≧100μF;	≧20%	0402≧2.2μF	4V	≧15%	-	-													
Rated vol.	D.F. ≡	Exception of D.F. ≡																																					
16V	≧3.5%	≧5%	0201≧0.01μF; 0402≧0.033μF; 0603≧0.15μF; 0805≧0.68μF; 1206≧2.2μF; 1210≧4.7μF																																				
		≧10%	0201/X7R≧0.022μF; 0402≧0.15uF; 0603>0.47μF; 0805≧2.2μF; 1206≧4.7μF; 1210≧22μF																																				
10V	≧5%	≧10%	0201≧0.012μF; 0402≧0.15μF; 0603≧0.33μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧22μF																																				
		≧15%	0201≧0.1μF; 0402≧1μF																																				
6.3V	≧10%	≧15%	0201≧0.1μF;0402≧1μF;0603≧10μF; 0805≧4.7μF; 1206≧47μF ;1210≧100μF;																																				
		≧20%	0402≧2.2μF																																				
4V	≧15%	-	-																																				

No	Item	Test Condition	Requirements			
			X5R:			
			Rated vol.	D.F. ≤	Exception of D.F. ≤	
					≤3%	1206≥0.47μF
			≥100V	≤2.5%	≤5%	0603≥0.068μF; 0805≥0.1μF; 1206≥1μF; 1210≥2.2μF
					≤10%	0805>0.22μF; 1210≥3.3μF
			≥50V	≤2.5%	≤3%	0201(50V); 0603≥0.047μF; 0805≥0.18μF; 1206≥0.47μF
					≤5%	0201≥0.01μF; 0402≥0.012μF; 1210≥3.3μF
					≤10%	0402≥0.047μF; 0603>0.1μF; 0805≥1μF; 1206≥2.2μF; 1210≥10μF
					≤12.5%	1206=10μF
			35V	≤3.5%	≤10%	0603≥1μF; 0805≥2.2μF; 1206≥2.2μF; 1210≥10μF
			25V	≤3.5%	≤5%	0201=0.01μF; 0805≥1μF
					≤7%	0603≥0.33μF
					≤10%	0201>0.01μF; 0402≥0.10μF; 0603≥0.47μF; 0805≥2.2μF; 1206≥4.7μF; 1210≥10μF
					≤12.5%	0402≥0.33μF; 0805=10μF
			16V	≤3.5%	≤5%	0201=0.01μF; 0402≥0.033μF; 0603≥0.15μF; 0805≥0.68μF; 1206≥2.2μF; 1210≥4.7μF
					≤10%	0201>0.01μF; 0402≥0.22μF; 0603>0.47μF; 0805≥2.2μF; 1206≥4.7μF; 1210≥22μF
					≤12.5%	0402≥1μF; 0805=10μF
			10V	≤5%	≤10%	0201≥0.012μF; 0402≥0.22μF; 0603≥0.33μF; 0805≥2.2μF; 1206≥2.2μF; 1210≥22μF; 01R5/X5R
					≤12.5%	0805=10μF
					≤15%	0201>0.1μF; 0402≥1μF; 0603≥10μF
			6.3V	≤10%	≤15%	0201>0.1μF; 0402≥1μF; 0603≥10μF; 0805≥4.7μF; 1206≥47μF; 1210≥100μF
					≤20%	0402≥2.2μF
			4V	≤15%	-	-
		X6S: 0201/474(4V), 0201>104 (6.3V, 10V), 0402≥225 (6.3V), 0402/475 (10V), 0603/106 (6.3V), X7S: 0402/225(6.3V) #1 Excluding X5R/0201/105(6.3V); 225(10V); 224 (16V), 0402X475M6R3, 0402X106M100 (1.0±0.2Vrms, 1kHz±10%) *Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp.				
	Q/ D.F. (Dissipation Factor)					

No	Item	Test Condition	Requirements			
Q/ D.F. (Dissipation Factor)			X6S:			
			Rated vol.	D.F. ≤	Exception of D.F. ≤	
			≥100V	≤2.5%	≤3%	1206≥0.47μF
					≤5%	0603≥0.068μF; 0805≥0.1μF; 1206≥1μF; 1210≥2.2μF
					≤10%	0805>0.22μF; 1210≥3.3μF
			≥50V	≤2.5%	≤3%	0201(50V); 0603≥0.047μF; 0805≥0.18μF; 1206≥0.47μF
					≤5%	0201≥0.01μF; 1210≥3.3μF
					≤10%	0402≥0.012μF; 0603>0.1μF; 0805≥1μF; 1206≥2.2μF; 1210≥10μF
			35V	≤3.5%	≤10%	0603≥1μF; 0805≥2.2μF; 1206≥2.2μF; 1210≥10μF
			25V	≤3.5%	≤5%	0201≥0.01μF; 0805≥1μF; 1210≥10μF
					≤7%	0603≥0.33μF
					≤10%	0201≥0.1μF; 0402≥0.10μF; 0603≥0.47μF; 0805≥2.2μF; 1206≥4.7μF; 1210≥22μF
					≤12.5%	0402≥0.33μF; 0805=10μF
			16V	≤3.5%	≤5%	0201=0.01μF; 0402≥0.033μF; 0603≥0.15μF; 0805≥0.68μF; 1206≥2.2μF; 1210≥4.7μF
					≤10%	0201>0.01μF; 0402≥0.22μF; 0603>0.47μF; 0805≥2.2μF; 1206≥4.7μF; 1210≥22μF
					≤12.5%	0402≥1μF; 0805=10μF
			10V	≤5%	≤10%	0201≥0.012μF; 0402≥0.22μF; 0603≥0.33μF; 0805≥2.2μF; 1206≥2.2μF; 1210≥22μF
					≤12.5%	0805=10μF
					≤15%	0201>0.1μF; 0402≥1μF
			6.3V	≤10%	≤15%	0201>0.1μF; 0402≥1μF; 0603≥10μF; 0805≥4.7μF; 1206≥47μF; 1210≥100μF
					≤20%	0402≥2.2μF
			4V	≤15%	-	-
			X7S:			
			Rated vol.	D.F. ≤	Exception of D.F. ≤	
			≥100V	≤2.5%	≤3%	1206≥0.47μF
					≤5%	0603≥0.068μF; 0805≥0.1μF; 1206≥1μF; 1210≥2.2μF
					≤10%	0805>0.22μF; 1210≥3.3μF
			≥50V	≤2.5%	≤3%	0201(50V); 0603≥0.047μF; 0805≥0.18μF; 1206≥0.47μF
					≤5%	0201≥0.01μF; 1210≥3.3μF
					≤10%	0402≥0.012μF; 0603>0.1μF; 0805≥1μF; 1206≥2.2μF; 1210≥10μF
			35V	≤3.5%	≤10%	0603≥1μF; 0805≥2.2μF; 1206≥2.2μF; 1210≥10μF
			25V	≤3.5%	≤5%	0201≥0.01μF; 0805≥1μF; 1210≥10μF
					≤7%	0603≥0.33μF
					≤10%	0201≥0.1μF; 0402≥0.10μF; 0603≥0.47μF; 0805≥2.2μF; 1206≥4.7μF; 1210≥22μF
					≤12.5%	0402≥0.33μF

No	Item	Test Condition	Requirements			
	Q/ D.F. (Dissipation Factor)		Rated vol.	D.F. ≡	Exception of D.F. ≡	
			16V	≡3.5%	≡5%	0201=0.01μF; 0402≧0.033μF; 0603≧0.15μF; 0805≧0.68μF; 1206≧2.2μF; 1210≧4.7μF
					≡10%	0201>0.01uF; 0402≧ 0.22uF; 0603>0.47μF; 0805≧2.2μF; 1206≧4.7μF; 1210≧22μF
			10V	≡5%	≡10%	0201≧0.012μF; 0402≧0.22μF; 0603≧0.33μF; 0805≧2.2μF; 1206≧2.2μF; 1210≧22μF;
					≡15%	0201>0.1μF; 0402≧1μF;
			6.3V	≡10%	≡15%	0201>0.1μF; 0402≧1μF; 0603≧10μF; 0805≧4.7μF; 1206≧47μF; 1210≧100μF
≡20%	0402≧2.2μF					
4V	≡15%	-	-			
4	Dielectric Strength	* To apply voltage (≦100V) 250%. * Duration: 1 to 5 sec. * Charge and discharge current less than 50mA.	* No evidence of damage or flash over during test.			
5	Insulation Resistance	*Test temp.: Room Temperature. *To apply rated voltage for MAX. 120sec.	10GΩ or RxC ≧ 500Ω-F whichever is smaller. Class II (X7R, X7E, X5R,X6S,X7S,Y5V:)			
			Rated voltage		Insulation Resistance	
			100V: All X7R		10GΩ or RxC ≧ 100 Ω-F whichever is smaller.	
			50V:0402>0.01μF;0603≧1μF;0805≧1μF;1206≧4.7μF; 1210≧4.7μF			
			35V:0805≧2.2μF;1206 ≧ 2.2μF;1210 ≧ 10μF			
			25V:0402≧1μF;0603≧2.2μF;0805≧2.2μF;1206≧10μF; 1210≧10μF			
			16V: 0201≧0.1μF,0402≧0.22μF;0603≧1μF; 0805≧2.2μF;1206≧10μF;1210≧47μF			
			10V: 0201≧47nF;0402≧0.47μF;0603≧0.47μF; 0805≧2.2μF; 1206≧4.7μF;1210≧47μF			
			6.3V ; 4V ; Size≧1812			
			All X6S items, All X7S items		RxC≧50 Ω-F.	
			100V: 1210≧3.3μF			
			50V: 0402≧0.1μF; 0603≧2.2μF; 0805≧10μF;1206≧10μF			
			35V: 0603≧1μF;			
			25V: 0201≧0.1μF; 0402≧2.2μF;0603≧10μF; 0805≧10μF;1206≧22μF			
			16V: 0603≧10μF; 0402≧1μF; 0201≧0.22μF			
			10V: 0201>0.1μF; 0402≧1μF; 0603≧10μF; 0805≧47μF			
			6.3V:0201≧0.1μF; 0402≧1μF; 0603>4.7μF; 0805≧47μF; 1206≧10μF			
			4V: 0603≧22μF; 0805≧47μF; 1206≧100μF			

No	Item	Test Condition	Requirements																																																				
6	Temperature Coefficient	With no electrical load. <table><tr><td>T.C.</td><td>Operating Temp</td></tr><tr><td>NPO</td><td>-55~125°C at 25°C</td></tr><tr><td>X7R</td><td>-55~125°C at 25°C</td></tr><tr><td>X7S</td><td>-55 ~ 125°C at 25°C</td></tr><tr><td>X5R</td><td>-55~ 85°C at 25°C</td></tr><tr><td>X6S</td><td>-55~105°C at 25°C</td></tr></table> *Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp. * Measurement voltage for Class II:	T.C.	Operating Temp	NPO	-55~125°C at 25°C	X7R	-55~125°C at 25°C	X7S	-55 ~ 125°C at 25°C	X5R	-55~ 85°C at 25°C	X6S	-55~105°C at 25°C	<table><tr><td>T.C.</td><td>Capacitance Change</td></tr><tr><td>NPO</td><td>Within ±30ppm/°C</td></tr><tr><td>X7R</td><td>Within ±15%</td></tr><tr><td>X7S</td><td>Within ±22%</td></tr><tr><td>X5R</td><td>Within ±15%</td></tr><tr><td>X6S</td><td>Within ±22%</td></tr></table> <table><tr><th>01005</th><th>0201</th></tr><tr><td>Cap≤0.01μF: 0.5V</td><td>Cap<0.1μF:1V</td></tr><tr><td>Cap>0.01μF: 0.2V</td><td>0.1μF≤Cap<1μF: 0.2V*</td></tr><tr><td></td><td>Cap≥1μF: 0.1V*</td></tr><tr><td>*0201X104/6.3V~25V: 0.5V 0201X224/10V~25V: 0.5V</td><td>*0201B104/6.3V~10V: 0.3V 0201S104/6.3V~16V: 0.3V 0201S224/6.3V: 0.3V 0201X334/474/105-6.3V&10V: 0.3V</td></tr><tr><th>0402</th><th>0603</th></tr><tr><td>Cap<1μF: 1V</td><td>Cap<1μF: 1V</td></tr><tr><td>Cap=1μF: 0.5V** 0402B224-16V: 0.5V 0402B334/474-6.3V&10V: 0.5V 0402S334/474-6.3V: 0.5V 0402X225/475-6.3V: 0.5V</td><td>1μF≤Cap≤4.7μF: 0.5V 0603X106-10V: 0.5V</td></tr><tr><td>1μF<Cap<10μF: 0.2V **0402B105M6R3V: 0.2V</td><td>Cap>4.7μF: 0.2V</td></tr><tr><td>Cap≥10μF: 0.1V</td><td></td></tr><tr><th>0805</th><th>1206/1210</th></tr><tr><td>Cap<10μF: 1V</td><td>Cap≤10μF: 1V</td></tr><tr><td>Cap=10μF: 0.5V 0805B475/6.3V~25V: 0.5V</td><td>10μF<Cap≤100μF: 0.5V</td></tr><tr><td>Cap>10μF: 0.2V</td><td>Cap>100μF: 0.2V 1206X107-6.3V: 0.2V 1206A476-6.3V: 0.1V 1210S107-6.3V: 0.2V</td></tr></table>	T.C.	Capacitance Change	NPO	Within ±30ppm/°C	X7R	Within ±15%	X7S	Within ±22%	X5R	Within ±15%	X6S	Within ±22%	01005	0201	Cap≤0.01μF: 0.5V	Cap<0.1μF:1V	Cap>0.01μF: 0.2V	0.1μF≤Cap<1μF: 0.2V*		Cap≥1μF: 0.1V*	*0201X104/6.3V~25V: 0.5V 0201X224/10V~25V: 0.5V	*0201B104/6.3V~10V: 0.3V 0201S104/6.3V~16V: 0.3V 0201S224/6.3V: 0.3V 0201X334/474/105-6.3V&10V: 0.3V	0402	0603	Cap<1μF: 1V	Cap<1μF: 1V	Cap=1μF: 0.5V** 0402B224-16V: 0.5V 0402B334/474-6.3V&10V: 0.5V 0402S334/474-6.3V: 0.5V 0402X225/475-6.3V: 0.5V	1μF≤Cap≤4.7μF: 0.5V 0603X106-10V: 0.5V	1μF<Cap<10μF: 0.2V **0402B105M6R3V: 0.2V	Cap>4.7μF: 0.2V	Cap≥10μF: 0.1V		0805	1206/1210	Cap<10μF: 1V	Cap≤10μF: 1V	Cap=10μF: 0.5V 0805B475/6.3V~25V: 0.5V	10μF<Cap≤100μF: 0.5V	Cap>10μF: 0.2V	Cap>100μF: 0.2V 1206X107-6.3V: 0.2V 1206A476-6.3V: 0.1V 1210S107-6.3V: 0.2V
			T.C.	Operating Temp																																																			
			NPO	-55~125°C at 25°C																																																			
			X7R	-55~125°C at 25°C																																																			
			X7S	-55 ~ 125°C at 25°C																																																			
			X5R	-55~ 85°C at 25°C																																																			
			X6S	-55~105°C at 25°C																																																			
			T.C.	Capacitance Change																																																			
			NPO	Within ±30ppm/°C																																																			
			X7R	Within ±15%																																																			
X7S	Within ±22%																																																						
X5R	Within ±15%																																																						
X6S	Within ±22%																																																						
01005	0201																																																						
Cap≤0.01μF: 0.5V	Cap<0.1μF:1V																																																						
Cap>0.01μF: 0.2V	0.1μF≤Cap<1μF: 0.2V*																																																						
	Cap≥1μF: 0.1V*																																																						
*0201X104/6.3V~25V: 0.5V 0201X224/10V~25V: 0.5V	*0201B104/6.3V~10V: 0.3V 0201S104/6.3V~16V: 0.3V 0201S224/6.3V: 0.3V 0201X334/474/105-6.3V&10V: 0.3V																																																						
0402	0603																																																						
Cap<1μF: 1V	Cap<1μF: 1V																																																						
Cap=1μF: 0.5V** 0402B224-16V: 0.5V 0402B334/474-6.3V&10V: 0.5V 0402S334/474-6.3V: 0.5V 0402X225/475-6.3V: 0.5V	1μF≤Cap≤4.7μF: 0.5V 0603X106-10V: 0.5V																																																						
1μF<Cap<10μF: 0.2V **0402B105M6R3V: 0.2V	Cap>4.7μF: 0.2V																																																						
Cap≥10μF: 0.1V																																																							
0805	1206/1210																																																						
Cap<10μF: 1V	Cap≤10μF: 1V																																																						
Cap=10μF: 0.5V 0805B475/6.3V~25V: 0.5V	10μF<Cap≤100μF: 0.5V																																																						
Cap>10μF: 0.2V	Cap>100μF: 0.2V 1206X107-6.3V: 0.2V 1206A476-6.3V: 0.1V 1210S107-6.3V: 0.2V																																																						
7	Adhesive Strength of Termination	*Pressurizing force: 2N (0201) and 5N (≤0603) and 10N (>0603) * Test time: 10±1 sec.	* No remarkable damage or removal of the terminations.																																																				
8	Vibration Resistance	* Vibration frequency: 10~55 Hz/min. * Total amplitude: 1.5mm * Test time: 6 hrs. (Two hrs each in three mutually perpendicular directions.) *Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp. *Cap./DF(Q) Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp.	* No remarkable damage. * Cap change and Q/D.F.: To meet initial spec.																																																				

No	Item	Test Condition	Requirements															
9	Solderability	* Solder temperature: 235±5°C * Dipping time: 2±0.5 sec.	95% min. coverage of all metalized area.															
10	Bending Test	* The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1mm per second until the deflection becomes 1mm and then the pressure shall be maintained for 5±1 sec. *Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp. * Measurement to be made after keeping at room temp. for 24±2 hrs.	* No remarkable damage. * Cap change: NP0: within ±5% or 0.5pF whichever is larger X7R, X5R, X6S, X7S: within ±12.5% (This capacitance change means the change of capacitance under specified flexure of substrate from the capacitance measured before the test.)															
11	Resistance to Soldering Heat	* Solder temperature: 260±5°C * Dipping time: 10±1sec * Preheating: 120 to 150°C for 1 minute before immerse the capacitor in a eutectic solder. *Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp. *Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp.	* No remarkable damage. * Cap change: NP0: within ±2.5% or 0.25pF whichever is larger X7R, X5R, X6S, X7S: within ±7.5% * Q/D.F., I.R. and dielectric strength: To meet initial requirements. * 25% max. leaching on each edge.															
12	Temperature Cycle	* Conduct the five cycles according to the temperatures and time. <table><tr><th>Step</th><th>Temp. (°C)</th><th>Time (min.)</th></tr><tr><td>1</td><td>Min. operating temp. +0/-3</td><td>30±3</td></tr><tr><td>2</td><td>Room temp.</td><td>2~3</td></tr><tr><td>3</td><td>Max. operating temp. +3/-0</td><td>30±3</td></tr><tr><td>4</td><td>Room temp.</td><td>2~3</td></tr></table> *Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp. * Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp.	Step	Temp. (°C)	Time (min.)	1	Min. operating temp. +0/-3	30±3	2	Room temp.	2~3	3	Max. operating temp. +3/-0	30±3	4	Room temp.	2~3	* No remarkable damage. * Cap change: NP0: within ±2.5% or 0.25pF whichever is larger X7R, X5R, X6S, X7S: within ±7.5% * Q/D.F., I.R. and dielectric strength: To meet initial requirements.
Step	Temp. (°C)	Time (min.)																
1	Min. operating temp. +0/-3	30±3																
2	Room temp.	2~3																
3	Max. operating temp. +3/-0	30±3																
4	Room temp.	2~3																

No	Item	Test Condition	Requirements																																																										
13	Humidity (Damp Heat) Steady State	Test temp.: 40±2°C Humidity: 90~95% RH Test time: 500+24/-0hrs. Before initial measurement (Class II only): Perform 150+0/-10°C for 1 hr and then set for 24±2 hrs at room temp. Measurement to be made after keeping at room temp. for 24±2 hrs.	* No remarkable damage. * Cap change: NP0: within ±5% or 0.5pF whichever is larger X7R, X5R, X6S, X7S: ≥10V**, within ±12.5%; ≤6.3V within ±25%; **10V: 0603 ≥ 4.7μF; 0402 ≥ 1μF; 0201 ≥ 0.1μF, within ±25%; * Q/D.F. value: NP0: More than 30pF Q ≥ 350, 10pF ≤ C ≤ 30pF, Q ≥ 275+2.5C Less than 10pF Q ≥ 200+10C X7R, X5R, X6S, X7S: <table> <tr> <th>Rated vol.</th><th>D.F. ≤</th><th colspan="2">Exception of D.F. ≤</th></tr> <tr> <td rowspan="4">≥100V</td><td rowspan="4">≤3%</td><td>≤6%</td><td>1206 ≥ 0.47μF</td></tr> <tr> <td>≤7%</td><td>1812 ≥ 4.7μF; 1825 ≥ 4.7μF; 2220 ≥ 4.7μF; 2225 ≥ 4.7μF</td></tr> <tr> <td>≤7.5%</td><td>0603 ≥ 0.068μF; 0805 ≥ 0.1μF; 1206 ≥ 1μF; 1210 ≥ 2.2μF</td></tr> <tr> <td>≤20%</td><td>0805 ≥ 0.22μF; 1210 ≥ 3.3μF</td></tr> <tr> <td rowspan="4">≥50V</td><td rowspan="4">≤3%</td><td>≤6%</td><td>0201(50V); 0603 ≥ 0.047μF; 0805 ≥ 0.18μF; 1206 ≥ 0.47μF</td></tr> <tr> <td>≤7%</td><td>1812 ≥ 4.7μF; 1825 ≥ 4.7μF; 2220 ≥ 4.7μF; 2225 ≥ 4.7μF</td></tr> <tr> <td>≤10%</td><td>0201 ≥ 0.01μF; 0402 ≥ 0.012μF; 1210 ≥ 3.3μF</td></tr> <tr> <td>≤20%</td><td>0402 ≥ 0.047μF; 0603 ≥ 0.1μF; 0805 ≥ 1μF (0805/X7R > 0.47μF); 1206 ≥ 2.2μF; 1210 ≥ 10μF;</td></tr> <tr> <td>35V</td><td>≤5%</td><td>≤20%</td><td>0603 ≥ 1μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 10μF</td></tr> <tr> <td rowspan="4">25V</td><td rowspan="4">≤5%</td><td>≤10%</td><td>0201 ≥ 0.01μF (0201/X5R = 0.01μF; 0805 ≥ 1μF; 1210 ≥ 10μF)*</td></tr> <tr> <td>≤14%</td><td>0603 ≥ 0.33μF</td></tr> <tr> <td>≤15%</td><td>0201 ≥ 0.1μF (0201/X5R > 0.01μF); 0603 ≥ 0.47μF; TT series 0402 ≥ 0.10μF (0402/X7R ≥ 0.056μF); 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF (1210/X5R ≥ 10μF)*</td></tr> <tr> <td>≤20%</td><td>0402 ≥ 0.33μF</td></tr> <tr> <td rowspan="2">16V</td><td rowspan="2">≤5%</td><td>≤10%</td><td>0603 ≥ 0.15μF; 0805 ≥ 0.68μF; 1206 ≥ 2.2μF; 1210 ≥ 4.7μF</td></tr> <tr> <td>≤15%</td><td>0201 ≥ 0.01μF (0201/X7R ≥ 0.022μF); 0402 ≥ 0.033μF; 0603 > 0.47μF; 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF</td></tr> <tr> <td rowspan="2">10V</td><td rowspan="2">≤7.5%</td><td>≤15%</td><td>0201 ≥ 0.012μF; 0402 ≥ 0.22μF (0402/X7R ≥ 0.15μF); 0603 ≥ 0.33μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 22μF</td></tr> <tr> <td>≤20%</td><td>0201 ≥ 0.1μF; 0402 ≥ 1μF; 0603/X5R ≥ 10μF; 01R5/X5R</td></tr> <tr> <td>6.3V</td><td>≤15%</td><td>≤30%</td><td>0201 ≥ 0.1μF; 0402 ≥ 1μF (0402/X6S ≥ 0.47μF); 0603 ≥ 10μF; 0805 ≥ 4.7μF; 1206 ≥ 47μF; 1210 ≥ 100μF</td></tr> <tr> <td>4V</td><td>≤20%</td><td>-</td><td>-</td></tr> </table>	Rated vol.	D.F. ≤	Exception of D.F. ≤		≥100V	≤3%	≤6%	1206 ≥ 0.47μF	≤7%	1812 ≥ 4.7μF; 1825 ≥ 4.7μF; 2220 ≥ 4.7μF; 2225 ≥ 4.7μF	≤7.5%	0603 ≥ 0.068μF; 0805 ≥ 0.1μF; 1206 ≥ 1μF; 1210 ≥ 2.2μF	≤20%	0805 ≥ 0.22μF; 1210 ≥ 3.3μF	≥50V	≤3%	≤6%	0201(50V); 0603 ≥ 0.047μF; 0805 ≥ 0.18μF; 1206 ≥ 0.47μF	≤7%	1812 ≥ 4.7μF; 1825 ≥ 4.7μF; 2220 ≥ 4.7μF; 2225 ≥ 4.7μF	≤10%	0201 ≥ 0.01μF; 0402 ≥ 0.012μF; 1210 ≥ 3.3μF	≤20%	0402 ≥ 0.047μF; 0603 ≥ 0.1μF; 0805 ≥ 1μF (0805/X7R > 0.47μF); 1206 ≥ 2.2μF; 1210 ≥ 10μF;	35V	≤5%	≤20%	0603 ≥ 1μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 10μF	25V	≤5%	≤10%	0201 ≥ 0.01μF (0201/X5R = 0.01μF; 0805 ≥ 1μF; 1210 ≥ 10μF)*	≤14%	0603 ≥ 0.33μF	≤15%	0201 ≥ 0.1μF (0201/X5R > 0.01μF); 0603 ≥ 0.47μF; TT series 0402 ≥ 0.10μF (0402/X7R ≥ 0.056μF); 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF (1210/X5R ≥ 10μF)*	≤20%	0402 ≥ 0.33μF	16V	≤5%	≤10%	0603 ≥ 0.15μF; 0805 ≥ 0.68μF; 1206 ≥ 2.2μF; 1210 ≥ 4.7μF	≤15%	0201 ≥ 0.01μF (0201/X7R ≥ 0.022μF); 0402 ≥ 0.033μF; 0603 > 0.47μF; 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF	10V	≤7.5%	≤15%	0201 ≥ 0.012μF; 0402 ≥ 0.22μF (0402/X7R ≥ 0.15μF); 0603 ≥ 0.33μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 22μF	≤20%	0201 ≥ 0.1μF; 0402 ≥ 1μF; 0603/X5R ≥ 10μF; 01R5/X5R	6.3V	≤15%	≤30%	0201 ≥ 0.1μF; 0402 ≥ 1μF (0402/X6S ≥ 0.47μF); 0603 ≥ 10μF; 0805 ≥ 4.7μF; 1206 ≥ 47μF; 1210 ≥ 100μF	4V	≤20%	-	-
Rated vol.	D.F. ≤	Exception of D.F. ≤																																																											
≥100V	≤3%	≤6%	1206 ≥ 0.47μF																																																										
		≤7%	1812 ≥ 4.7μF; 1825 ≥ 4.7μF; 2220 ≥ 4.7μF; 2225 ≥ 4.7μF																																																										
		≤7.5%	0603 ≥ 0.068μF; 0805 ≥ 0.1μF; 1206 ≥ 1μF; 1210 ≥ 2.2μF																																																										
		≤20%	0805 ≥ 0.22μF; 1210 ≥ 3.3μF																																																										
≥50V	≤3%	≤6%	0201(50V); 0603 ≥ 0.047μF; 0805 ≥ 0.18μF; 1206 ≥ 0.47μF																																																										
		≤7%	1812 ≥ 4.7μF; 1825 ≥ 4.7μF; 2220 ≥ 4.7μF; 2225 ≥ 4.7μF																																																										
		≤10%	0201 ≥ 0.01μF; 0402 ≥ 0.012μF; 1210 ≥ 3.3μF																																																										
		≤20%	0402 ≥ 0.047μF; 0603 ≥ 0.1μF; 0805 ≥ 1μF (0805/X7R > 0.47μF); 1206 ≥ 2.2μF; 1210 ≥ 10μF;																																																										
35V	≤5%	≤20%	0603 ≥ 1μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 10μF																																																										
25V	≤5%	≤10%	0201 ≥ 0.01μF (0201/X5R = 0.01μF; 0805 ≥ 1μF; 1210 ≥ 10μF)*																																																										
		≤14%	0603 ≥ 0.33μF																																																										
		≤15%	0201 ≥ 0.1μF (0201/X5R > 0.01μF); 0603 ≥ 0.47μF; TT series 0402 ≥ 0.10μF (0402/X7R ≥ 0.056μF); 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF (1210/X5R ≥ 10μF)*																																																										
		≤20%	0402 ≥ 0.33μF																																																										
16V	≤5%	≤10%	0603 ≥ 0.15μF; 0805 ≥ 0.68μF; 1206 ≥ 2.2μF; 1210 ≥ 4.7μF																																																										
		≤15%	0201 ≥ 0.01μF (0201/X7R ≥ 0.022μF); 0402 ≥ 0.033μF; 0603 > 0.47μF; 0805 ≥ 2.2μF; 1206 ≥ 4.7μF; 1210 ≥ 22μF																																																										
10V	≤7.5%	≤15%	0201 ≥ 0.012μF; 0402 ≥ 0.22μF (0402/X7R ≥ 0.15μF); 0603 ≥ 0.33μF; 0805 ≥ 2.2μF; 1206 ≥ 2.2μF; 1210 ≥ 22μF																																																										
		≤20%	0201 ≥ 0.1μF; 0402 ≥ 1μF; 0603/X5R ≥ 10μF; 01R5/X5R																																																										
6.3V	≤15%	≤30%	0201 ≥ 0.1μF; 0402 ≥ 1μF (0402/X6S ≥ 0.47μF); 0603 ≥ 10μF; 0805 ≥ 4.7μF; 1206 ≥ 47μF; 1210 ≥ 100μF																																																										
4V	≤20%	-	-																																																										

No	Item	Test Condition	Requirements																																						
	Humidity (Damp Heat) Steady State		*I.R.: $\geq 10V$, $1G\Omega$ or $50\Omega\cdot F$ whichever is smaller. Class II (X7R, X5R, X6S, X7S) <table><tr><th>Rated voltage</th><th>Insulation Resistance</th></tr><tr><td>100V: All X7R;1210$\geq 3.3\mu F$</td><td rowspan="7">1GΩ or RxC$\geq 10\Omega\cdot F$ whichever is smaller.</td></tr><tr><td>50V: 0402$> 0.01\mu F$;0603$\geq 1\mu F$;0805$\geq 1\mu F$;1206$\geq 4.7\mu F$;1210$\geq 4.7\mu F$</td></tr><tr><td>35V:0603$\geq 1\mu F$;0805$\geq 2.2\mu F$; 1206$\geq 2.2\mu F$;1210$\geq 10\mu F$</td></tr><tr><td>25V:0201$\geq 0.1\mu F$; 0402$\geq 0.22\mu F$; 0603$\geq 2.2\mu F$; 0805$\geq 2.2\mu F$; 1206$\geq 10\mu F$;1210$\geq 10\mu F$</td></tr><tr><td>16V: 0201$\geq 0.1\mu F$;0402$\geq 0.22\mu F$;0603$\geq 1\mu F$;0805$\geq 2.2\mu F$; 1206$\geq 10\mu F$;1210$\geq 47\mu F$</td></tr><tr><td>10V: 0201$\geq 47nF$;0402$\geq 0.47\mu F$;0603$\geq 0.47\mu F$; 0805$\geq 2.2\mu F$; 1206$\geq 4.7\mu F$;1210$\geq 47\mu F$</td></tr><tr><td>6.3V ; 4V ; All X6S/X7S items; Size≥ 1812</td></tr></table>	Rated voltage	Insulation Resistance	100V: All X7R;1210 $\geq 3.3\mu F$	1G Ω or RxC $\geq 10\Omega\cdot F$ whichever is smaller.	50V: 0402 $> 0.01\mu F$;0603 $\geq 1\mu F$;0805 $\geq 1\mu F$;1206 $\geq 4.7\mu F$;1210 $\geq 4.7\mu F$	35V:0603 $\geq 1\mu F$;0805 $\geq 2.2\mu F$; 1206 $\geq 2.2\mu F$;1210 $\geq 10\mu F$	25V:0201 $\geq 0.1\mu F$; 0402 $\geq 0.22\mu F$; 0603 $\geq 2.2\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 10\mu F$;1210 $\geq 10\mu F$	16V: 0201 $\geq 0.1\mu F$;0402 $\geq 0.22\mu F$;0603 $\geq 1\mu F$;0805 $\geq 2.2\mu F$; 1206 $\geq 10\mu F$;1210 $\geq 47\mu F$	10V: 0201 $\geq 47nF$;0402 $\geq 0.47\mu F$;0603 $\geq 0.47\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$;1210 $\geq 47\mu F$	6.3V ; 4V ; All X6S/X7S items; Size ≥ 1812																												
Rated voltage	Insulation Resistance																																								
100V: All X7R;1210 $\geq 3.3\mu F$	1G Ω or RxC $\geq 10\Omega\cdot F$ whichever is smaller.																																								
50V: 0402 $> 0.01\mu F$;0603 $\geq 1\mu F$;0805 $\geq 1\mu F$;1206 $\geq 4.7\mu F$;1210 $\geq 4.7\mu F$																																									
35V:0603 $\geq 1\mu F$;0805 $\geq 2.2\mu F$; 1206 $\geq 2.2\mu F$;1210 $\geq 10\mu F$																																									
25V:0201 $\geq 0.1\mu F$; 0402 $\geq 0.22\mu F$; 0603 $\geq 2.2\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 10\mu F$;1210 $\geq 10\mu F$																																									
16V: 0201 $\geq 0.1\mu F$;0402 $\geq 0.22\mu F$;0603 $\geq 1\mu F$;0805 $\geq 2.2\mu F$; 1206 $\geq 10\mu F$;1210 $\geq 47\mu F$																																									
10V: 0201 $\geq 47nF$;0402 $\geq 0.47\mu F$;0603 $\geq 0.47\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$;1210 $\geq 47\mu F$																																									
6.3V ; 4V ; All X6S/X7S items; Size ≥ 1812																																									
14	Humidity (Damp Heat) Load	*Test temp.:40$\pm 2^{\circ}C$ *Humidity: 90~95%RH *Test time: 500+24/-0 hrs. *To apply voltage: Rated voltage (MAX. 500V) *Before initial measurement (Class II only): To apply de-aging at 150$^{\circ}C$ for 1hr then set for 24± 2 hrs at room temp. * Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150$^{\circ}C$ for 1hr then set for 24± 2 hrs at room temp.	* No remarkable damage. Cap change: NP0: $\pm 7.5\%$ or 0.75pF whichever is larger. X7R, X5R, X6S, X7S: $\geq 10V^{**}$,within $\pm 12.5\%$; $\leq 6.3V$ within $\pm 25\%$; **10V: 0603$\geq 4.7\mu F$;0402 $\geq 1\mu F$;0201$\geq 0.1\mu F$, within $\pm 25\%$; Y5V: $\geq 10V$, within $\pm 30\%$; $\leq 6.3V$, within +30/-40% Q/D.F. value: NP0: C$\geq 30pF$,Q≥ 200;C<30pF, Q$\geq 100+10/3C$ X7R, X5R, X6S, X7S: <table><tr><th>Rated vol.</th><th>D.F. $\leq$</th><th colspan="2">Exception of D.F. $\leq$</th></tr><tr><td rowspan="4">$\geq 100V$</td><td rowspan="4">$\leq 3\%$</td><td>$\leq 6\%$</td><td>1206$\geq 0.47\mu F$</td></tr><tr><td>$\leq 7\%$</td><td>1812$\geq 4.7\mu F$;1825$\geq 4.7\mu F$; 2220$\geq 4.7\mu F$; 2225$\geq 4.7\mu F$</td></tr><tr><td>$\leq 7.5\%$</td><td>0603$\geq 0.068\mu F$;0805$\geq 0.1\mu F$;1206$\geq 1\mu F$; 1210$\geq 2.2\mu F$</td></tr><tr><td>$\leq 20\%$</td><td>0805$\geq 0.22\mu F$;1210$\geq 3.3\mu F$</td></tr><tr><td rowspan="4">$\geq 50V$</td><td rowspan="4">$\leq 3\%$</td><td>$\leq 6\%$</td><td>0201(50V);0603$\geq 0.047\mu F$;0805$\geq 0.18\mu F$; 1206$\geq 0.47\mu F$</td></tr><tr><td>$\leq 7\%$</td><td>1812$\geq 4.7\mu F$;1825$\geq 4.7\mu F$; 2220$\geq 4.7\mu F$; 2225$\geq 4.7\mu F$</td></tr><tr><td>$\leq 10\%$</td><td>0201$\geq 0.01\mu F$; 0402$\geq 0.012\mu F$;1210$\geq 3.3\mu F$</td></tr><tr><td>$\leq 20\%$</td><td>0402$\geq 0.047\mu F$;0603$> 0.1\mu F$;0805$\geq 1\mu F$ (0805/X7R$> 0.47\mu F$); 1206$\geq 2.2\mu F$;1210$\geq 10\mu F$;</td></tr><tr><td>35V</td><td>$\leq 5\%$</td><td>$\leq 20\%$</td><td>0603$\geq 1\mu F$;0805$\geq 2.2\mu F$;1206$\geq 2.2\mu F$;1210$\geq 10\mu F$</td></tr><tr><td rowspan="4">25V</td><td rowspan="4">$\leq 5\%$</td><td>$\leq 10\%$</td><td>0201$\geq 0.01\mu F$(0201/X5R$= 0.01\mu F$;0805$\geq 1\mu F$; 1210$\geq 10\mu F$*)</td></tr><tr><td>$\leq 14\%$</td><td>0603$\geq 0.33\mu F$</td></tr><tr><td>$\leq 15\%$</td><td>0201$\geq 0.1\mu F$(0201/X5R$> 0.01\mu F$);0603$\geq 0.47\mu F$; TT series 0402$\geq 0.10\mu F$(0402/X7R$\geq 0.056\mu F$); 0805$\geq 2.2\mu F$; 1206$\geq 4.7\mu F$;1210$\geq 22\mu F$ (1210/X5R$\geq 10\mu F$*)</td></tr><tr><td>$\leq 20\%$</td><td>0402$\geq 0.33\mu F$</td></tr></table>	Rated vol.	D.F. $\leq$	Exception of D.F. $\leq$		$\geq 100V$	$\leq 3\%$	$\leq 6\%$	1206 $\geq 0.47\mu F$	$\leq 7\%$	1812 $\geq 4.7\mu F$;1825 $\geq 4.7\mu F$; 2220 $\geq 4.7\mu F$; 2225 $\geq 4.7\mu F$	$\leq 7.5\%$	0603 $\geq 0.068\mu F$;0805 $\geq 0.1\mu F$;1206 $\geq 1\mu F$; 1210 $\geq 2.2\mu F$	$\leq 20\%$	0805 $\geq 0.22\mu F$;1210 $\geq 3.3\mu F$	$\geq 50V$	$\leq 3\%$	$\leq 6\%$	0201(50V);0603 $\geq 0.047\mu F$;0805 $\geq 0.18\mu F$; 1206 $\geq 0.47\mu F$	$\leq 7\%$	1812 $\geq 4.7\mu F$;1825 $\geq 4.7\mu F$; 2220 $\geq 4.7\mu F$; 2225 $\geq 4.7\mu F$	$\leq 10\%$	0201 $\geq 0.01\mu F$; 0402 $\geq 0.012\mu F$;1210 $\geq 3.3\mu F$	$\leq 20\%$	0402 $\geq 0.047\mu F$;0603 $> 0.1\mu F$;0805 $\geq 1\mu F$ (0805/X7R $> 0.47\mu F$); 1206 $\geq 2.2\mu F$;1210 $\geq 10\mu F$;	35V	$\leq 5\%$	$\leq 20\%$	0603 $\geq 1\mu F$;0805 $\geq 2.2\mu F$;1206 $\geq 2.2\mu F$;1210 $\geq 10\mu F$	25V	$\leq 5\%$	$\leq 10\%$	0201 $\geq 0.01\mu F$ (0201/X5R $= 0.01\mu F$;0805 $\geq 1\mu F$; 1210 $\geq 10\mu F$ *)	$\leq 14\%$	0603 $\geq 0.33\mu F$	$\leq 15\%$	0201 $\geq 0.1\mu F$ (0201/X5R $> 0.01\mu F$);0603 $\geq 0.47\mu F$; TT series 0402 $\geq 0.10\mu F$ (0402/X7R $\geq 0.056\mu F$); 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$;1210 $\geq 22\mu F$ (1210/X5R $\geq 10\mu F$ *)	$\leq 20\%$	0402 $\geq 0.33\mu F$
Rated vol.	D.F. $\leq$	Exception of D.F. $\leq$																																							
$\geq 100V$	$\leq 3\%$	$\leq 6\%$	1206 $\geq 0.47\mu F$																																						
		$\leq 7\%$	1812 $\geq 4.7\mu F$;1825 $\geq 4.7\mu F$; 2220 $\geq 4.7\mu F$; 2225 $\geq 4.7\mu F$																																						
		$\leq 7.5\%$	0603 $\geq 0.068\mu F$;0805 $\geq 0.1\mu F$;1206 $\geq 1\mu F$; 1210 $\geq 2.2\mu F$																																						
		$\leq 20\%$	0805 $\geq 0.22\mu F$;1210 $\geq 3.3\mu F$																																						
$\geq 50V$	$\leq 3\%$	$\leq 6\%$	0201(50V);0603 $\geq 0.047\mu F$;0805 $\geq 0.18\mu F$; 1206 $\geq 0.47\mu F$																																						
		$\leq 7\%$	1812 $\geq 4.7\mu F$;1825 $\geq 4.7\mu F$; 2220 $\geq 4.7\mu F$; 2225 $\geq 4.7\mu F$																																						
		$\leq 10\%$	0201 $\geq 0.01\mu F$; 0402 $\geq 0.012\mu F$;1210 $\geq 3.3\mu F$																																						
		$\leq 20\%$	0402 $\geq 0.047\mu F$;0603 $> 0.1\mu F$;0805 $\geq 1\mu F$ (0805/X7R $> 0.47\mu F$); 1206 $\geq 2.2\mu F$;1210 $\geq 10\mu F$;																																						
35V	$\leq 5\%$	$\leq 20\%$	0603 $\geq 1\mu F$;0805 $\geq 2.2\mu F$;1206 $\geq 2.2\mu F$;1210 $\geq 10\mu F$																																						
25V	$\leq 5\%$	$\leq 10\%$	0201 $\geq 0.01\mu F$ (0201/X5R $= 0.01\mu F$;0805 $\geq 1\mu F$; 1210 $\geq 10\mu F$ *)																																						
		$\leq 14\%$	0603 $\geq 0.33\mu F$																																						
		$\leq 15\%$	0201 $\geq 0.1\mu F$ (0201/X5R $> 0.01\mu F$);0603 $\geq 0.47\mu F$; TT series 0402 $\geq 0.10\mu F$ (0402/X7R $\geq 0.056\mu F$); 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$;1210 $\geq 22\mu F$ (1210/X5R $\geq 10\mu F$ *)																																						
		$\leq 20\%$	0402 $\geq 0.33\mu F$																																						

No	Item	Test Condition	Requirements																								
			<table><tr><th>Rated vol.</th><th>D.F. ≦</th><th colspan="2">Exception of D.F. ≦</th></tr><tr><td rowspan="2">16V</td><td rowspan="2">≦5%</td><td>≦10%</td><td>0603≧0.15μF;0805≧0.68μF;1206≧2.2μF;1210≧4.7μF</td></tr><tr><td>≦15%</td><td>0201≧0.01μF(0201/X7R≧0.022μF);0402≧0.033μF;0603>0.47μF;0805≧2.2μF;1206≧4.7μF;1210≧22μF</td></tr><tr><td rowspan="2">10V</td><td rowspan="2">≦7.5%</td><td>≦15%</td><td>0201≧0.012μF;0402≧0.22μF (0402/X7R≧0.15μF);0603≧0.33μF;0805≧2.2μF;1206≧2.2μF;1210≧22μF</td></tr><tr><td>≦20%</td><td>0201≧0.1μF;0402≧1μF;0603/X5R≧10μF;01R5/X5R</td></tr><tr><td>6.3V</td><td>≦15%</td><td>≦30%</td><td>0201≧0.1μF;0402≧1μF(0402/X6S≧0.47μF);0603≧10μF;0805≧4.7μF;1206≧47μF;1210≧100μF</td></tr><tr><td>4V</td><td>≦20%</td><td>-</td><td>-</td></tr></table>	Rated vol.	D.F. ≦	Exception of D.F. ≦		16V	≦5%	≦10%	0603≧0.15μF;0805≧0.68μF;1206≧2.2μF;1210≧4.7μF	≦15%	0201≧0.01μF(0201/X7R≧0.022μF);0402≧0.033μF;0603>0.47μF;0805≧2.2μF;1206≧4.7μF;1210≧22μF	10V	≦7.5%	≦15%	0201≧0.012μF;0402≧0.22μF (0402/X7R≧0.15μF);0603≧0.33μF;0805≧2.2μF;1206≧2.2μF;1210≧22μF	≦20%	0201≧0.1μF;0402≧1μF;0603/X5R≧10μF;01R5/X5R	6.3V	≦15%	≦30%	0201≧0.1μF;0402≧1μF(0402/X6S≧0.47μF);0603≧10μF;0805≧4.7μF;1206≧47μF;1210≧100μF	4V	≦20%	-	-
			Rated vol.	D.F. ≦	Exception of D.F. ≦																						
			16V	≦5%	≦10%	0603≧0.15μF;0805≧0.68μF;1206≧2.2μF;1210≧4.7μF																					
					≦15%	0201≧0.01μF(0201/X7R≧0.022μF);0402≧0.033μF;0603>0.47μF;0805≧2.2μF;1206≧4.7μF;1210≧22μF																					
			10V	≦7.5%	≦15%	0201≧0.012μF;0402≧0.22μF (0402/X7R≧0.15μF);0603≧0.33μF;0805≧2.2μF;1206≧2.2μF;1210≧22μF																					
					≦20%	0201≧0.1μF;0402≧1μF;0603/X5R≧10μF;01R5/X5R																					
			6.3V	≦15%	≦30%	0201≧0.1μF;0402≧1μF(0402/X6S≧0.47μF);0603≧10μF;0805≧4.7μF;1206≧47μF;1210≧100μF																					
			4V	≦20%	-	-																					
			*I.R.: ≥10V, 500MΩ or 25 Ω-F whichever is smaller. Class II (X7R, X5R, X6S, X7S)																								
			<table><tr><th>Rated voltage</th><th>Insulation Resistance</th></tr><tr><td>100V: All X7R;1210≧3.3μF</td><td rowspan="7">1GΩ or RxC ≧ 10 Ω-F whichever is smaller.</td></tr><tr><td>50V: 0402>0.01μF;0603≧1μF;0805≧1μF;1206≧4.7μF;1210≧4.7μF</td></tr><tr><td>35V:0603≧1μF;0805≧2.2μF; 1206 ≧ 2.2μF;1210 ≧ 10μF</td></tr><tr><td>25V:0201 ≧ 0.1uF; 0402≧0.22μF; 0603≧2.2μF; 0805≧2.2μF; 1206≧10μF;1210≧10μF</td></tr><tr><td>16V: 0201 ≧ 0.1uF;0402≧0.22μF;0603≧1μF;0805≧2.2μF; 1206≧10μF;1210≧47μF</td></tr><tr><td>10V: 0201≧47nF;0402≧0.47μF;0603≧0.47μF; 0805≧2.2μF; 1206≧4.7μF;1210≧47μF</td></tr><tr><td>6.3V ; 4V ; All X6S/X7S items; Size≧1812</td></tr></table>	Rated voltage	Insulation Resistance	100V: All X7R;1210≧3.3μF	1GΩ or RxC ≧ 10 Ω-F whichever is smaller.	50V: 0402>0.01μF;0603≧1μF;0805≧1μF;1206≧4.7μF;1210≧4.7μF	35V:0603≧1μF;0805≧2.2μF; 1206 ≧ 2.2μF;1210 ≧ 10μF	25V:0201 ≧ 0.1uF; 0402≧0.22μF; 0603≧2.2μF; 0805≧2.2μF; 1206≧10μF;1210≧10μF	16V: 0201 ≧ 0.1uF;0402≧0.22μF;0603≧1μF;0805≧2.2μF; 1206≧10μF;1210≧47μF	10V: 0201≧47nF;0402≧0.47μF;0603≧0.47μF; 0805≧2.2μF; 1206≧4.7μF;1210≧47μF	6.3V ; 4V ; All X6S/X7S items; Size≧1812														
Rated voltage	Insulation Resistance																										
100V: All X7R;1210≧3.3μF	1GΩ or RxC ≧ 10 Ω-F whichever is smaller.																										
50V: 0402>0.01μF;0603≧1μF;0805≧1μF;1206≧4.7μF;1210≧4.7μF																											
35V:0603≧1μF;0805≧2.2μF; 1206 ≧ 2.2μF;1210 ≧ 10μF																											
25V:0201 ≧ 0.1uF; 0402≧0.22μF; 0603≧2.2μF; 0805≧2.2μF; 1206≧10μF;1210≧10μF																											
16V: 0201 ≧ 0.1uF;0402≧0.22μF;0603≧1μF;0805≧2.2μF; 1206≧10μF;1210≧47μF																											
10V: 0201≧47nF;0402≧0.47μF;0603≧0.47μF; 0805≧2.2μF; 1206≧4.7μF;1210≧47μF																											
6.3V ; 4V ; All X6S/X7S items; Size≧1812																											
15	High Temperature Load (Endurance)	*Test temp.: NP0, X7R/X7E/X7S: 125±3°C X6S: 105±3°C X5R, 85±3°C *Test time: 1000+24/-0 hrs. *To apply voltage: (1) 100% of rated voltage for below range.	* No remarkable damage. Cap change: NP0: ±3.0% or ±0.3pF whichever is larger X7R, X5R, X6S, X7S: ≥10V**, within ±12.5%; ≤ 6.3V within ±25%; **10V: 0603≥4.7μF;0402≥1μF;0201≥0.1μF, within ±25% Q/D.F. value: NP0: More than 30pF, Q≥350 10pF≤C<30pF, Q≥275+2.5C Less than 10pF, Q≥200+10C X7R, X5R, X6S, X7S:																								


General Purpose Multilayer Ceramic Capacitors
4 to 100V (NP0, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicomp PRO

No	Item	Test Condition				Requirements			
		Size	Dielectric	Rated Voltage	Capacitance	Rated vol.	D.F. $\leq$	Exception of D.F. $\leq$	
		01R5	X5R	$\approx 10V$	$C=0.1\mu F$	$\geq 100V$	$\leq 3\%$	$\leq 6\%$	1206 $\geq 0.47\mu F$
		0201	X5R/X7R/ X6S/X7S	$\leq 10V$	$C \geq 0.1\mu F$			$\leq 7\%$	1812 $\geq 4.7\mu F$; 1825 $\geq 4.7\mu F$; 2220 $\geq 4.7\mu F$; 2225 $\geq 4.7\mu F$
				$\geq 16V$	$C > 0.1\mu F$			$\leq 7.5\%$	0603 $\geq 0.068\mu F$; 0805 $\geq 0.1\mu F$; 1206 $\geq 1\mu F$; 1210 $\geq 2.2\mu F$
		0402	X5R	$\leq 16V$	$C > 1.0\mu F$			$\leq 20\%$	0805 $\geq 0.22\mu F$; 1210 $\geq 3.3\mu F$
				25V, 50V	$C \geq 1.0\mu F$	$\geq 50V$	$\leq 3\%$	$\leq 6\%$	0201(50V); 0603 $\geq 0.047\mu F$; 0805 $\geq 0.18\mu F$; 1206 $\geq 0.47\mu F$
			X6S	6.3V, 10V	$C > 1.0\mu F$			$\leq 7\%$	1812 $\geq 4.7\mu F$; 1825 $\geq 4.7\mu F$; 2220 $\geq 4.7\mu F$; 2225 $\geq 4.7\mu F$
				16V, 25V	$C \geq 1.0\mu F$			$\leq 10\%$	0201 $\geq 0.01\mu F$; 0402 $\geq 0.012\mu F$; 1210 $\geq 3.3\mu F$
		0603	X5R/X7R/ X6S/X7S	4V	$C \geq 22\mu F$	35V	$\leq 5\%$	$\leq 20\%$	0402 $\geq 0.047\mu F$; 0603 $> 0.1\mu F$; 0805 $\geq 1\mu F$ (0805/X7R $> 0.47\mu F$); 1206 $\geq 2.2\mu F$; 1210 $\geq 10\mu F$
				6.3V, 10V	$C \geq 4.7\mu F^{*1}$			$\leq 10\%$	0201 $\geq 0.01\mu F$ (0201/X5R $= 0.01\mu F$; 0805 $\geq 1\mu F$; 1210 $\geq 10\mu F$ *)
			X5R/X6S/X7S	25V	$C \geq 1.0\mu F$			$\leq 15\%$	0201 $\geq 0.1\mu F$ (0201/X5R $> 0.01\mu F$); 0603 $\geq 0.47\mu F$; TT series 0402 $\geq 0.10\mu F$ (0402/X7R $\geq 0.056\mu F$); 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$; 1210 $\geq 22\mu F$ (1210/X5R $\geq 10\mu F$ *)
		0805	X5R/X7R/ X6S/X7S	4V	$C \geq 47\mu F$	25V	$\leq 5\%$	$\leq 10\%$	0603 $\geq 0.15\mu F$; 0805 $\geq 0.68\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 4.7\mu F$
				6.3V	$C \geq 22\mu F$			$\leq 14\%$	0603 $\geq 0.33\mu F$
				10V, 50V	$C \geq 10\mu F$			$\leq 15\%$	0201 $\geq 0.1\mu F$ (0201/X5R $> 0.01\mu F$); 0603 $\geq 0.47\mu F$; TT series 0402 $\geq 0.10\mu F$ (0402/X7R $\geq 0.056\mu F$); 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$; 1210 $\geq 22\mu F$ (1210/X5R $\geq 10\mu F$ *)
			X6S	16V	$C > 10\mu F$			$\leq 20\%$	0402 $\geq 0.33\mu F$
		1206	X5R/X7R/X6S	4V	$C \geq 47\mu F$	16V	$\leq 5\%$	$\leq 10\%$	0603 $\geq 0.15\mu F$; 0805 $\geq 0.68\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 4.7\mu F$
				6.3V	$C \geq 22\mu F$			$\leq 15\%$	0201 $\geq 0.1\mu F$ (0201/X7R $\geq 0.022\mu F$); 0402 $\geq 0.033\mu F$; 0603 $> 0.47\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$; 1210 $\geq 22\mu F$
		1210	X7R	100V	$C \geq 3.3\mu F$	10V	$\leq 7.5\%$	$\leq 15\%$	0201 $\geq 0.012\mu F$; 0402 $\geq 0.22\mu F$ (0402/X7R $\geq 0.15\mu F$); 0603 $\geq 0.33\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 22\mu F$
		TT15	X5R	6.3V	$C > 1.0\mu F$			$\leq 20\%$	0201 $\geq 0.1\mu F$; 0402 $\geq 1\mu F$; 0603/X5R $\geq 10\mu F$; 01R5/X5R
		TT21	X5R/X7R/X6S	$\leq 10V$	$C \geq 10\mu F$	6.3V	$\leq 15\%$	$\leq 30\%$	0201 $\geq 0.1\mu F$; 0402 $\geq 1\mu F$ (0402/X6S $\geq 0.47\mu F$); 0603 $\geq 10\mu F$; 0805 $\geq 4.7\mu F$; 1206 $\geq 47\mu F$; 1210 $\geq 100\mu F$
		**1WV items must follow de-rating conditions. #1. 0603X106/475(10V)&0603S106(4V&6.3V): 150% of rated voltage (2) 150% of rated voltage for below range.				4V	$\leq 20\%$	-	-
		Size	Dielectric	Rated Voltage	Capacitance				
		0201	X5R/X6S	16V, 25V	$C=0.1\mu F$				
			X7R	16V	$C \geq 0.022\mu F$				
		0402	X7R/X5R/X6S	50V	$C > 0.01\mu F$				
				10~25V	$C \geq 0.22\mu F$				
		0603	X7S	50V~100V	$C > 0.22\mu F$				
				50V	$C > 0.1\mu F$				
			X5R	25V	$C \geq 1.0\mu F$				
				50V	$C \geq 1.0\mu F$				
		0805	X5R/X7R/ X6S/ X7S	10V, 16V	$C \geq 1.0\mu F$				
				100V	$C \geq 0.47\mu F$				
				50V	$C \geq 0.68\mu F$				
				35V	$C \geq 2.2\mu F$				
				10~25V	$C \geq 4.7\mu F$				

*I.R.: $\geq 10V$, 1G Ω or 50 Ω -F whichever is smaller.
 Class II (X7R, X5R, X6S, X7S)


Rated voltage	Insulation Resistance
100V: All X7R; 1210 $\geq 3.3\mu F$	1G Ω or RxC $\geq 10\Omega$ -F whichever is smaller.
50V: 0402 $> 0.01\mu F$; 0603 $\geq 1\mu F$; 0805 $\geq 1\mu F$; 1206 $\geq 4.7\mu F$; 1210 $\geq 4.7\mu F$	
35V: 0603 $\geq 1\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 2.2\mu F$; 1210 $\geq 10\mu F$	
25V: 0201 $\geq 0.1\mu F$; 0402 $\geq 0.22\mu F$; 0603 $\geq 2.2\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 10\mu F$; 1210 $\geq 10\mu F$	
16V: 0201 $\geq 0.1\mu F$; 0402 $\geq 0.22\mu F$; 0603 $\geq 1\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 10\mu F$; 1210 $\geq 47\mu F$	
10V: 0201 $\geq 47nF$; 0402 $\geq 0.47\mu F$; 0603 $\geq 0.47\mu F$; 0805 $\geq 2.2\mu F$; 1206 $\geq 4.7\mu F$; 1210 $\geq 47\mu F$	
6.3V ; 4V ; All X6S/X7S items; Size ≥ 1812	

No	Item	Test Condition	Requirements																													
		<table border="1"> <thead> <tr> <th>Size</th><th>Dielectric</th><th>Rated Voltage</th><th>Capacitance</th></tr> </thead> <tbody> <tr> <td rowspan="4">1206</td><td rowspan="2">X7R</td><td>100V</td><td>$C \cong 1.0\mu\text{F}$</td></tr> <tr> <td>50V</td><td>$C \cong 2.2\mu\text{F}$</td></tr> <tr> <td rowspan="2">X5R/X6S/X7S</td><td>100V</td><td>$C > 1.0\mu\text{F}$</td></tr> <tr> <td>50V</td><td>$C \cong 4.7\mu\text{F}$</td></tr> <tr> <td>1210</td><td>X5R/X7R/ X6S/ X7S</td><td>50V~100V</td><td>$C \cong 2.2\mu\text{F}$</td></tr> <tr> <td rowspan="2">1812</td><td rowspan="2">X7R</td><td>$\cong 50\text{V}$</td><td>$C \cong 4.7\mu\text{F}$</td></tr> <tr> <td>100V</td><td>$C \cong 1.0\mu\text{F}$</td></tr> <tr> <td>1825 2220 2225</td><td>X7R</td><td>100V~250V</td><td>$C \cong 1.0\mu\text{F}$</td></tr> </tbody> </table> (3) $\leq 6.3\text{V}$ or $C \geq 10\mu\text{F}$ or TT series: 150% of rated voltage. (4) 10V~250V: 200% of rated voltage. Excluding 1812/NP0(250V)/104: 100% of rated voltage. (5) 400V~450V: 120% of rated voltage. (6) 500V: 150% of rated voltage. (7) 630V~3000V: 120% of rated voltage. Excluding 1210/X7R(2kV)/103: 110% of rated voltage. 1210/NP0(1kV)/333: 100% of rated voltage. 1812/NP0(1kV)/472~562: 100% of rated voltage. (8) Ur=3.5kV & 4kV: 110% of rated voltage. * Before initial measurement (Class II only): To apply de-aging at 150°C for 1hr then set for 24±2 hrs at room temp. * Cap. / DF(Q) / I.R. Measurement to be made after de-aging at 150°C for 1hr then set for 24±2 hrs at room temp.	Size	Dielectric	Rated Voltage	Capacitance	1206	X7R	100V	$C \cong 1.0\mu\text{F}$	50V	$C \cong 2.2\mu\text{F}$	X5R/X6S/X7S	100V	$C > 1.0\mu\text{F}$	50V	$C \cong 4.7\mu\text{F}$	1210	X5R/X7R/ X6S/ X7S	50V~100V	$C \cong 2.2\mu\text{F}$	1812	X7R	$\cong 50\text{V}$	$C \cong 4.7\mu\text{F}$	100V	$C \cong 1.0\mu\text{F}$	1825 2220 2225	X7R	100V~250V	$C \cong 1.0\mu\text{F}$	** De-rating conditions:  The general MLCC products are designed for use in devices with a typical lifetime around 10 years. The general MLCC products are designed so that the useful lifetime can be extended longer than 10 years under the following conditions: *80% of the rated voltage or less, Maximum operating temperature -20 degree C or less Extended useful lifetime, under specific operating conditions, can be estimated from the chart. *The useful lifetime is the time when cumulative failure rate becomes 1%. *Please note that the useful lifetime data is for reference only and not guaranteed.
Size	Dielectric	Rated Voltage	Capacitance																													
1206	X7R	100V	$C \cong 1.0\mu\text{F}$																													
		50V	$C \cong 2.2\mu\text{F}$																													
	X5R/X6S/X7S	100V	$C > 1.0\mu\text{F}$																													
		50V	$C \cong 4.7\mu\text{F}$																													
1210	X5R/X7R/ X6S/ X7S	50V~100V	$C \cong 2.2\mu\text{F}$																													
1812	X7R	$\cong 50\text{V}$	$C \cong 4.7\mu\text{F}$																													
		100V	$C \cong 1.0\mu\text{F}$																													
1825 2220 2225	X7R	100V~250V	$C \cong 1.0\mu\text{F}$																													


* "Room condition" Temperature: 15 to 35°C, Relative humidity: 25 to 75%, Atmospheric pressure: 86 to 106kPa

Appendixes

Tape & Reel Dimensions



The dimension of paper tape




The dimension of plastic tape

General Purpose Multilayer Ceramic Capacitors
4 to 100V (NPO, X7R, Y5V, X6S, X7S & X5R Dielectrics)

multicomp PRO

Size	0201	0402	0603	0805			1206			1210				1808		1812		
Thickness	L	N,E	S,H,X	A,H	B,T	D,I	B,T	C,J,D	G,P	T	C,D	G,K	M	D,F	G,K	D,F	G,K	M,U
A ₀	0.4 ±0.1	0.7 ±0.2	1.05 ±0.3	1.5 ±0.20	1.5 ±0.20	< 1.8	1.9 ±0.5	< 2	<2.3	< 3.05	< 3.05	< 3.05	< 3.20	< 2.50	< 2.50	< 3.90	< 3.90	< 3.9
B ₀	0.7 ±0.1	1.2 ±0.2	1.8 ±0.3	2.3 ±0.2	2.3 ±0.2	< 2.7	3.5 ±0.5	< 3.7	< 4	< 3.8	< 3.8	< 3.8	<4	< 5.3	< 5.3	< 5.3	< 5.3	< 5.3
T	≦0.55	≦0.8	≦1.2	≦1.15	≦1.2	0.23 ±0.1	≦1.2	0.23 ±0.1	0.23 ±0.1	0.23 ±0.1	0.23 ±0.1	0.23 ±0.1	0.23 ±0.1	0.25 ±0.1	0.25 ±0.1	0.25 ±0.1	0.25 ±0.1	0.25 ±0.1
K ₀	0.44 ±0.05	-	-	-	-	< 2.5	-	< 2.5	< 2.5	< 1.5	< 2	< 2.5q	< 3.2	< 2.5	< 2.5	< 2.5	< 2.5	< 3.5
W	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	8.00 ±0.30	12.00 ±0.30	12.00 ±0.30	12.00 ±0.30	12.00 ±0.30	12 ±0.3
P ₀	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4.00 ±0.10	4 ±0.1
10xP ₀	40 ±0.1	40 ±0.1	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2	40 ±0.2
P ₁	2 ±0.05	2 ±0.05	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	4 ±0.1	8 ±0.1	8 ±0.1	8 ±0.1
P ₂	2 ±0.05	2 ±0.05	2±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2 ±0.05	2. ±0.1	2. ±0.1	2. ±0.1	2. ±0.1	2 ±0.1
D ₀	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0	1.5 ±0.1/-0
D ₁	-	-	-	-	-	1 ±0.1	-	1 ±0.1	1 ±0.1	1 ±0.1	1 ±0.1	1 ±0.1	1 ±0.1	1.5 ±0.1	1.5 ±0.1	1.5 ±0.1	1.5 ±0.1	1.5 ±0.1
E	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1	1.75 ±0.1
F	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	3.5 ±0.05	5.5 ±0.1	5.5 ±0.1	5.5 ±0.1	5.5 ±0.1	5.5 ±0.1


Dimensions : Millimetres



The dimension of reel

Size	0201, 0402, 0603, 0805, 1206, 1210			1812
Reel size	7"	10"	13"	7"
C	13 ±0.5	13 ±0.5	13 ±0.5	13 ±0.5
W ₁	10 ±1.5	10 ±1.5	10 ±1.5	12.4 +2.0/-0
A	178 ±2	250 ±2	330 ±2	178 ±2.0
N	60 +1.0/-0	50 min	50 min	60 +1.0/-0

Constructions



No.	Name	NPO, X7R, X5R, X6S, X7S, Y5V
1	Ceramic material	BaTiO ₃ based
2	Inner electrode	Ni
3	Termination	Inner layer
4		Middle layer
5		Outer layer

Storage and handling conditions


- (1) To store products at 5°C to 40°C ambient temperature and 20 to 70% related humidity conditions.
- (2) The product is recommended to be used within one year after shipment. Check solderability in case of shelf life extension is needed.

Cautions:


- a. The corrosive gas reacts on the terminal electrodes of capacitors, and results in the poor solderability. Do not store the capacitors in the ambience of corrosive gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine, ammonia gas etc.)
- b. In corrosive atmosphere, solderability might be degraded, and silver migration might occur to cause low reliability.
- c. Due to the dewing by rapid humidity change, or the photochemical change of the terminal electrode by direct sunlight, the solderability and electrical performance may deteriorate. Do not store capacitors under direct sunlight or dewing condition. To store products on the shelf and avoid exposure to moisture.

Recommended Soldering Conditions:

The lead-free termination MLCCs are not only to be used on SMT against lead-free solder paste, but also suitable against lead-containing solder paste. If the optimized solder joint is requested, increasing soldering time, temperature and concentration of N₂ within oven are recommended.



Recommended reflow soldering profile for SMT process with SnAgCu series solder paste.



Recommended wave soldering profile for SMT process with SnAgCu series solder.

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.