

Load cells SAUTER CB Q1 · CB Q2 · CB P1







Fig. shows accessories, base plate ■ SAUTER CE Q30903 and bearings ■ SAUTER CE Q30904, for further accessories please visit our online shop



Fig. shows optional accessories load corner

3 SAUTER CE P4022

CB Q1 · CB Q2

Bending beam and shear beam load cells made of stainless steel





- Accuracy in accordance with OIML R60 C3
- · CE and RoHS compliant
- Dust and spray protection to IP68/IP69K (in accordance with EN 60529), welded to create a hermetic seal
- · Stainless steel
- Area of application: Weight measurement as well as compressive force in harsh environments
- Suitable for platform scales, funnel scales, floor scales and other weighing devices
- 4-wire connection
- Nominal sensitivity: 2 mV/V
- Note: Accuracy class OIML R60 C6 or EX version on request

Nominal load

30

50

75

100

150

200

250

300

500

750

1000

1500

CB P1

Load cells made of stainless steel





- Accuracy in accordance with OIML R60 C3
- CE and RoHS compliant
- Dust and spray protection to IP67 (in accordance with EN 60529), hermetically encapsulated
- · Nickel-plated steel
- Area of application: Weight measurement as well as compressive force in harsh environments
- Suitable for platform scales, silo scales, bed scales and other diverse scales
- · 4-wire connection
- · Nominal sensitivity: 3 mV/V

Accessories CB Q1 · CB Q2:

- Traction device, steel, galvanised, suitable for CB Q1, SAUTER CE Q30901
- Traction device, steel, rustproof, suitable for CB Q2, SAUTER CE Q34905
- Base plate, steel, galvanised, suitable for CB Q1, SAUTER CE Q30903
- Base plate, steel, rustproof, suitable for CB Q1, SAUTER CE RQ30903
- Base plate, steel, rustproof, suitable for CB Q2, SAUTER CE Q34903
- Bearing, steel, rustproof, suitable for CB Q1 (nominal load 5 kg-50 kg), SAUTER CE Q30904
- Bearing, steel, rustproof, suitable for CB Q1 (nominal load 75 kg-300 kg), SAUTER CE Q30905
- Bearing, steel, rustproof, suitable for CB 500-3Q1, SAUTER CE Q30906
- Bearing, steel, rustproof, suitable for CB 750-3Q2, CB 1000-3Q2, CB 1500-3Q2, SAUTER CE Q34906
- Load corner, steel, galvanised, suitable for CB Q1, SAUTER CE Q30907
- Load corner, steel, rustproof, suitable for CB Q1, SAUTER CE RQ30907
- Adjustable foot, steel, rustproof, suitable for SAUTER CE Q34901

~ ~	 	 0

Model

CB 30-3Q1

CB 50-3Q1

CB 75-3Q1

CB 100-3Q1

CB 150-3Q1

CB 200-3Q1

CB 250-3Q1

CB 300-3Q1

CB 500-3Q1

CB 750-3Q2**

CB 1000-3Q2**

CB 1500-3Q2**

Model	Nominal load

SAUTER	kg	SAUTER	kg	
CB 5-3Q1	5	CB 100-3P1	100	
CB 10-3Q1	10	CB 250-3P1	250	
CB 20-3Q1	20			

Accessories CB P1:

- Adjustable foot, steel, nickel-plated, load base M12 for CT 500-3P1, CT 1000-3P1 and CT 1500-3P1, SAUTER CE P2012
- 3 Load corner, steel, nickel-plated for CT 500-3P1, CT 1000-3P1 and CT 1500-3P1, SAUTER CE P4022
- Spacer plates for bending beam CB P1 made of steel, SAUTER CE P3012

** ONLY WHILE STOCKS LAST!



Tip

Further details and technical data sheet as well as extensive accessories see internet

^{*} up to max. 500 kg

MEASURING TECHNOLOGY & TEST SERVICE 2023

SAUTER PICTOGRAMS





Adjusting program (CAL):

For quick setting of the instrument's accuracy. External adjusting weight required



Calibration block:

Standard for adjusting or correcting the measuring device



Peak hold function:

Capturing a peak value within a measuring process



Scan mode:

Continuous capture and display of measurements



Push and Pull:

The measuring device can capture tension and compression forces



Length measurement:

Captures the geometric dimensions of a test object or the movement during a test process



Focus function:

Increases the measuring accuracy of a device within a defined measuring range



Internal memory:

To save measurements in the device memory



Data interface RS-232:

Bidirectional, for connection of printer and PC



Profibus:

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference.



Profinet:

Enables efficient data exchange between decentralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



Data interface USB:

To connect the measuring instrument to a printer, PC or other peripheral devices



Bluetooth* data interface:

To transfer data from the balance/ measuring instrument to a printer, PC or other peripherals



WLAN data interface:

To transfer data from the balance/ measuring instrument to a printer, PC or other peripherals



Data interface Infrared:

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



Control outputs

(optocoupler, digital I/O): To connect relays, signal lamps,

valves, etc.



Analogue interface:

To connect a suitable peripheral device for analogue processing of the measurements



Analog output:

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



Statistics:

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software:

To transfer the measurement data from the device to a PC



Printer:

A printer can be connected to the device to print out the measurement



Network interface:

For connecting the scale/measuring instrument to an Ethernet network



KERN Communication Protocol (KCP):

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO record keeping:

Of measurement data with date, time and serial number. Only with SAUTER printers



Measuring units:

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function):
Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

ZERO:

Resets the display to "0"



Battery operation:

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack:

Rechargeable set



Plug-in power supply:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available



Integrated power supply unit: Integrated, 230V/50Hz in EU.

More standards e.g. GB, AUS or USA on request



Motorised drive:

The mechanical movement is carried out by a electric motor



Motorised drive:

The mechanical movement is carried out by a synchronous motor (stepper)



Fast-Move:

The total length of travel can be covered by a single lever movement



Verification possible:

Models with type approval for construction of verifiable systems



DAkkS calibration possible:

The time required for DAkkS calibration is shown in days in the pictogram



Factory calibration:

The time required for factory calibration is specified in the pictogram



Package shipment:

The time required for internal shipping preparations is shown in days in the



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram

[→]0+

^{*}The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Othear trademarks and trade names are those of their respective owners.