

Step ladder with rungs

Double-sided access



Application:

For anyone wanting to get up high: flexible ascent with up to 20 rungs for working heights up to 6.70 m.

Execution:

- Strong, light metal rungs (30 mm x 30 mm) with non-slip, grooved surface
- Rung-rail connections made of high-strength Zarges quality flanging
- Robust, firmly bolted steel hinges
- Secured against spreading by two high-strength, nylon belts fastened to the rung so as to prevent twisting
- Rungs and rails made of extruded aluminium profiles
- Additional stabilisation with bracing on the lowest rung
- Replaceable 2-component plastic end caps which fit securely on the rail and ensure that the ladder does not slip

Advantage:

- Very light yet extremely robust



Art. no.	50260 641
Brand	ZARGES
Manufacturer Part Number	40312
Working height	3.55 m
Number of rungs	2 x 8
Accessibility	Both sides
Weight	8.4 kg
Folding	Yes
Length	2.34 m
Height, vertical	2.3 m
Width (bottom)	0.59 m
Rail height	58 mm
With storage tray	No
Material	Aluminium
Max. load capacity	150 kg
EN standard	131
Gross Weight	8.400 kg
Product Group	5AK

EAN

4003866403127