

WEVF 10-125 Quick Inox flat head angle grinder

1000 W

metabo[®]

Application:

Specially developed for removing weld slag, rust or paint in narrow frame constructions and for working in tight spaces

Execution:

- Metabo S-automatic mechanical safety clutch
- cut-out carbon brushes for protecting the motor
- speed adjustment for perfect machining of stainless steel

Delivery:

Protective cover, support flange, M-Quick clamping nut, additional handle, lamellar grinding disc Flexiamant Super Convex (125 mm; P60)



Art. no.	70373 510
Brand	METABO
Manufacturer Part Number	613080000
Model	WEVF 10-125 Quick Inox
Manufacturer Article Number	613080000
Battery included	No
Number of rechargeable batteries/batteries	0
Washer diameter	125 mm
Power input	1000 W
Power output	590 W
Thread dimension of spindle	M14
Min./max. idle speed	2000-7600 rpm
Weight	2.3 kg
With restart protection	Yes
With soft start	Yes
With overload protection	Yes
With electronic feedback	Yes
With reverse switch off	Yes
With disc brake	No
With quick clamping system	Yes
With dead man function	No
Gross Weight	3.050 kg
Product Group	745

EAN

4007430275677