

Collet chuck type ER with mini nut DIN 6499

Slim design, ISO 7388-1

ATORN[®]

Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm²
- Internal coolant supply
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm
- max. concentricity < 0.005 mm
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- All functional surfaces machined

Delivery

with clamping nut



Art. no.	23297 109
Tool holding device	SK 40
Min./max. clamping range 2	0.5-7 mm
Projecting length	55 mm
Outer diameter	16 mm
Clearance length to collar	36 mm

EAN-Code

40502937 102 12