



Blue (/52) - PL-L, PL-S

PL-L 18W/52/4P 1CT/25

By emitting light almost entirely within the 400 to 500 nm bandwidth and peaking at 450 nm, Philips PL-L/PL-S color 52 lamps have no radiation from the short wave UVB. waveband. They are therefore suitable to be used in systems for applications such as Agriculture and Neonatal Jaundice Phototherapy

Warnings and Safety

- lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take them to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Photobiological safety – IEC 62471 - Risk Group 2. CAUTION - Possibly hazardous optical radiation emitted from these products.


Product data

General Information		Mechanical and Housing	
Cap-Base	2G11	Bulb Shape	2xT16
Light Technical		Approval and Application	
Color Code	52	Mercury (Hg) Content (Nom)	4.4 mg
Luminous Flux	330 lm	Product Data	
Chromaticity Coordinate X (Nom)	155	Order product name	PL-L 18W/52/4P 1CT/25
Chromaticity Coordinate Y (Nom)	75	Full product name	PL-L 18W/52/4P 1CT/25
Operating and Electrical		Full product code	872790080517800
Power Consumption	17.5 W	Order code	927904105206
Lamp Current (Nom)	0.375 A	Material Nr. (12NC)	927904105206
Voltage (Nom)	57 V	Numerator - Quantity Per Pack	1
		Net Weight (Piece)	60.900 g
		EAN/UPC - Product/Case	8727900805178

Blue (/52) - PL-L, PL-S

Numerator - Packs per outer box	25
EAN/UPC - Case	8727900805185

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 18W/52/4P 1CT/25	18 mm	39 mm	188.2 mm	214 mm	220.6 mm

