

## Precision scales PCD

**KERN**

### Application:

Ideal for working in glove bag or under laboratory extractors. Especially practical for weighing toxic, volatile or contaminated substances

### Execution:

- Laboratory scales with separate platform
- PRE-TARE function for manual prior deduction of a known container weight, useful for fill level checks
- Freely programmable weighing unit, e.g. display directly in thread length g/m, paper weight g/m<sup>2</sup>, or similar
- Level and foot screws for precise levelling of the scales come as standard, producing the most accurate weighing results
- high-resolution and flexible thanks to removable evaluation unit

### Delivery:

with power supply unit and work protection hood



<b>Art. no.</b>	<b>49000 015</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	PCD 10K-3
<b>Type description</b>	PCD 10K-3
<b>Max. weight measuring range</b>	10000 g
<b>Digit increment, weight</b>	1 g
<b>Plate size</b>	160 x 160 mm
<b>Material of cover panel</b>	Stainless steel
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	20 g
<b>Reproducibility</b>	1 g
<b>Linearity</b>	3 g
<b>Settling time scale</b>	3 s
<b>Data transmission type</b>	RS232
<b>Housing dimensions (LxWxH)</b>	165 x 280 x 75 mm
<b>Display type</b>	LCD
<b>Gross Weight</b>	2.469 kg
<b>Product Group</b>	447

### EAN

4045761192027