





Dimension :

Poles	DIM:(mm)		Poles	DIM:(mm)	
	A	B		A	B
4	2.54	5.58	24	27.94	30.98
6	5.08	8.12	26	30.48	33.52
8	7.62	10.66	28	33.02	36.06
10	10.16	13.20	30	35.56	38.60
12	12.70	15.74	32	38.10	41.14
14	15.24	18.28	34	40.64	43.68
16	17.78	20.82	36	43.18	46.22
18	20.32	23.36	38	45.72	48.76
20	22.86	25.90	40	48.26	51.30
22	25.40	28.44			



PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PA 9T
 FLAMABILITY RATING: UL94-V0
 MAX TEMPERATURE: 260°C 10 S
 COLOR: BLACK
 CONTACT MATERIAL: COPPER ALLOYS
 CONTACT TYPE: STAMPED
 CONTACT PLATING: GOLD
 QUALITY CLASS: 3 AS PER CECC 75 301-802
 PITCH: 2.54MM

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 3A MAX
 WORKING VOLTAGE: 250V AC
 INSULATOR RESISTANCE: >1000 MOHM
 WITHSTANDING VOLTAGE: 600V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX

SOLDERING
 JEDEC LEAD FREE REFLOW SOLDERING

PACKAGING
 TUBE

DIMENSION
 A = 2.54 x (NB. PIN / 2 - 1)
 B = (2.54 x NB. PIN / 2) + 0.5

RoHS Compliant

PROJECTION:



APPROVAL: GM

GENERAL TOLERANCE

.X = +/- 0.2
 .XX = +/- 0.15



UNIT: MM

SCALE:

SHEET: 1/2

DRAW: MARY

DESCRIPTION: PHD 2.54MM DUAL SMT SOCKET HEADER

WERI PART NO: 610 0xx 218 21

SIZE

A4

1

2

3

4

5

Cautions and Warnings:

This electronic component is designed and developed with the intention for use in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Würth Elektronik must be asked for a written approval.



In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

A

B

C

RoHS Compliant

G				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		
F							
E							
D							
C				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE A4
B					SCALE:		
A	10-SEP-14	PDF	QL		SHEET: 1/1	WERI PART NO: DISCLAIMER	
REV	DATE	FILE	BY		DRAW: QL		

D