

Pneumatic straight grinder G 813 H

**MANNESMANN
DEMAG**

Application:

For fine milling, grinding, engraving and polishing work

Delivery:

Incl. hose unit



Art. no.	75061 045
Model	G 813 H
Valve design	Lever valve
Max. idle speed	70000 rpm
Min./max. idle speed	0-70000 rpm
Power input	70 W
Air consumption	2 l/s
Sound-pressure level	76 dB
Length	120 mm
Diameter of housing	14 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	6 mm
Max. HM rotating milling cutter diameter	4 mm
Weight	0.11 kg

EAN-Code

4251757301032