



CorePro - LED HID SON-T



TForce Core LED road 26W 727 E27 MV

The Philips CorePro LED HID SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant saving with a low initial investment. Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our HighPower LED filament technology. Plus, its unique IP65 design means it can be used for outdoor applications

Warnings and Safety

· Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Product data

General Information		
Cap-Base	E27	
Nominal lifetime	25,000 hour(s)	
Switching Cycle	50,000	
Lighting Technology	LED	
Flux measurement reference	Sphere	
CE mark	Yes	
EU RoHS compliant	Yes	
Light Technical		
Color Code	727 [CCT of 2700K]	
Beam Angle (Nom)	330 degree(s)	
Luminous Flux	4,000 lm	
Color Designation	Warm White (WW)	

Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	153 lm/W
Color Consistency	<6
Color rendering index (CRI)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per	1
EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	4
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	26 W
Lamp Current (Nom)	120 mA

Datasheet, 2024, March 18 data subject to change

CorePro - LED HID SON-T

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Inrush current at mains	8.5
Max. lamp no. on MCB B type 10A - Mains	35
Max. lamp no. on MCB B type 10A – EM ballast	-
without Comp. Cap.	
Max. lamp no. on MCB B type 10A – EM ballast	-
with Comp. Cap.	
Max. lamp no. on MCB B type 16A - Mains	56
Max. lamp no. on MCB B type 16A – EM ballast	-
without Comp. Cap.	
Max. lamp no. on MCB B type 16A – EM ballast	-
with Comp. Cap.	
Ballast Compatibility	Mains
Temperature	
Ambient temperature range	-30 to +45 °C
T-Case Maximum (Nom)	44.55 °C
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T38
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	26 kWh
EPREL Registration Number	1617393
Product Data	
rder product name	TForce Core LED road 26W 727 E27
	MV
Full product name	TForce Core LED road 26W 727 E27
	MV
Full product code	872016926773200
Order code	929003730902
Material Nr. (12NC)	929003730902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169267732
Numerator - Packs per outer box	6
EAN/UPC - Case	8720169267749


Dimensional drawing



Product	D	С
TForce Core LED road 26W 727 E27 MV	38.5 mm	214 mm


CorePro - LED HID SON-T

Photometric data




Calculat Presentation 4.5 Philips Lighting B.V. Page:

General uniform lighting - TForce Core LED road 26W 727 E27 MV





Light Distribution Diagram - TForce Core LED road 26W 727 E27 MV



Spectral Power Distribution Colour - TForce Core LED road 26W 727 E27 MV

Lifetime





Life Expectancy Diagram - TForce Core LED road 26W 727 E27 MV

Lumen Maintenance Diagram - TForce Core LED road 26W 727 E27 MV

CorePro - LED HID SON-T



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.