



Identification	Part number	Drawing	Dimensions in mm
<p>Hybrid fibre optic cable, single mode, double ended 2 x FO + 3 x 2.5 mm², 2 x Han® 3 A</p> <p>Length: a = 1 m AC version DC version</p> <p>a = 5 m AC version DC version</p> <p>a = 10 m AC version DC version</p> <p>a = 20 m AC version DC version</p> <p>a = 40 m AC version DC version</p> <p>a = 50 m AC version DC version</p> <p>a = 100 m AC version DC version</p>	<p>33 57 211 0015 003</p> <p>33 57 211 0015 004</p> <p>33 57 211 0055 003</p> <p>33 57 211 0055 004</p> <p>33 57 211 0105 003</p> <p>33 57 211 0105 004</p> <p>33 57 211 0205 003</p> <p>33 57 211 0205 004</p> <p>33 57 211 0405 003</p> <p>33 57 211 0405 004</p> <p>33 57 211 0505 003</p> <p>33 57 211 0505 004</p> <p>33 57 211 1005 003</p> <p>33 57 211 1005 004</p>	<p>double ended</p> <p>a = length</p> <p>Protection level: IP65/IP67</p>	
<p>Hybrid fibre optic cable, single mode, single ended 2 x FO + 3 x 2.5 mm², 1 x Han® 3 A</p> <p>Length: a = 1 m AC version DC version</p> <p>a = 5 m AC version DC version</p> <p>a = 10 m AC version DC version</p> <p>a = 20 m AC version DC version</p> <p>a = 40 m AC version DC version</p> <p>a = 50 m AC version DC version</p> <p>a = 100 m AC version DC version</p>	<p>33 57 111 0015 003</p> <p>33 57 111 0015 004</p> <p>33 57 111 0055 003</p> <p>33 57 111 0055 004</p> <p>33 57 111 0105 003</p> <p>33 57 111 0105 004</p> <p>33 57 111 0205 003</p> <p>33 57 111 0205 004</p> <p>33 57 111 0405 003</p> <p>33 57 111 0405 004</p> <p>33 57 111 0505 003</p> <p>33 57 111 0505 004</p> <p>33 57 111 1005 003</p> <p>33 57 111 1005 004</p>	<p>single ended</p> <p>a = length</p>	
<p>Hybrid fibre optic cable, single mode</p> <p>Length: 10 m</p> <p>Length: 20 m</p> <p>Length: 500 m</p>	<p>33 57 851 0100 004</p> <p>33 57 851 0200 004</p> <p>33 57 851 5000 004</p>	<p>PVC jacket</p> <p>2 x 9/125 + 3 x 2.5 mm²</p> <p>Outer diameter: 12.6 mm</p> <p>Min. bending radius:</p> <p>single: 5 x OD</p> <p>repeated: 10 x OD</p>	

Other cable lengths on request