

# EMG 22-DIO 4E

Order No.: 2950048




<http://eshop.phoenixcontact.ch/phoenix/treeViewClick.do?UID=2950048>

Diode module, with 4 diodes, individually wired, diode type 1N 4007



## Commercial data

EAN	 4 017918 083922
Pack	10 pcs.
Customs tariff	85411000
country of origin	DE
Catalog page information	Page 734 (IF-2011)

## Product notes

WEEE/RoHS-compliant since:  
01/02/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### General data

Diode type	1 N 4007
Max. operating voltage	250 V AC
Peak reverse voltage per diode	1300 V
Reverse current per diode	5 $\mu$ A

Conducting state voltage per diode	Approx. 0.8 V
Conducting state current per diode	0.7 A (with single load) 0.5 A (with simultaneous loads)
Width	22.5 mm
Height	75 mm
Depth	55 mm
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Surge voltage category	III, basic insulation (as per EN 50178)
Mounting position	Any
Assembly instructions	In rows with zero spacing

#### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection method	Screw connection

#### Certificates



Certification GOST

#### Accessories

Item	Designation	Description
------	-------------	-------------


#### Marking

2947035	EMG-GKS 12	Equipment marker, width 12 mm
---------	------------	-------------------------------

**Drawings**

Circuit diagram

---



**Address**

PHOENIX CONTACT AG  
Zürcherstrasse 22  
8317 Tagelswangen, Schweiz  
Phone ++41 (0) 52 354 55 55  
Fax ++41 (0) 52 354 56 99  
<http://www.phoenixcontact.ch>



Phoenix Contact  
Technical modifications reserved;