


ENERGIZER E92

AAA



Industry Standard Dimensions




Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-24A, IEC-LR03
Nominal Voltage:	1.5 volts
Nominal IR:	150 to 300 milliohms (fresh)*
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	11.5 grams (0.4 oz.)
Typical Volume:	3.8 cubic centimeters (0.2 cubic inch)
Jacket:	Plastic Label
Shelf Life:	7 years at 21°C (80% of initial capacity)
Terminal:	Flat Contact

* For additional information, please reference the [IR technical white paper](#).

Milliamp-Hours Capacity


Continuous discharge to 0.8 volts at 21°C



Device Selection Guide:

Photoflash	
Games, Digital Audio	
Lighting	
Remote Control	
Radio	

Battery Selection Indicator



Important Notice


This data sheet contains typical information specific to products manufactured at the time of its publication.
© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER E92

AAA


Constant Power Performance

Typical Characteristics (21°C)




Constant Current Performance

Typical Characteristics (21°C)




Constant Power Performance

Discharge Characteristics (21°C)




Constant Current Performance

250 mA Discharge (-20°C / 0°C / 21°C)




Industry Standard Tests (21°C)


LIGHTING
5.1 ohm LIF




REMOTE
24 ohm 15 sec/ min 8 hrs/ day



TAPE-GAME-DIGITAL AUDIO
100 mA 1 hr/ day



PHOTOFLASH
600 mA 10 sec/ min 1 hr/ day



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.
© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.



Eveready Battery Company, Inc.

533 Maryville University Drive
St. Louis, MO 63141
Telephone 1-800-383-7323
Internet: www.energizer.com

Engineering Data


AAA

Alkaline 1.5V

No Added Mercury or Cadmium

ENERGIZER NO. E92

Dimensions (mm)



Millimeters	Inches
0.10	0.004
0.80	0.031
3.80	0.15
9.50	0.374
10.50	0.413
42.35	1.667
42.85	1.687
43.30	1.705
44.50	1.752

Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

Designation: ANSI-24A, IEC-LR03

Battery Voltage: 1.5 Volts

Average Weight: 11.5 grams (0.4 oz.)

Volume: 3.8 cubic centimeters (0.2 cubic inch)

Average Service capacity (to 0.8 Volts / cell): 1250 mAh


(Rated Capacity at 25 mA continuous drain)

Cell: One No. 3-312 (size "AAA")


Jacket: Plastic Label

Shelf Life: 7 years


Temperature Effects Typical Service to 0.8 Volts




Constant Resistance Discharge Typical Service









Constant Current Discharge Typical Service





Typical Applications



Important Notice

This data sheet contains information specific to batteries manufactured at time of its publication. Please contact your Energizer representative for most current information. Contents herein do not constitute a warranty.