



Part no.: 50136824
MTKS 12x20M.5
Reflector

Figure can vary

Contents

- Technical data
- Dimensioned drawings

Part no.: 50136824 – MTKS 12x20M.5 – Reflector

Technical data

Basic data

Area of application	Food and pharmaceutical
---------------------	-------------------------

Mechanical data

Design	Rectangular
Mounting dimension, width	17.5 mm
Reflection surface width	12 mm
Mounting dimension, height	31 mm
Reflection surface height	20 mm
Mounting dimension, thickness	4 mm
Triple reflector size	0.3 mm
Material of base material	Stainless steel
Structure, active surface	Mikrotriple
Net weight	10.5 g
Type of fastening	Through-hole mounting
Compatibility of materials	Alcohol CleanProof+ ECOLAB H2O2

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 65 IP 67 IP 69K
----------------------	--------------------------

Classification

Customs tariff number	73269098
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings

All dimensions in millimeters

