

ELECTRONIC THERMOSTAT ETR011 AC 230 V, -20 TO +60 C



Figure similar

Model		
product brand name		SIVACON
Product designation		thermostat
<b>Design of the switching function</b>		CO contact
General technical data		
Operating temperature / minimum	°C	-45
<b>Mechanical service life (switching cycles) / typical</b>		50 000
Voltage		
<b>Inrush current / typical</b>	A	8
Main circuit		
Operating voltage / Rated value	V	230
Operating current / Rated value	A	8
Adjustable parameters		
<b>Adjustable temperature</b>		
• initial value	°C	-20
• Full-scale value	°C	60
Product details		
<b>Product component</b>		
• digital display		No
• hygrostat		No
Mechanical Design		
<b>Height</b>	mm	64.5
<b>Width</b>	mm	42

<b>Depth</b>	mm	38
<b>Mounting type</b>		terminal mounting
<b>Material / of the enclosure</b>		plastic

#### Environmental conditions

<b>Relative humidity / Reference value</b>	%	90
<b>Ambient temperature</b>		
• during storage / minimum	°C	-45
• during storage / maximum	°C	86

#### Certificates

<b>Equipment marking</b>		
• acc. to DIN EN 61346-2		K
• acc. to DIN EN 81346-2		K

#### General Product Approval



#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21701GC>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21701GC/all>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MR21701GC](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR21701GC)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015