

twist drill bit, solid carbide TiAlN, type N 3xD without internal cooling
 For universal use up to 1300 N/mm²



Application

Standard geometry for use up to a strength of 1300 N/mm².

Version

- Standard solid carbide tool with universal precision grinding

Advantage

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Cutting edge preparation minimises micro-fractures on the cutter
- TiAlN coating for up to 50% longer service life, dry processing possible in steel

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	80	70	60	32	30	150		140	150	150	130		80	90	30	30	30		

Art. No.	11153 383
Cutting material	VHM
Surface	TiAlN
Type	N
Tool holding device	HA parallel shank
Cutting edge diameter	8.30 mm
Chip flute length	37 mm
Length	79 mm
f steel 1000	0.12 mm/U
DIN	1897

EAN-Code

4050293327281