

Digimar height measuring device 816 CL

Motorised measuring carriage



Application:

For measuring external, internal, height, depth and distance dimensions, as well as diameters and reversal points in bores and shafts. Also allows dynamic measurements.

Delivery:

Height measuring device includes operating and display element, carrier 817 h 1, gauge slide K6/51, setting block 817 eb, operating instructions, charger, USB cable, protective cover, calibration certificate



Art. no.	35131 035
Brand	MAHR
Manufacturer Part Number	4429030
Weight	25 kg
Length measuring range	350 mm
Min./max. application area with standard gauge slide carrier	0-520 mm
Digit increment (can be pre-selected)	0.001 mm, 0.01 mm
Height gauge error limit	2.8 + L/300 (L in mm)
Repeat accuracy of drill hole	3 µm
Repetition accuracy, level	2 µm
Perpendicularity tolerance (front)	15 µm
Min./max. measurement force	0.8-1.2 N
Data transmission type	RS232
With air cushion equipment	Yes
Number of rechargeable batteries/batteries	1 PCS
Type of rechargeable battery/battery	NiMH
Max. battery operating time	14 h
Gross Weight	30.000 kg
Product Group	306

EAN

4059192017170