






133



134



- D** Anschluss **ausschließlich** durch ausgebildete Elektro-Fachkräfte.
- G** Electrical connection is to be made by trained electrical specialists **only**.
- F** Le branchement doit **uniquement** être effectué par des professionnels.
- I** Il collegamento deve essere eseguito **solo** da elettricisti specializzati.
- E** La conexión **sólo** debe ser realizada por electricistas debidamente formados.
- P** A ligação deve ser feita **exclusivamente** por profissional eléctrico especializado.
- CZ** Připojení smí **provádět** pouze kvalifikovaný personál.
- PL** Podłączenie **wyłącznie** przez specjalistów-elektryków.
- FI** Liittäminen kuuluu **ainoastaan** koulutettujen sähköalan ammattilaisten tehtäviin.
- RUS** Подключение проводится только специалистом-электриком.
- TR** Bağlantı **sadece** eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
- CN** 布线需由专业电工执行



134



$I_0 < 500 \text{ mA} / 24 \text{ V}$
133 000 75 24 V≈, ≤ 80 mA
134 000 75 24 V≈, ≤ 80 mA




(vgl. Abb. 6 / see Fig. 6 / ref. III 6)

Stufe Stage Niveau	Code 123	Tonart Tone type Tonalité	Frequenz Frequencies Fréquence
1	000	Hupenton, horn tone, trompe	
2	001	Dauerton, continuous, continu	2300 Hz
3	010	1 Hz Ton, 1 Hz tone, 1 Hz ton	2300 Hz
4	011	20 Hz Trillerton, 20 Hz whistle tone, 20 Hz trille	2300 Hz
5	100	ansteigend, rising, montant	800 - 970 Hz @ 1 Hz
6	101	ansteigend, rising, montant	2400 - 2850 Hz @ 7 Hz
7	110	abfallend, falling, incliné	1200 - 500 Hz @ 1 Hz
8	111	alternierend, alternating, alternant	800/1200 Hz @ 1 Hz




1 1a - 133 000 75
1b - 134 000 75


1a



1b




2




3 3a - 133 000 75
3b - 134 000 75


3a



3b




4




X3
X1

X3
X1
V+
-
L


5



6



7



310.133.001.0608

© D

 **WERMA**
SIGNALTECHNIK