

Appliance trolley with spoked wheel and support wheels

Load-bearing capacity 400 kg

fetra
TRANSPORT
Transportgeräte

Application:

For transporting large loads such as boilers on flat surfaces and especially on stairs

Execution:

- Very sturdy welded steel tube structure
- Supports with wide rubber profiles
- Toe plate with non-slip coating
- Support wheels, solid rubber, 160 x 40 mm, „no tracks“. As a result, the cart can be moved effortlessly when in a lowered state
- Locking device on the support wheels. This means that the support wheels can be used as brakes when descending stairs
- Height-adjustable handle bar can be rotated by 180°. This means that the grip position can be adjusted optimally for any transport situation

Delivery:

With wheel spiders. Without pneumatic wheels, without carrier spars, without tensioning belt



| | |
|---------------------------------|------------------|
| Art. no. | 50270 393 |
| Brand | FETRA |
| Manufacturer Part Number | 11052 |
| Toe plate width | 550 mm |
| Height | 1300 mm |
| Toe plate depth | 190 mm |
| Material of wheel | Solid rubber |
| Load-carrying capacity | 400 kg |
| Width | 700 mm |
| Surface | Powder-coated |
| Wheel diameter | 160 mm |
| Material | Steel pipe |
| Ability to climb stairs | Yes |
| Total stop optional | No |
| Gross Weight | 48.000 kg |
| Product Group | 5AB |

EAN

4017976210506