




ROHS-COMPLIANT

| LTR | REV. | DESCRIPTION | DATE |
|-----|------|-------------|------|
| | | | |

USB 3.0 A/M 9PIN
INS:BLUE(P.T 300C)



USB 3.0 B/M 9PIN
INS:BLUE(P.T 300C)



NOTE:

1.CABLE: UL-2725 [#28(7/0.127 T.C)×1P INS:Foam-PE+D.W(7/0.127 T.C)
+AL/MY+Hot-melt-Mylar]×2C+#28(7/0.127 T.C)×1P INS:Polyolefin
+#28(7/0.127 T.C)×2C INS:Polyolefin+AL/MY+B.D(85%)
PVC JACKET; OD:5.2±0.15mm COLOR:BLACK(NK-K01) REV 3.0.

2.CONNECTOR:

P1: USB 3.0 A TYPE MALE 9PIN CONTACT:30u",SHELL:NI-PLATED.

P2 :USB 3.0 B TYPE MALE 9PIN CONTACT:30u",SHELL:NI-PLATED.

3.HOOD:MOLDED TYPE,PVC 45P, COLOR:BLACK(NK-K01).

4.ELECTRICAL TEST:

- (1)100% OPEN SHORT & MIS WIRE TEST.
- (2)CONTACT RESISTANCE 3 ohm Max .
- (3)INSULATION RESISTANCE 10M ohm Min .
- (4)HI-POT DC300V

5.PACKING:EACH PC / POLY BAG.

| P1 | | PIN OUT | P2 | |
|-------|---|---------|-------|-------------------------|
| 1 | — | RED | 1 | PWR |
| 2 | — | WHITE | 2 | UTP_D- |
| 3 | — | GREEN | 3 | UTP_D+ |
| 4 | — | BLACK | 4 | GND_PWRrt |
| 5 | — | BLUE | 5 | SDP1- |
| 6 | — | YELLOW | 6 | SDP1+ |
| 7 | — | D.W | 7 | SDP1_Drain & SDP2_Drain |
| 8 | — | PURPLE | 8 | SDP2- |
| 9 | — | ORANGE | 9 | SDP2+ |
| SHELL | | B.D | SHELL | |

| Tolerance Inch M/M | | | Title | | | |
|--------------------|------|-----|-------------------------|-----|------------------------|-----------------|
| .X | .015 | .30 | USB 3.0 A/M - B/M CABLE | | | |
| .XX | .010 | .10 | Customer P/N | | | |
| .XXX | .005 | .05 | App'd | | | |
| Draw | | | Scale | | Units | Customer: E-DIR |
| FANNIE 11/12/09' | | | NONE | M/M | Third Angle Projection | |
| Chek | | | Dwg No. 170-3450 | | REF: I | Sheet.1/1 |
| Engr | | | | | | |

| DWG | L(mm) | T(mm) |
|------------|-------|-------|
| 170-3450-3 | 3000 | 30 |
| 170-3450-2 | 2000 | 30 |
| 170-3450-1 | 1000 | 20 |