








FINISH TYPE	TIN		15MICROINCH GOLD			
	CKT	HDR ASSY PN	HDR ASSY PN	A	B	C
2	2125280200	2125280201	3.85	NA	NA	2.95
4	2125280400	2125280401	6.85	3.00	NA	2.95
6	2125280600	2125280601	9.85	6.00	NA	2.95
8	2125280800	2125280801	12.85	9.00	4.70	7.70
10	2125281000	2125281001	15.85	12.00	7.70	10.70
12	2125281200	2125281201	18.85	15.00	10.70	13.70
14	2125281400	2125281401	21.85	18.00	13.70	16.70
16	2125281600	2125281601	24.85	21.00	16.70	19.70
18	2125281800	2125281801	27.85	24.00	19.70	22.70
20	2125282000	2125282001	30.85	27.00	22.70	25.70
22	2125282200	2125282201	33.85	30.00	25.70	28.70
24	2125282400	2125282401	36.85	33.00	28.70	31.70



PCB LAYOUT: COMPONENT SIDE
RECOMMEND PCB THICKNESS: 1.57mm




FIRST CKT INDICATOR
(APPROX. LOCATION SHOWN FOR REF.)




- NOTES:
- HOSING MATERIAL: GLASS FILLED LIQUID CRYSTAL POLYMER, UL 94V-0, COLOR: BLACK
TERMINAL MATERIAL: HIGH COPPER ALLOY
 - FINISH:
OPTION 1: REFLOW MATTE TIN OVER NICKEL
OPTION 2: SELECT 15MICROINCH GOLD AND SELECT MATTE TIN OVER NICKEL.
 - PRODUCT SPECIFICATION : 2064600000-PS
 - PRODUCT TEST SUMMARY: 2064600000-TS
 - TRAY PACK : 2125280000-PK
 - MATE WITH RECEPTACLE 206461
 - THIS PART CONFORMS TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.


SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
	DIMENSION UNITS	SCALE				
▽ = 0	mm	5:1	EC NO: 637768			
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: ALUO02	2020/05/18	MICRO-FIT + DUAL ROW R/A HEADER ASSY.	
▽ = 0	ANGULAR TOL ± °		CHK'D: AYIN	2020/05/28		
▽ = 0	4 PLACES ±		APPR: AYIN	2020/05/28	PRODUCT CUSTOMER DRAWING	
▽ = 0	3 PLACES ±		INITIAL REVISION:			
▽ = 0	2 PLACES ± 0.25		DRWN: MUM	2019/03/08	DOCUMENT NUMBER	
▽ = 0	1 PLACE ± 0.36		APPR: AYIN	2019/09/27		
▽ = 0	0 PLACES ±		THIRD ANGLE PROJECTION		DOC TYPE	
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING	SERIES		DOC PART
▽ = 0			A2-SIZE	212528	REVISION	
			MATERIAL NUMBER	CUSTOMER		SHEET NUMBER
			2125280000	GENERAL MARKET	1 OF 2	




2 CKT




4 CKT




6 CKT




8 CKT




10 CKT




12 CKT




14 CKT




16 CKT




18 CKT



20 CKT



22 CKT



24 CKT

SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	5:1
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	± 0.25
	1 PLACE	± 0.36
	0 PLACES	±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION
		DRAWING
		SERIES
		MATERIAL NUMBER
		CUSTOMER
		SHEET NUMBER

CURRENT REV DESC:
 EC NO: 637768
 DRWN: ALUO02 2020/05/18
 CHK'D: AYIN 2020/05/28
 APPR: AYIN 2020/05/28

INITIAL REVISION:
 DRWN: MUM 2019/03/08
 APPR: AYIN 2019/09/27

molex

MICRO-FIT + DUAL ROW R/A HEADER ASSY.

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
2125280000	PSD	000	A3
MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
	GENERAL MARKET	2 OF 2	