

Die, HSS MF left, pre-slotted and 1.75 thread chamfer
for universal use up to 700 N/mm²



Application

For cutting fine metric threads externally in the material groups of steel and non-ferrous metals up to a strength of 700 N/mm².

Version

- left die, tol. 6 g with spiral point, pre-slotted and 1.75 pitch

Advantage

- universal use for maximum flexibility during application
- micro cut edge treatment and special lapping method for excellent process reliability and long service life



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.		
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC	
	●					●					●	●								

Art. No.	13442 126
Thread type	Metric fine thread
Cutting material	HSS
Tolerance of dies	6 g
Thread type x nominal diameter	MF12
Pitch	1.5 mm
Outer diameter	38 mm
Height	10 mm
Cutting direction	Left-hand cutting

EAN-Code

4050293115505