

FI/LS-PROTECTOR TYPE A (PSE), D=70MM IFN  
300MA, 10KA, 4-POLEE C 125A FOR PARTIAL  
SHUTDOWN



Figure similar

Model		
product brand name		SENTRON
Product designation		RCBO
<b>Design of the product</b>		selective
<b>version</b>		RCCB/MCB
General technical data		
<b>Number of poles</b>		4
<b>Number of poles / Note</b>		4P
<b>Number of poles / with protection</b>		4
<b>Tripping characteristic class</b>		C
<b>circuit-breaker / Design</b>		5SU1
<b>Mechanical service life (switching cycles) / typical</b>		10 000
<b>Overvoltage category</b>		III
Voltage		
<b>Surge current resistance / at (8/20) <math>\mu</math>s</b>	kA	5
Supply voltage		
Supply voltage frequency / Rated value	Hz	50
Protection class		
<b>Protection class IP</b>		IP20, if the distribution board is installed, with connected conductors
<b>Energy limiting class</b>		3
Switching capacity		
<b>Switching capacity current</b>		

- acc. to EN 60898 / Rated value
- acc. to IEC 60947-2 / Rated value

kA	10
kA	15

### Electricity

<b>Tripping residual current / Rated value</b>	mA	300
rated current $I_n$ / IEC, DIN/VDE / at 40 Cel	A	115.62
Current / with AC / Rated value	A	125

### Product details

Product feature / Touch protection		Yes
<b>Product property</b>		
• halogen-free		Yes
• silicon-free		Yes

### Product function

Product function / neutral conductor switching		Yes
--	--	-----

### Number

<b>Number of test cycles / for environmental testing / acc. to IEC 60068-2-30</b>		26
---	--	----

### Connections

<b>Connectable conductor cross-section / stranded</b>		
• minimum	mm <sup>2</sup>	6
• maximum	mm <sup>2</sup>	50
<b>Connectable conductor cross-section</b>		
• solid		
— minimum	mm <sup>2</sup>	6
— maximum	mm <sup>2</sup>	50
• finely stranded / with core end processing		
— minimum	mm <sup>2</sup>	6
— maximum	mm <sup>2</sup>	35
<b>Tightening torque / with screw-type terminals</b>		
• minimum	N·m	3
• maximum	N·m	3.5
Position / of power supply cord		Either top or bottom

### Mechanical Design

<b>Height</b>	mm	90
<b>Width</b>	mm	198
<b>Depth</b>	mm	77
<b>mounting position</b>		any
<b>Installation depth</b>	mm	70
<b>Number of width units</b>		11

### Environmental conditions

<b>Influence of the surrounding temperature</b>		Max. 95% humidity
---	--	-------------------

### Ambient temperature

• minimum	°C	-25
• maximum	°C	55
• during storage / minimum	°C	-40
• during storage / maximum	°C	75

### Certificates

#### Equipment marking

• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

### General Product Approval



[other](#)

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SU16447WK82>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SU16447WK82/all>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=5SU16447WK82](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5SU16447WK82)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015