

## Micrometer

Robust, light metal bracket

Hartig

### Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

### Execution:

- Scale with anti-glare, brushed chromium plated finish
- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- Robust, light metal bracket
- Measuring spindle hardened and ground from one piece
- Bolted hand-warmth insulation plates

### Advantage:

- Measuring spindle increment: 1 mm (direct 1/100 reading for prevention of reading errors, no need to add the 0.5 mm value)

### Delivery:

In high-quality wooden case



<b>Art. no.</b>	<b>31345 070</b>
<b>Brand</b>	HARTIG
<b>Manufacturer Part Number</b>	1168 150-175 H
<b>Min./max. length measuring range</b>	150-175 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	8 mm
<b>Measuring spindle increments</b>	1 mm
<b>Spindle clamping</b>	No
<b>Display</b>	Nonius
<b>DIN</b>	863
<b>Calibration Group</b>	D
<b>Gross Weight</b>	1.300 kg
<b>Product Group</b>	316