

Measuring beams

lightweight design, accuracy class I++



Application:

For simple and accurate checking of straightness and parallelism deviations on travelling axes of e.g. coordinate measuring instruments and machine tools.

Execution:

- Carefully selected and flawless South African hard stone material – Diabas.
- torsion-resistant, distortion-proof, anti-magnetic
- Exactly 2-sided. The two narrow longitudinal surfaces are finely machined to a high-quality finish to be flat and parallel to one another
- accuracy I++: finely ground and lapped
- screwed-on handles on both sides
- Calibration certificate included in the scope of delivery. measurement results are based on national standards
- DAkkS calibration certificate available on request

Advantage:

- solid material with perforations, reducing weight by approx. 40%



| | |
|--------------------------------|--------------------|
| Art. no. | 35342 520 |
| Brand | JFA |
| Length x width x height | 2000 x 80 x 250 mm |
| JFA accuracy I++ | 0.004 mm |
| Weight | 65 kg |
| Gross Weight | 65.000 kg |
| Product Group | 341 |