

Pneumatic rod grinder RRG-2690

Angled version



Application:

for deburring, finishing welding and cast seams as well as other light grinding work

Advantage:

- Movable air connection guarantees easy mobility of the grinder
- The tool performance can be adjusted via the adjustment wheel if desired by the operator



Art. no.	75066 054
Model	RRG-2690
Design	Offset
Valve design	Lever valve
Max. idle speed	20000 rpm
Power output	260 W
Air consumption	7.5 l/s
Connection thread	1/4 inch
Sound-pressure level	84 dB
Inner hose diameter	10 mm
Length	166 mm
Max. clamping diameter	6 mm
Collet chuck diameter	6 mm
Suitable for max. sanding block diameter	35 mm
Weight	0.6 kg

EAN-Code

8717981400102