

Product information

97 53 14

Self-Adjusting Crimping Pliers for wire ferrules

With lateral access



- Hexagonal crimp layout for near round form, particularly suitable for confined connections
- Automatic self-adjustment to wire ferrules with ratcheting mechanism ensuring a complete crimping cycle for consistent, reliable and fast crimping
- Reliable hexagonal crimping of wire ferrules from 0.08 to 16 mm² (AWG 6) by simply turning and setting the adjusting wheel and all twin wire ferrules up to 2 x 10 mm² (AWG 2 x 8)
- Automatic adaptation by self-adjustment to the wire ferrule size for precise and quick crimping
- Crimping pressure calibrated in the factory for precise crimping
- Optimum transmission of force due to toggle lever for fatigue-reduced operation
- Ergonomic and comfortable handle, smooth operation and lightweight
- Crimping of wire ferrules according to DIN 46228 parts 1+4
- Special quality chrome vanadium electric steel, oil-hardened



| General | |
|-----------------|----------------------------|
| Article No. | 97 53 14 |
| EAN | 4003773041474 |
| Pliers | burnished |
| Handles | with multi-component grips |
| Weight | 445 g |
| Dimensions | 180 x 75 x 21 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

| Technical details | |
|--------------------------------|---------------------------|
| Application | Wire ferrules |
| Capacity in square millimetres | 0.08 — 16 mm ² |
| Number of crimping positions | 1 |
| AWG | 28 — 8 |

technical change and errors excepted







