

## Elastic machine mounting elements

**EFFBE**

### Application:


The elements prevent the transfer of machine vibrations and impacts to the floor and building.

### Execution:

- For erecting machines without foundations and floor anchor points
- Insulated against vibrations
- Non-slip
- Resistant to oil and ageing
- Without anchor points
- Number of fastening holes = number of elements
- Height-adjustable
- Machine weight divided by the number of mounts to be supported = weight per mount
- Elements are selected according to the load table
- Insulated against structure-borne noise and impact-absorbing

### Advantage:

- Long service life and easy to mount
- Building damage cancelled out through vibration
- Structure-borne noise can spread



<b>Art. no.</b>	<b>26400 010</b>
<b>Brand</b>	EFFBE
<b>Manufacturer Part Number</b>	FB60015149
<b>Size</b>	1
<b>Height</b>	25 mm
<b>Adjustment travel of levelling range</b>	15 mm
<b>Thread dimension</b>	M10
<b>Screw length</b>	80 mm
<b>Load-carrying capacity per element for presses in general with stroke speed up to 100/min</b>	450 kg
<b>Load-carrying capacity per element for lathes</b>	220 kg
<b>Load-carrying capacity per element for milling machines</b>	300 kg
<b>Load-carrying capacity per element for surface grinders</b>	220 kg
<b>Load-carrying capacity per element for machinery in general</b>	480 kg
<b>Max. static loading</b>	600 kg
<b>Gross Weight</b>	0.410 kg
<b>Product Group</b>	265