

Tilting drum with roll-off mechanism—low overall height

Carrying capacity 750-1500 kg, without wheels

Application:

For the collection and disposal of all types of bulk goods and solid materials.

Execution:

- Favourable load centre
- Tilting at any height using a wire rope from the stacker seat
- Sheet metal tray with surrounding edge profile
- Sturdy base frame with fork pockets
- Protection against accidental slipping and tipping
- All dimensions without wheels

Delivery:

Available upon request: zinc-plated cover, can be opened on both sides

Goods supplied without packaging as standard. Packaging available for an additional charge.



Art. no.	50266 816
Volume	2.1 m ³
Length	1720 mm
Width	1870 mm
Tipper edge height	963 mm
Height	1095 mm
Fork pocket clearance	600 mm
Fork pocket size (W x H)	200 x 80 mm
With drain valve	No
With stacker seat tilt function	Yes
With perforated sheet	No
Load-carrying capacity	1500 kg
Surface	Lacquered
Colour	Yellow orange RAL 2000
Gross Weight	280.000 kg
Product Group	5AI