

FUSE-TERMINAL BLOCK 5X20MM 4 MM2, 6,2 MM  
WIDTH SCHWARZ 250V LED

Model		
Type of light source / as fault indicator		LED
Design of the fuse link		glass fuse 5x20 mm
Design of fuse holder		pluggable
General technical data		
Insulation material		thermoplastic
Terminal contact spacing	mm	6.2
Supply voltage		
Type of voltage / for supply of the fault indicator		AC/DC
Protection class		
Combustibility class acc. to UL 94		V0
Main circuit		
Operating voltage / Rated value	V	500
Operating current / Rated value	A	6.3
Appearance		
Color		black
Product details		
Product component / required / connection plate		Yes
Number		
Number of terminal levels		1
Connections		
<b>Connectable conductor cross-section / stranded</b>		
• minimum	mm <sup>2</sup>	0.25
• maximum	mm <sup>2</sup>	4
<b>Connectable conductor cross-section</b>		
• solid		
— minimum	mm <sup>2</sup>	0.2
— maximum	mm <sup>2</sup>	6
• finely stranded		
— with core end processing / minimum	mm <sup>2</sup>	0.25
— with core end processing / maximum	mm <sup>2</sup>	4
— without core end processing / minimum	mm <sup>2</sup>	0.2

— without core end processing / maximum

mm<sup>2</sup>

4

Position / of the terminal

top

## Mechanical Design

Height / with lowest-profile installation

mm

62.5

Length

mm

56

Mounting type

DIN rail 35 mm

Material / of the insulating body

Thermoplast

## General Product Approval

## Declaration of Conformity



GOST



UL



EG-Konf.

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WH60001MG88>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8WH60001MG88/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8WH60001MG88](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8WH60001MG88)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015