

# TECHNICAL DATA SHEET



## PVC Insulation Sleeving

RoHS  
Compliant

Specification	
RoHS compliant	Yes
Continuous temperature	-20°C to +70°C
Insulation resistance	1010 Ohm/cm
Dialectric strength	20kV/mm
Tensile strength	15MPa
Elongation at break	220%
Hardness	BSS20-30
Self extinguishing	30 seconds

Code	Description	Colour	Inside Dia (mm)	Nominal Wall (mm)	Length (m)
APVC2B	PVC Sleeving Black 2mm x 100m	Black	2.00	0.40	100
APVC2GRY	PVC Sleeving Grey 2mm x 100m	Grey	2.00	0.40	100
APVC2BL	PVC Sleeving Blue 2mm x 100m	Blue	2.00	0.40	100
APVC2RED	PVC Sleeving Red 2mm x 100m	Red	2.00	0.40	100
APVC2BRN	PVC Sleeving Brown 2mm x 100m	Brown	2.00	0.40	100
APVC2GY	PVC Sleeving Green/ Yellow 2mm x 100m	Green/Yellow	2.00	0.40	100
APVC3B	PVC Sleeving Black 3mm x 100m	Black	3.00	0.40	100
APVC3GRY	PVC Sleeving Grey 3mm x 100m	Grey	3.00	0.40	100
APVC3BL	PVC Sleeving Blue 3mm x 100m	Blue	3.00	0.40	100
APVC3RED	PVC Sleeving Red 3mm x 100m	Red	3.00	0.40	100
APVC3BRN	PVC Sleeving Brown 3mm x 100m	Brown	3.00	0.40	100
APVC3GY	PVC Sleeving Green/ Yellow 3mm x 100m	Green/Yellow	3.00	0.40	100
APVC4B	PVC Sleeving Black 4mm x 100m	Black	4.00	0.40	100
APVC4GRY	PVC Sleeving Grey 4mm x 100m	Grey	4.00	0.40	100
APVC4BL	PVC Sleeving Blue 4mm x 100m	Blue	4.00	0.40	100
APVC4RED	PVC Sleeving Red 4mm x 100m	Red	4.00	0.40	100
APVC4BRN	PVC Sleeving Brown 4mm x 100m	Brown	4.00	0.40	100
APVC4GY	PVC Sleeving Green/ Yellow 4mm x 100m	Green/Yellow	4.00	0.40	100
APVC5GRY	PVC Sleeving Grey 5mm x 100m	Grey	5.00	0.45	100

**Important Notice :** This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.



# TECHNICAL DATA SHEET



## PVC Insulation Sleeving

RoHS  
Compliant

Specification	
RoHS compliant	Yes
Continuous temperature	-20°C to +70°C
Insulation resistance	1010 Ohm/cm
Dialectric strength	20kV/mm
Tensile strength	15MPa
Elongation at break	220%
Hardness	BSS20-30
Self extinguishing	30 seconds

Code	Description	Colour	Inside Dia (mm)	Nominal Wall (mm)	Length (m)
APVC6B	PVC Sleeving Black 6mm x 100m	Black	6.00	0.45	100
APVC6GRY	PVC Sleeving Grey 6mm x 100m	Grey	6.00	0.45	100
APVC6BL	PVC Sleeving Blue 6mm x 100m	Blue	6.00	0.45	100
APVC6RED	PVC Sleeving Red 6mm x 100m	Red	6.00	0.45	100
APVC6BRN	PVC Sleeving Brown 6mm x 100m	Brown	6.00	0.45	100
APVC6GY	PVC Sleeving Green/ Yellow 6mm x 100m	Green/Yellow	6.00	0.45	100
APVC10B	PVC Sleeving Black 10mm x 100m	Black	10.00	0.45	100
APVC10GRY	PVC Sleeving Grey 10mm x 100m	Grey	10.00	0.45	100
APVC10BL	PVC Sleeving Blue 10mm x 100m	Blue	10.00	0.45	100
APVC10RED	PVC Sleeving Red 10mm x 100m	Red	10.00	0.45	100
APVC10BRN	PVC Sleeving Brown 10mm x 100m	Brown	10.00	0.45	100
APVC10WHI	PVC Sleeving White 10mm x 100m	White	10.00	0.45	100
APVC10GY	PVC Sleeving Green/ Yellow 10mm x 100m	Green/Yellow	10.00	0.45	100
APVC16B	PVC Sleeving Black 16mm x 100m	Black	16.00	0.45	100
APVC16GRY	PVC Sleeving Grey 16mm x 100m	Grey	16.00	0.45	100
APVC16BL	PVC Sleeving Blue 16mm x 100m	Blue	16.00	0.45	100
APVC16RED	PVC Sleeving Red 16mm x 100m	Red	16.00	0.45	100
APVC16BRN	PVC Sleeving Brown 16mm x 100m	Brown	16.00	0.45	100
APVC16GY	PVC Sleeving Green/ Yellow 16mm x 100m	Green/Yellow	16.00	0.45	100

**Important Notice :** This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

