

SIRIUS SAFETY RELAY FOR SAFETY-ORIENTED STANDSTILL MONITORING, 24V DC, 45.0MM, SPRING-LOADED TERMINAL, FK INSTANT.: 3NO 1NC, FK DELAYED: 0, MK: 3, AUTO START, BASIC UNIT, MAX. ACHIEV. CAT. EN954-1: 4, MAX. ACHIEV. SIL TO IEC61508:3,

General technical data:		
product brand name		SIRIUS
Product designation		safety relays
Design of the product		for safe stoppage monitoring
Protection class IP of the enclosure		IP20
Protection class IP of the terminal		IP20
Protection against electrical shock		finger-safe
Insulation voltage Rated value	V	690
Ambient temperature		
• during storage	°C	-40 ... +75
• during operation	°C	-25 ... +60
Air pressure acc. to SN 31205	kPa	90 ... 106
Relative humidity during operation	%	10 ... 95
Installation altitude at height above sea level maximum	m	2 000
Vibration resistance acc. to IEC 60068-2-6		10 ... 55 Hz: 0.35 mm
Shock resistance		8g / 10 ms
Surge voltage resistance Rated value	V	6 000
EMC emitted interference		IEC 61000-6-2, IEC 61000-6-3
Installation environment regarding EMC		This product is suitable for Class A environments only. It can cause undesired radio-frequency interference in residential environments. If this is the case, the user must take appropriate measures.
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		KT
Equipment marking acc. to DIN EN 61346-2		F

Number of sensor inputs • 1-channel or 2-channel		1
Design of the cascading		none
Type of the safety-related wiring of the inputs		measuring inputs
Product property cross-circuit-proof		No
Safety Integrity Level (SIL) • acc. to IEC 61508 • for delayed release circuit acc. to IEC 61508		SIL3 SIL3
SIL Claim Limit (subsystem) acc. to EN 62061		3
Performance level (PL) • acc. to EN ISO 13849-1 • for delayed release circuit acc. to EN ISO 13849-1		e e
Category acc. to EN 954-1		4
Category acc. to EN ISO 13849-1		4
Hardware fault tolerance acc. to IEC 61508		1
Safety device type acc. to IEC 61508-2		Type B
PFHD with high demand rate acc. to EN 62061	1/h	0.0000000015
T1 value for proof test interval or service life acc. to IEC 61508	y	20
Number of outputs as contact-affected switching element • as NC contact — for signaling function instantaneous contact • as NO contact — safety-related instantaneous contact — safety-related delayed switching		2 4 0
Number of outputs as contact-less semiconductor switching element • safety-related — delayed switching — instantaneous contact • for signaling function — delayed switching — instantaneous contact		0 0 0 2
Stop category acc. to DIN EN 60204-1		0

General technical data:

Design of input • cascading input/functional switching • feedback input • Start input		No Yes No
Type of electrical connection Plug-in socket		Yes

Operating frequency maximum	1/h	1 200
Switching capacity current		
<ul style="list-style-type: none"> • of semiconductor outputs <ul style="list-style-type: none"> — for signaling function at DC-13 at 24 V • of the NO contacts of the relay outputs <ul style="list-style-type: none"> — at DC-13 — at 24 V — at AC-15 — at 115 V — at 230 V • of the NC contacts of the relay outputs <ul style="list-style-type: none"> — at DC-13 — at 24 V — at AC-15 — at 115 V — at 230 V 	A A A A A A A A	0.1 2 3 3 2 2 2
Thermal current of the switching element with contacts maximum	A	5
Electrical endurance (switching cycles) typical		200 000
Mechanical service life (switching cycles) typical		50 000 000
Design of the fuse link for short-circuit protection of the NO contacts of the relay outputs required		quick: 5 A
Adjustable OFF-delay time after opening of the safety circuits	s	0.2 ... 6

Control circuit/ Control:

Type of voltage of the control supply voltage		DC
Control supply voltage 1		
<ul style="list-style-type: none"> • for DC Rated value 	V	24
Operating range factor control supply voltage rated value of the magnet coil		
<ul style="list-style-type: none"> • for DC 		0.9 ... 1.2

Installation/ mounting/ dimensions:

mounting position		any
Mounting type		screw and snap-on mounting
Width	mm	45
Height	mm	138.5
Depth	mm	120

Connections/ Terminals:

Type of electrical connection		spring-loaded terminals
Type of connectable conductor cross-section		
<ul style="list-style-type: none"> • solid • finely stranded 		2x (0.25 ... 1.5 mm ²)

— with core end processing	2 x (0.25 ... 1.5 mm ²)
— without core end processing	2x (0.25 ... 1.5 mm ²)
Type of connectable conductor cross-section for AWG conductors	
• solid	2x (24 ... 16)
• stranded	2x (20 ... 16)

Product Function:

Product function	
• Light barrier monitoring	No
• Standstill monitoring	Yes
• protective door monitoring	No
• Automatic start	No
• magnetically operated switch monitoring NC-NO	No
• rotation speed monitoring	No
• laser scanner monitoring	No
• monitored start-up	No
• Light array monitoring	No
• magnetically operated switch monitoring NC-NC	No
• EMERGENCY OFF function	No
• Pressure-sensitive mat monitoring	No
Suitability for interaction press control	No
Suitability for use	
• safety switch	Yes
• position switch monitoring	No
• EMERGENCY-OFF circuit monitoring	No
• valve monitoring	No
• tactile sensor monitoring	No
• magnetically operated switch monitoring	No
• safety-related circuits	Yes

Certificates/ approvals:

Certificate of suitability	UL, CSA, EN 60204-1, EN ISO 12100, EN 954-1, IEC 61508
• TÜV (German technical inspectorate) certificate	Yes
• UL approval	Yes
• BG BIA certificate	Yes

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity
--------------------------	---------------------------------------	---------------------------



[Type Examination](#)



Test Certificates	other
-------------------	-------

[Special Test Certificate](#)

[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TK28100BA02>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TK28100BA02>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TK28100BA02&lang=en



last modified:

16.03.2015